

# 12-ft. Component Video Gold Cable (3 x RCA M/M)

MODEL NUMBER: **A008-012**



## Description

Tripp Lite's premium Component Video Gold Cable separates color into its primary components (Red, Green, Blue), using three cables to transmit three distinct signals. This provides brighter, more accurate colors and sharper images, exceeding the performance of Composite and S-Video.

## Features

- Superb video clarity resulting in brighter colors and sharper images
- Premium grade 99.99% pure solid copper coaxial conductors with silver plating
- True 75 ohm impedance for widest bandwidth
- 6-cut, RCA connector, with split tip center pin, ensures a precise connection
- 24kt gold plating resists corrosion and provides increased durability
- Color coded connectors for easy identification
- Abrasion resistant flexible PVC jacket

## Specifications

OVERVIEW	
UPC Code	037332121844
CONNECTIONS	
Side A - Connector 1	RCA (MALE)
Side B - Connector 1	RCA (MALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black

## Highlights

- Constructed of high quality, 99.99% pure solid copper coaxial cable with silver plating for best high frequency response
- 75 ohm impedance for maximum bandwidth
- Double-shielded construction provides superior protection against EMI/RFI
- Excellent noise isolation with 100% aluminum foil/braid shielding

## System Requirements

- Home theater equipment with RCA digital audio/video connectors

## Package Includes

- 12 ft. Component Video Gold Cable



Powering Business Worldwide



Cable Length (ft.)	12
Cable Length (m)	3.66
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	1.18
Shipping Weight (kg)	0.54
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.