

Eco-Surge 8-Outlet Surge Protector, 6-ft. Cord, 1080 Joules

MODEL NUMBER: AV86G



Highlights

- 8 outlets / 6-ft. cord
- 1080 joule rating
- Auto/Manual switch offers GREEN energy savings or standard protection
- Unique Netbook switch allows user to select wattage

Package Includes

- AV86G ECO-SURGE Energy-Saving Surge Suppressor

Description

Tripp Lite's AV86G offers reliable, GREEN surge technology that protects your computer and peripherals, the environment and your wallet. The ECO-SURGE offers a unique Netbook switch that allows users to select wattage, making ECO-SURGE the only green surge suppressors compatible with all PC's, Notebooks and Netbooks. Energy -saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. AV86G offers 8 total outlets, 6 foot cord with space saving angled plug and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Integrated child-safety outlet covers safely seal off unused outlets. Attractive black suppressor housing with keyhole mounting tabs and 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).
PLUG/OUTLETS: Input: NEMA5-15P/Output: 8 NEMA5-15R/6 ft. AC line cord
ELECTRICAL: 120V AC, 60Hz, 15A (Requires NEMA5-15R wall receptacle)
FORMAT: Corded multi-outlet strip with transformer spaced outlets
SUPPRESSION AC: 150V RMS Clamping/1080 joules

Features

- Allows user to switch between GREEN (auto) power save mode and standard (manual) surge protection mode
- 8 total AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- "Master" outlet controls power flow for 1 primary device and up to 5 peripheral devices
- Five "Power Save" outlets cut AC power when not in use--perfect for non-essential peripherals like monitors, printers, scanners, speakers, lamps, etc.
- Two "Always-On" outlets provide continuous power for interminable devices such as modems, routers, external hard drives, cordless phones and fax machines
- User-selectable wattage switch accommodates PC's, Netbooks and other Internet research tools
- 1080 joules AC surge suppression shields equipment from the strongest surges and line noise
- Long 6 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets



Powering Business Worldwide



- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive black suppressor housing with keyhole mounting tabs allow versatile placement options
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

| OVERVIEW | |
|------------------------------------|---|
| UPC Code | 037332155573 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Cord Gauge Type | 14 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 72000 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 6 |
| Right-Angle Plug | Yes |
| Input Cord Length (m) | 1.83 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 60 Hz |
| Output Receptacles | (8) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (6) Yes |
| Outlet Orientation | Single row of 5, plus a second row of 3 for transformer accommodation |
| Right-Angle Outlets | Yes |
| Outlet Safety Covers Detail | Includes built-in sliding outlet safety covers |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | Yes |
| Switches | Combination AC circuit breaker and 2 position red illuminated on/off power switch |
| Diagnostic LED Details | Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

| | |
|--|--|
| AC Suppression Joule Rating | 1080 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| UL1449 Let Through Rating | 400 L-G, 400 L-N, 400 N-G |
| EMI / RFI Filtering | Up to 40 dB |
| Automatic Shut-Off | No |
| DATALINE SURGE SUPPRESSION | |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| Telephone/DSL Protection | No |
| PHYSICAL | |
| Color | Black |
| Material of Construction | Plastic |
| Power Cord Color | Black |
| Housing Color | Black |
| Mounting Holes or Slots | Yes |
| Receptacle Color | Gray; green |
| Shipping Dimensions (hwd / in.) | 11.90 x 2.00 x 8.80 |
| Shipping Dimensions (hwd / cm) | 30.23 x 5.08 x 22.35 |
| Shipping Weight (lbs.) | 2.00 |
| Shipping Weight (kg) | 0.91 |
| Unit Dimensions (hwd / in.) | 1.510 x 4.860 x 9.550 |
| Unit Dimensions (hwd / cm) | 3.84 x 12.34 x 24.26 |
| Unit Weight (lbs.) | 1.81 |
| Unit Weight (kg) | 0.82 |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$75,000 Ultimate Lifetime Insurance |



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.