

TAA-Compliant AVR Series 120V 750VA 450W Ultra-Compact Line-Interactive UPS with USB port

MODEL NUMBER: **AVR750UTAA**



Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 750VA ultra-compact 120V line interactive UPS
- Corrects brownouts and overvoltages from 83V to 147V
- 6 UPS outlets, 6 surge-only outlets, USB, TEL/DSL protection, Wall mountable, 98% efficient
- NEMA 5-15P input plug and 12 NEMA 5-15R outlets

Package Includes

- AVR750UTAA UPS System
- USB cable
- Instruction manual

Description

Tripp Lite's AVR750UTAA Ultra-Compact Line Interactive UPS offers complete power protection for desktop PCs, network workstations and a wide variety of professional and consumer electronic devices. Uninterruptible Power Supply / UPS circuits switch to battery backup mode within milliseconds to keep connected equipment running without interruption or data loss during power failures. Automatic Voltage Regulation / AVR power conditioning maintains smooth, continuous operation of connected equipment during brownouts and overvoltages. Surge-only outlets offer convenient protection for printers and other desktop accessories not requiring battery support. AC and dataline surge suppression prevents connected equipment damage. USB communications port supports built-in power management and auto-shutdown features of Windows and Mac OS X or full featured monitoring and data-saving auto-shutdown options using Tripp Lite's free PowerAlert monitoring software.

Features

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- AVR750UTAA ultra-compact 120V line interactive UPS offers complete AC power protection from blackouts, brownouts and transient surges
- 750VA / 450 watt UPS output capacity
- Uninterruptible Power Supply / UPS operation maintains battery-derived AC output during blackouts to prevent data loss and system downtime for connected equipment
- Built-in USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from tripplite.eaton.com/products/power-alert
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Automatic Voltage Regulation / AVR corrects extended brownouts and overvoltages from 83 to 147V, without using battery power
- 3 minutes runtime at 100% load (450 watts), 8.6 minutes runtime at 50% load (225 watts)
- 44 minutes runtime for a desktop computer system consuming 80 watts continuous
- 12 built-in NEMA 5-15R outlets, two with extra wide spacing to accommodate transformer plugs
- 6 UPS battery backup outlets, plus 6 additional surge-only outlets
- Right angle NEMA 5-15P input connection with 6ft / 1.8m line cord
- Network grade AC surge protection is available from all outlets

- Built-in data line surge suppression protects a single dialup or DSL line
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment, ideal for unattended kiosk applications
- 98% line mode efficiency rating uses less energy and BTU emissions
- Built-in grounding lug
- Hot swappable user battery replacement
- Space saving, ultra-compact housing with support for wall-mount, desktop or floor placement

Specifications

OVERVIEW	
UPC Code	037332184108
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P; Right-Angled
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
OUTPUT	
Output Capacity (VA)	750
Output Capacity (kVA)	0.75
Output Capacity (Watts)	450
Output Capacity (kW)	0.45
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	120V (+8%, -21%)
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	6 UPS outlets, 6 surge-only outlets
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave

Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(12) 5-15R
Individually Controllable Load Banks	No
BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	3 min. (450W)
Runtime Half Load (min.)	8.6 min. (225W)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	15.8 hours (10% to 90%)
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	RBC51
Battery Replacement Description	Hot-swappable, user replaceable battery
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
Overvoltage Correction	Input voltages between 129 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 83 and 104 are boosted by 14%
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination switch controls on/off power status and self-test operation
Audible Alarm	Audible alarm indicates power-failure and overload status
LED Indicators	2 LEDs indicate power status and overload/check battery status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	420
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 2 out)
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Desktop
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop; Wallmount
Primary UPS Depth (mm)	178
Primary UPS Height (mm)	102

Primary UPS Width (mm)	305
Shipping Dimensions (hwd / in.)	5.50 x 14.50 x 9.75
Shipping Dimensions (hwd / cm)	13.97 x 36.83 x 24.76
Shipping Weight (lbs.)	16.45
Shipping Weight (kg)	7.46
UPS Housing Material	ABS
UPS Power Module Dimensions (hwd, cm)	10.16 x 30.48 x 17.78
UPS Power Module Dimensions (hwd, in.)	4 x 12 x 7
UPS Power Module Weight (kg)	6.94
UPS Power Module Weight (lbs.)	15.3
Unit Weight (lbs.)	15.0000
Unit Weight (kg)	6.80
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	27
AC Mode Efficiency Rating (100% Load)	98%
COMMUNICATIONS	
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at https://tripplite.eaton.com/products/power-alert
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management not supported
Communications Interface	USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	1-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	147
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported



Powering Business Worldwide



High Availability UPS Features	Hot swappable batteries; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
Grounding Details	Included
APPLICATIONS	
UPS Applications	Home/Office Desktop; Audio/Video; Retail/Point of Sale; Hospitality
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class B (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.