

USB-C to VGA Adapter with PD Charging, White

MODEL NUMBER: U444-06N-V-C



Adds VGA and USB-C PD charging ports to the USB-C port on your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC.

Description

The U444-06N-V-C USB 3.2 Gen 1 USB-C to VGA Adapter expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C port. It's ideal for transmitting 1080p video to a large display and powering and charging a PD Charging-compliant mobile device—all at the same time. With a source device that also supports USB DisplayPort Alternate Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

The plug-and-play U444-06N-V-C requires no software, drivers or external power. Connect the reversible USB-C plug to your source device's USB-C port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

To send HD video to a VGA television, projector or monitor, connect the VGA port to the display using a VGA cable (sold separately). The VGA port supports HD video resolutions up to 1920 x 1080 (1080p) at 60 Hz.

The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook or Chromebook) the U444-06N-V-C is connected to. Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W).

Features

Turn Your Device's USB-C Port into a Multiport Workstation Ideal for transmitting video to a large display and powering and charging a PD Charging-compliant mobile device simultaneously Plug-and-play operation with no software, drivers or external power required Smaller than a credit card for easy carrying in a pocket, purse or laptop bag

Transmit Crystal-Clear 1920x1080 (1080p) Video to VGA Display Compatible with USB-C source devices that support USB DisplayPort Alternate Mode Supports HD video resolutions up to 1920 x 1080 (1080p) @ 60 Hz Extends video from your primary display to another Duplicates the same video on 2 displays Converts a secondary display to your primary display

Charge a Connected Device USB-C PD port connects to wall charger to power and charge the connected PD Charging-compliant USB-C device Supports power input up to 20V 3A (60W) Note: USB-C PD port does not support Quick Charge (QC).

Built-In Cable with Reversible USB-C Connector Fumble-free reversible USB-C plug connects in either direction for quick connection every time

Highlights

- Supports USB DisplayPort Alternate Mode for transmitting video
- Supports HD video resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- USB-C PD charging port supports power input up to 20V 3A (60W)
- Reversible USB-C plug connects in either direction
- Plug-and-play operation with no software or drivers required

System Requirements

- Source device with USB-C port that supports USB DisplayPort Alternate Mode
- Display device with VGA input (VGA port)

Package Includes

- U444-06N-V-C USB 3.2 Gen 1 USB-C to VGA Adapter
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332193704
Technology	VGA/SVGA
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	HD15 (FEMALE)
Number of Monitors Supported	1
Video Ports	HD15 (FEMALE)
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p)
Max Supported Video Resolution	VGA: 1920 x 1200 (1080p) @ 60Hz
Extended Mode	Yes
Extended Mode Details	Extend the desktop of the host computer to a VGA display at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
Mirror Mode	Yes
Mirror Mode Details	Mirror the video output of the host computer on a VGA display at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
HDR Support	No
3D Video Supported	No
EDID Support	No
DisplayPort Alt Mode	Yes
INPUT	
Built-In Cable Length (ft.)	0.36
Built-In Cable Length (m)	0.11
Built-In Cable Length (in.)	4.33
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	



Powering Business Worldwide



Power Consumption (Watts)	0.60
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	USB C (FEMALE)
Connector Plating	Nickel
CHARGING	
Number of Charging Ports	1
Total Charging Watts	60
Charging Port Type	USB C (FEMALE)
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports Details	(x1) USB-C Port provides PD 2.0 charging up to 20V/3A (60W) to the host device
Charging Ports / Amps	3A
PHYSICAL	
Color	White
Material of Construction	PVC, ABS
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.9mm
Wire Gauge (AWG)	34 / 28
Shipping Dimensions (hwd / in.)	0.79 x 4.72 x 3.94
Shipping Dimensions (hwd / cm)	2.01 x 11.99 x 10.01
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
Unit Dimensions (hwd / in.)	0.551 x 2.323 x 1.575
Unit Dimensions (hwd / cm)	1.4 x 5.9 x 4.0
Unit Packaging Type	Box
Unit Weight (lbs.)	0.07
Unit Weight (kg)	0.03



Powering Business Worldwide



ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	2.1 BTU/Hr
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C)
FEATURES & SPECIFICATIONS	
USB Hub Ports	No
Number of USB Hub Ports	0
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Multi-Resolution Support	Yes
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Displayport Specification	1.2
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Certifications	EN 55024; EN 55032
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.