



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: B064-016-04-IP

16-Port, 5-User NetDirector Cat5 IP KVM Switch

Highlights

- Supports up to 5 simultaneous users: One Local, Four Remote
- Features two, 10/100/1000 RJ45 Network connections for redundant or dual-IP operation
- Panel array mode
- Multi-Platform support: Windows, Linux, UNIX, Novell, Mac and DOS
- On-Screen keyboard; choose from multiple keyboard languages
- Windows based log server
- Remote authentication: RADIUS, LDAP, LDAPS and active directory
- Expand the number of connected computers/servers by cascading a second level of B007-008 KVM switches. (Up to 128 computers/servers can be connected when a B007-008 is cascaded from each of the 16 ports)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 3 Year limited warranty



Description

Tripp Lite's 16-port NetDirector® IP KVM Switch is the optimal solution for remotely controlling multiple computers (combination of PS/2 and USB) by up to 4 independent, simultaneous users. Up to 5 users (1 Local and 4 Remote) can simultaneously access the KVM switch. A single unit occupies a mere 1U of rack space, yet can control up to 16 computers, and a maximum of 128 computers when a second level of B007-008 KVM switches are cascaded. A full-screen graphical OSD with multi-level authentication (Super Administrator, Administrator and User) allows you to quickly and efficiently manage your installation, while the provided Windows-based log server tracks all of the events that take place on the installation. Accessing the connected computers is a breeze; view multiple computers at the same time using panel array mode, automatically sync USB mice, access the on-screen keyboard feature in numerous language formats. Other features include remote authentication support via RADIUS, LDAP, LDAPS and Active Directory, dial-in modem access and non-browser access using Windows and Java applications.

For Government purchasers, B064-016-04-IP is Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

System Requirements

- Remote Console Computers (Web browser) - To access the KVM switch via browser, your computer needs to be running Sun's Java Runtime Environment (JRE) v.6, Update 3 or higher, and your browser must support 128-bit SSL encryption.
- Browsers - The NetDirector Cat5 IP KVM switch supports the following browsers; Internet Explorer 6 and higher, Firefox 1.5 and higher, Mozilla 1.7 and higher, Safari 2.0 and higher, Opera 9.0 and higher, and Netscape 8.1 and higher.
- Remote Console Computers (non-Browser Windows or Java Client) - To access the KVM switch using the non-browser based Windows client, your computer/server must be running Windows, and DirectX 7.0 or higher must be installed. To access the non-browser based Java client, your computer must be running Sun's Java Runtime Environment (JRE) v.6, Update 3 or higher.
- Connected Computers/Servers - Computers/servers being connected to the KVM switch must have a VGA port and USB or PS/2 Keyboard and Mouse ports.
- Operating Systems - The NetDirector Cat5 IP KVM switch supports connected computers/servers with the following operating systems: Windows 2000 and higher, Linux Red Hat 7.1 and higher, Linux Fedora Core 2 and higher, Linux SuSE 9.0 and higher, Linux Mandriva 9.0 and higher, UNIX AIX 4.3 and higher, UNIX FreeBSD 4.2 and higher, UNIX Sun Solaris 8 and higher, Novell Netware 5.0 and higher, Mac OS 9 and higher, and DOS 6.2 and higher.

Package Includes

- NetDirector Cat5 IP KVM Switch
- Power Cord
- CD with Owner's Manual, IP Installer, Non-Browser Java Client, Non-Browser Windows Client and Windows-Based Log Server
- RJ45 to DB9 Adapter for Dial-In Modem functionality
- Console Cable Kit (includes both USB and PS/2 connectors)
- Rackmount hardware

Features

- Up to 5 users (1 Local, 4 Remote) can simultaneously access the connected computers/servers
- Features 2 RJ45 10/100/1000Mbps network ports for redundant or dual-IP operation
- Directly connect up to 16 computers/servers, or up to 128 by cascading a second level of B007-008 KVM switches
- Multi-level authentication; Super Administrator, Administrator and User
- Advanced security features include password protection and advanced encryption technologies - 1024 bit RSA; 56 bit DES; 256 bit AES and 128 bit SSL
- RJ45 connectors allow for a more efficient installation using Cat5 cables
- Access the connected computers/servers via local console, browser based Java application or non-browser based Windows and Java applications
- View multiple ports at the same time using the panel array mode feature
- Connect up to 3 additional USB1.1 devices using the USB ports on the front of the KVM switch
- Remote authentication support; RADIUS, LDAP, LDAPS and Active Directory
- Windows based Log Server records events that take place on the installation
- Dial-in modem support
- Graphical OSD and toolbars provide convenient, user friendly operation
- Full-screen or sizable remote desktop window; in full-screen mode the remote desktop display scales to user's monitor display size
- Supports up to 1600x1200 @ 60Hz resolutions
- Multi Language support: English, German, Traditional Chinese, Simplified Chinese and Japanese
- Features an on-screen keyboard with numerous language formats
- Automatically syncs USB mice
- Supports 10Base-T, 100Base-T, 1000Base-T, Auto-Sense, TCP/IP, HTTP, DNS, DHCP, UDP, ARP and Ping
- Flash upgradeable firmware over the network
- Message Board: Communicate instantly with other users
- UL/cUL
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 3 Year limited warranty

Specifications

| OVERVIEW | |
|-----------------------|----------------------------|
| # Of Users | 4 |
| Console | No |
| Port Control | Push Buttons, Hotkeys, OSD |
| Max CPU | 128 |
| PC/Server | VGA, USB or PS/2 |
| Cat5 KVM Switch | Yes |
| IP Remote Access | YES, BUILT IN |
| INPUT | |
| Input connection type | IEC-320-C14 |
| Plug Type | IEC-320-C13 |
| PHYSICAL | |

| | |
|-----------------------|------------------|
| Unit weight (lbs) | 12.2 |
| Color | Black |
| Style | 1U Rackmount |
| LCD Monitor (in.) | Not Applicable |
| ENVIRONMENTAL | |
| BTUs | 135.2 to 136.6 |
| CONNECTIONS | |
| Ports | 16 |
| CERTIFICATIONS | |
| Approvals | CE, FCC and RoHS |

Related Items

Required Products

| Product Type | Related Model | Description | Qty. |
|----------------------------|------------------------------|---|------|
| KVM Switches & Accessories | B054-001-PS2 | KVM Switch Accessories - PS/2 Server Interface Module for NetDirector Matrix KVM Switches | 1 |
| KVM Switches & Accessories | B054-001-USB | KVM Switch Accessories - USB Server Interface Module for NetDirector Matrix KVM Switches | 1 |

Optional Products

| Product Type | Related Model | Description | Qty. |
|-----------------------|--------------------------------|---|------|
| Patch Cables | N001-003-BK | 3-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black | 1 |
| Patch Cables | N001-005-BK | 5-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black | 1 |
| Patch Cables | N001-007-BK | 7-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black | 1 |
| Patch Cables | N001-010-BK | 10-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black | 1 |
| Patch Cables | N001-014-BK | 14-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black | 1 |
| Patch Cables | N001-025-BK | 25-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Black | 1 |
| Rackmount Consoles | B021-000-17 | Rackmount Console - 1U Rackmount Console with 17" LCD | 1 |
| Rackmount Consoles | B021-000-19 | Rackmount Console - 1U Rackmount Console with 19" LCD | 1 |
| Rackmount Consoles | B021-000-19-SH | Rackmount Console - 1U Short-Depth Rackmount Console with 19" LCD | 1 |
| USB Cables & Adapters | U022-006 | 6-ft. USB2.0 A/B Gold Device Cable (A Male to B Male) | 1 |
| USB Cables & Adapters | U022-010 | 10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male) | 1 |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4204.

