



HDMI over Cat5/6 Active Extender Kit, Wall Plate Transmitter/Receiver for Video/Audio, Up to 150 ft. (45 m), TAA

MODEL NUMBER: B126-1A1-WP







Transmitter and receiver work in tandem to extend an HDMI signal via Cat5e/6 cable to a projector, monitor or television. Ideal for digital signs, schools and trade show presentations.

Description

The B126-1A1-WP HDMI over Cat5/Cat6 Active Extender Kit includes a transmitter unit and a receiver unit that work in tandem to extend an HDMI signal to a projector, monitor or television. The kit is ideal for digital signs, trade shows, presentations, classrooms, churches, retail settings and other applications where the video source is located farther than conventional cables allow or that require multiple displays connected to one source.

HDMI cable (see Tripp Lite's P568-Series) connects a monitor to the receiver and the video source to the transmitter. Cat5e/6 cable (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series) connects the two units. No 110 punchdown connection is required.

The B126-1A1-WP can extend a 1080i (60 Hz) signal up to 200-ft. (60.96 m), a 1080p (60 Hz) signal up to 150-ft. (45.72 m) and a 3D signal up to 125-ft. (38.1 m). You can also connect up to three B126-110 remote repeaters in the chain (using Cat5e/6 cable) for a total of five HDMI displays and full signal extension of 700-ft. (213.36 m) (1080i), 500-ft. (152.4 m) (1080p) or 400-ft. (121.92 m) (3D).

In addition to crystal-clear video, the B126-1A1-WP delivers full, rich stereo and 7.1-channel surround sound (multi-channel or PCM) audio. Built-in equalization control lets you fine-tune the image quality at each remote display. Supports 24-bit True Color (8 bits per channel) and HDCP compatibility. Easy to set up with no software or drivers to install. Mounts to a wall using the included hardware.

Features

Extends High-Definition Signals

Extends a 1080i (60 Hz) signal up to 200-ft. (60.96 m), a 1080p (60 Hz) signal up to 150-ft. (45.72 m) and a 3D signal up to 125-ft. (38.1 m)

Highlights

- Supports high-definition video resolutions up to 1080p (60 Hz)
- Supports stereo and 7.1channel surround sound audio
- Works with all operating systems and HDMI video sources
- Plug and play—no software or drivers to install
- Built-in equalization control lets you fine-tune image quality

System Requirements

Package Includes

- Transmitter unit
- Receiver unit
- Screwdriver for adjusting equalization
- (2) External Power Supplies with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Mounting hardware
- Owner's Manual





- Connect up to 3 B126-110 remote repeaters to the chain for maximum signal range of 700-ft. (213.36 m) (1080i), 500-ft. (152.4 m) (1080p) and 400-ft. (121.92 m) (3D)
- Transmitter and receiver connect with one Cat5e/6 cable (for best results, use 24 AWG solid-wire Cat5e/6 cable, such as Tripp Lite's N202-Series)
- No 110 punchdown connection required

Supports the Latest Video and Audio Resolutions

- Works with all operating systems and HDMI video sources
- Supports HD resolutions up to 1080p (60 Hz)
- Supports stereo and 7.1-channel surround sound (multi-channel or PCM) audio
- Supports 24-bit True Color (8 bits per channel) and HDCP
- Built-in equalization control lets you adjust the image on the local monitor

Easy to Set Up and Use

- · Plug-and-play engineering—no software or drivers to download and install
- Units connect quickly to source and display with HDMI cable, such as Tripp Lite's P568-Series
- LEDs indicate at a glance when the unit is receiving power and a signal from the previous link in the chain
- Included mounting hardware lets you install the unit on a wall

TAA-Compliant

• Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW		
-		
UPC Code	037332168078	
Product Type	Extender Kit	
Technology	HDMI; Cat5/5e; Cat6	
VIDEO		
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)	
Recommended Cabling	Cat5/Cat6 Cables	
Max Supported Color Depth	24-bit True Color	
HDR Support	No	
3D Video Supported	Yes	
Maximum Signal Range (ft)	150	
Maximum Signal Range (m)	46	
ALIDIO		
AUDIO		
Audio Specification	7.1 Channel Surround Sound (Multi-Channel or PCM)	





INPUT		
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A	
AC Power Adapter Output Specs (V / A)	5V/2A	
AC Power Adapter Cord Length (ft.)	4.5	
AC Power Adapter Cord Length (m)	1.37	
Bus Powered	No	
POWER		
Power Source Type	AC Adapter	
AC Plug Type	NEMA 1-15P	
Power Source	Transmitter and Receiver (Included)	
Power Over Cable (PoC) Support	No	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A	
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve	
CONNECTIONS		
Side A - Connector 1	HDMI (FEMALE); RJ45 (FEMALE)	
Side B - Connector 1	HDMI (FEMALE); RJ45 (FEMALE)	
Connector Plating	Nickel	
USER INTERFACE, ALERTS & CON	TROLS	
LED Indicators	Green (Power), Orange (Activity), Blue (Audio)	
PHYSICAL		
Color	White	
Material of Construction	Steel	
Number of Displays	1	
Rackmountable	No	
Receiver Unit Dimensions (hwd / cm.)	2.6 x 9.2 x 6.4	
Receiver Unit Dimensions (hwd / in.)	1 x 3.6 x 2.5	
Receiver Unit Weight (kg)	0.09	
Receiver Unit Weight (lbs.)	0.2	
Shipping Dimensions (hwd / in.)	0.25 x 5.00 x 10.60	
Shipping Dimensions (hwd / cm)	0.64 x 12.70 x 26.92	
Shipping Weight (lbs.)	0.30	
Shipping Weight (kg)	0.14	





Transmitter Unit Dimensions (hwd / cm.)	2.6 x 9.2 x 6.4	
Transmitter Unit Dimensions (hwd / in.)	1 x 3.6 x 2.5	
Transmitter Unit Weight (kg)	0.09	
Transmitter Unit Weight (lbs.)	0.2	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
Unit Packaging Type	Вох	
Housing	Metal	
ENVIRONMENTAL		
Operating Temperature Range	14 to 167 F (-10 to 75 C)	
Storage Temperature Range	-4 to 176 F (-20 to 80 C)	
Relative Humidity	0% to 85%, Non-Condensing	
COMMUNICATIONS		
Signal Range (ft.)	200	
Signal Range (m)	61	
EDID Compatible	No	
IR Remote Extension Support	No	
RS-232 Serial Extension Support	No	
Consumer Electronics Control (CEC) Supported	No	
USB Extension Support	No	
FEATURES & SPECIFICATIONS		
10/100 Ethernet Extension Support	No	
Built-In Equalizer	No	
HDCP Specification	1.4	
Driver Required	No	
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables	
STANDARDS & COMPLIANCE		
External Power Supply Certifications	FCC; RoHS; UL; cUL	
WARRANTY & SUPPORT		
	1 year limited warranty	
Product Warranty Period (Worldwide)	1-year limited warranty	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.