

VGA over Cat5 Extender, 4-Port Transmitter

MODEL NUMBER: B132-004-1



Description

Tripp Lite's B132-004-1 allows you to split a single VGA signal into 5 (1 local, 4 remote). Increase the number of displays to up to 25 (1 local, 24 remote) by daisy-chaining up to six B132-004-1 units together. Along with a B132-100-1 or B132-100-WP-1 remote receiver unit, you can extend a 1920 x 1440 (60Hz) signal up to 500 ft., or a 1024 x 768 (60Hz) signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6). For optimal video image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K. Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted. Up to three B132-004-1 units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19 in. rackmount bracket. Ideal for digital signage situations, such as retail, schools, churches, etc.

Features

- Splits a single VGA signal into 5 (1 local, 4 remote)
- Increase the number of displays to up to 25 (1 local, 24 remote) by daisy-chaining up to six B132-004-1 units together
- A B132-100-1 or B132-100-WP-1 remote receiver unit is required for each connected monitor
- Extends a 1920 x 1440 (60Hz) signal up to 500 ft., or a 1024 x 768 (60Hz) signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Includes mounting hardware that allows unit to be wallmounted, rackmounted or pole mounted
- Up to three B132-004-1 units can be mounted in 1U of rack space using a Tripp Lite B132-004-RB Extender/Splitter 19 in. rackmount bracket
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Splits a single VGA signal into 5 (1 local, 4 remote)
- Extends a 1920 x 1440 (60Hz) signal up to 500 ft., or a 1024 x 768 (60Hz) signal up to 1,000 ft., when using 24Awg, Solid Wire Cat5e/6 cable, such as Tripp Lite's N022-01K-GY (Cat5) and N222-01K-GY (Cat6)
- For optimal image quality between 500 and 1,000 ft., use Zero-Skew cable, such as Tripp Lite P524-01K
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 4 Port Extender/Splitter local (Transmitter) unit
- 1 ft. VGA daisychain cable
- Mounting hardware
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's Manual

Specifications

OVERVIEW



Powering Business Worldwide



| | |
|-------------------------------------|--|
| UPC Code | 037332160140 |
| Product Type | Cat5/Cat6 Transmitter |
| Technology | VGA/SVGA |
| POWER | |
| AC Adapter | Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A |
| CONNECTIONS | |
| Number of Ports | 4 |
| Side A - Connector 1 | HD15 (FEMALE) |
| Side B - Connector 1 | (4) RJ45 (FEMALE) |
| Side B - Connector 2 | HD15 (FEMALE) |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / in.) | 2.20 x 8.40 x 6.50 |
| Shipping Dimensions (hwd / cm) | 5.59 x 21.34 x 16.51 |
| Shipping Weight (lbs.) | 1.80 |
| Shipping Weight (kg) | 0.82 |
| Unit Dimensions (hwd / in.) | 1.200 x 5.300 x 3.900 |
| Unit Dimensions (hwd / cm) | 3.05 x 13.46 x 9.91 |
| Unit Weight (lbs.) | 0.85 |
| Unit Weight (kg) | 0.39 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.