



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: BP192V18-4U

BP192V18-4U - External Battery Pack for UPS System

Highlights

- Extends runtime of compatible Tripp Lite UPS Systems with 192VDC external battery connection
- Provides daisy-chain capability
- Simple installation; 4U rackmount, tower or stack adaptable
- 2-year warranty



Description

Tripp Lite's BP192V18-4U rack/tower external battery pack offers extended battery runtime when used in conjunction with compatible Tripp Lite UPS systems. Multi-use form factor supports configuration in rackmount or stacking applications using only 4 rack spaces (4U). Upright tower configuration supported with optional 2-9USTAND accessory. Includes heavy-gauge cabling with high-current DC connectors for simple installation. Additional output connector allows multiple BP192V18-4U battery packs to be daisy-chained to the UPS for even longer extended run operation.

COMPATIBLE UPS SYSTEMS - SU16000RT4U, SU16000RT4UHW, and other Tripp Lite UPS systems that specify the use of this battery pack.

Applications

- Ideal means of lengthening the battery runtime provided by compatible Tripp Lite UPS systems. Additional battery packs may be ordered at time of original UPS purchase or sourced at a later date to extend runtime performance if site power conditions deteriorate and longer battery runtime is desired.

Package Includes

- BP192V18-4U external battery pack
- Mounting Hardware
- Instruction manual with warranty information

Features

- Offers extended-run UPS operation when used in conjunction with compatible Tripp Lite UPS systems
- Supports stacking or rackmount installation using only 4 rack spaces (4U)
- Supports upright tower installation with optional 2-9USTAND accessory (holds 2 battery packs in tower configuration)
- Set of input/output connectors allows multiple BP192V18-4U battery packs to be daisy-chained to the UPS for even longer extended run operation
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- 2-year warranty

Specifications

OUTPUT

Overload protection	120A DC output fuse system
INPUT	
UPS Input cord length (ft.)	16 in./ .41m, 4 AWG, 2 conductor
BATTERY	
Expandable battery runtime	Includes a second input/output connector to daisy-chain multiple BP192V18-4U battery packs
DC system voltage	192 VDC
Connects to UPS via	Detachable cable with UPS specific DC connector (40.6 cm length, 4 gauge cable)
Typical battery lifespan	4-6 years typical (North America)
PHYSICAL	
Shipping weight (lbs)	288
Shipping weight (kg)	129.6
Unit Dimensions (HWD/in)	7 x 17.5 x 27.8
Unit Dimensions (HWD/cm)	18 x 44.5 x 70.6
Shipping Dimensions (HWD/in)	13 x 23.25 x 34.25
Shipping Dimensions (HWD/cm)	33 x 59.1 x 87
Unit weight (lbs)	239
Unit weight (kg)	107.55
Material of construction	Black steel cabinet
Form factors supported	4U rack/tower
WARRANTY	
Standard warranty period	2-year product warranty
Optional Coverage	3 year, 5 year, next day, on-site warranty coverage available

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Tower Stands	2-9USTAND	Enables Tower Placement of Rackmount UPS Systems	-
Extended Warranties	WEXT3-BP192V18	3-Year Extended Warranty - For BP192V18-4U	-
Extended Warranties	WEXT5-BP192V18	5-Year Extended Warranty - For BP192V18-4U	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3654.