

# External 72V 2U Rack-Mount Battery Pack for Select UPS Systems (BP72V15-2U)

MODEL NUMBER: BP72V15-2U



### Highlights

- Extends the runtime of compatible 72V UPS Systems
- Supports 2U rack-mount installation, 4-post installation accessories included
- Options for 2-post rack-mount and wall-mount installation available

### Package Includes

- BP72V15-2U external battery pack with attached DC cabling
- 4 post compatible rack mounting hardware
- Owner's manual

### Description

BP72V15-2U rack-mount external battery pack offers extended battery runtime when used in conjunction with expandable 72V rack-mount and tower UPS systems. Includes heavy-gauge cabling with high-current DC connector for safe, simple installation. Included mounting accessories support 2U rack-mount installation in 4-post racks. Options for 2-post center-mounting and wall-mount installation available. Compatible with SU3000RTXL2U, SU3000RTXL3U, SU3000RTXLCD3U, SU3000RTXR3U, SU3000RTXR3UHW, SU3000XL, SUIINT3000RTXL2U, SUIINT3000RTXL3U, SU3000LCD2UHV, SUIINT3000LCD2U and other UPS systems that specify the use of this battery pack.

### Features

- Offers extended-run UPS operation when used in conjunction with compatible 72V DC UPS systems
- Includes heavy-gauge cabling with high-current DC connectors for simple installation
- Included mounting brackets support rack-mount installation in 4-post racks using only 2 rack spaces (2U)
- 2POSTRMKITWM option supports balanced two-point center-mounting in 2-post equipment racks
- 2POSTRMKITWM option also enables wallmount installation
- NOTE: LIMIT OF 1 BP72V15-2U PER UPS, SEE BP72V18-2US or BP72V28RT-3U FOR MULTI-PACK COMPATIBILITY

## Specifications

OVERVIEW	
UPC Code	037332124333
INPUT	
Input Phase	Single-Phase
BATTERY	



Powering Business Worldwide



DC System Voltage (VDC)	72
UPS Connection	Attached cable with black 3-point DC connector
Typical Battery Lifespan	4-6 years typical (North America)
<b>PHYSICAL</b>	
Material of Construction	Steel
Rack Height	2U
External Battery Pack Form Factor	Rack
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="https://tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> ); Wallmount ( <a href="https://tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> )
Minimum Required Rack Depth (cm)	60.96
Minimum Required Rack Depth (inches)	24
Shipping Dimensions (hwd / in.)	10.00 x 26.00 x 28.00
Shipping Dimensions (hwd / cm)	25.40 x 66.04 x 71.12
Shipping Weight (lbs.)	120.00
Shipping Weight (kg)	54.43
Unit Dimensions (hwd / in.)	3.500 x 17.500 x 20.750
Unit Dimensions (hwd / cm)	8.9 x 52.7 x 52.7
Unit Weight (lbs.)	72.4
Unit Weight (kg)	32.84
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; CE (Europe)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (U.S. & Canada)	2-year limited warranty
Product Warranty Period (International)	1-year limited warranty
Product Warranty Period (Mexico)	1-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.