

Waber-by-Tripp Lite Surge Suppressor with heavy-duty metal housing

MODEL NUMBER: DG115-SR



Highlights

- 6 outlets/6 ft. cord
- 600 joule rating
- Audible surge indication
- · Remote switch included

Package Includes

- DG115-SR Power Strip
- Warranty information
- Instruction manual

Description

The Waber-by-Tripp Lite DG115-SR Power Strip offers a convenient method of power distribution and surge suppression in workbench, wallmount or floor mount applications. Unique design includes remote power switch at the end of a 6 foot cord allows remote power control of connected equipment. Includes 6 NEMA 5-15R output receptacles, 6 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built in surge suppression rated at 600 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15 amp resettable circuit breaker and attractive gray color scheme. Lifetime warranty.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle) FORMAT - Corded power distribution strip with remote power switch on a 6 ft. cord SUPPRESSION - 600 joules AC suppression

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Mountable remote power switch at the end of a 6 foot cord allows remote power control of connected equipment.
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs support permanent installation on a wide variety of surfaces
- UL1449 (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6 foot AC line cord
- Lifetime warranty

Specifications

OVERVIEW



UPC Code	037332115621	
INPUT		
Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
	120	
Voltage Compatibility (VAC)		
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)		
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Circuit Breaker (amps)	15	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Lighted two position mountable remote power switch at the end of a dedicated 6 ft. cord controls power to all outlets	
Diagnostic LED Details	Protection present (green)	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	600	
AC Suppression Response Time	<1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression	
UL1449 Let Through Rating	400V - UL Verified	
EMI / RFI Filtering	Up to 20 dB	
Immunity	Conforms to IEE 587 / ANSI C62.41	
Automatic Shut-Off	No	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Color	Light Gray	
Material of Construction	Metal	



Power Cord Color	Light Gray	
Housing Color	Light Gray	
Mounting Holes or Slots	Yes	
Receptacle Color	Light gray	
Shipping Dimensions (hwd / in.)	2.16 x 15.00 x 6.00	
Shipping Dimensions (hwd / cm)	5.50 x 38.10 x 15.24	
Shipping Weight (lbs.)	2.12	
Shipping Weight (kg)	0.96	
Unit Dimensions (hwd / in.)	1.500 x 12.594 x 2.500	
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.