



Protect It! Surge Protector with 6 Swivel Outlets, Direct Plug-In, 1500 Joules, Coax/Tel/Modem Protection

MODEL NUMBER: HTSWIVEL6











Highlights

- 6 rotatable outlets
- · Direct plug-in design
- 1500 joule rating
- 1 line tel/modem and 1-line gold coax (2.2GHz bandwidth) protection

Package Includes

- HTSWIVEL6 Surge Suppressor
- Instruction manual with warranty information
- 6 ft. gold coaxial cable
- 6 ft. phone cord

Description

Tripp Lite's HTSWIVEL6 Home/Business Theater Surge Suppressor provides high-performance protection--1500 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 6 outlets, 1-line coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only). Includes two diagnostic LEDs, 6 ft. gold coaxial cable and 6 ft. phone cord.

Features

- 6 rotatable outlets allow for easier plug connection and removal
- 1500 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 1 set of surge-protected Type F gold coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line (2.2GHz bandwidth)
- 1 set of surge-protected tel/modem connectors (with included 6 ft. phone cord) safeguard personal video recorders (PVRs) on a single dial-up line
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by pluggin into any wall outlet
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
 equipment damage and indicating replacement is required

Specifications





OVERVIEW		
UPC Code	037332138279	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Length Details	Direct Plug-In	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	60000	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	0	
Right-Angle Plug	No	
Input Cord Length (m)	0.00	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Outlet Orientation	Rotatable	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	1500	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression	
UL1449 Let Through Rating	400, 500, 500	
EMI / RFI Filtering	Up to 20 dB	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection Details	1 line	





Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
PHYSICAL	
Color	Black
Material of Construction	Plastic
Housing Color	Black
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	29mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	7.60 x 2.40 x 5.80
Shipping Dimensions (hwd / cm)	19.30 x 6.10 x 14.73
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	6.250 x 4.000 x 2.250
Unit Dimensions (hwd / cm)	15.88 x 10.16 x 5.72
Unit Weight (lbs.)	0.6
Unit Weight (kg)	0.27
FEATURES & SPECIFICATIONS	
Rotatable Outlets	Yes
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.