



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: HTSWIVEL6

**6 Rotatable Outlets, Direct plug-in, 1500 Joules, 1-line gold coaxial 1-line tel/modem protection - Surge Suppressor**



### Highlights

- 6 rotatable outlets
- Direct plug-in design
- 1500 joule rating
- 1 line tel/modem and 1-line gold coax (2.2GHz bandwidth) protection
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

### Description

Tripp Lite's HTSWIVEL6 Home/Business Theater Surge Suppressor provides high-performance protection--1500 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 6 outlets, 1-line coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$50,000 [Ultimate Lifetime Insurance](#) coverage (USA and Canada only). Includes two diagnostic LEDs, 6 ft. gold coaxial cable and 6 ft. phone cord.

#### Applications

- Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more

#### Package Includes

- HTSWIVEL6 Surge Suppressor
- Instruction manual with warranty information
- 6 ft. gold coaxial cable
- 6 ft. phone cord

### Features

- 6 rotatable outlets allow for easier plug connection and removal
- 1500 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 1 set of surge-protected Type F gold coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line (2.2GHz bandwidth)
- 1 set of surge-protected tel/modem connectors (with included 6 ft. phone cord) safeguard personal video recorders (PVRs) on a single dial-up line
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by plugging into any wall outlet
- \$50,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only)

### Specifications

#### OVERVIEW

Intended Application	Audio/Video
<b>OUTPUT</b>	
Frequency compatibility	60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
Outlet orientation	Rotatable
<b>INPUT</b>	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (m)	Direct plug-in
Input cord length details	Direct Plug-In
Voltage compatibility (VAC)	120
Maximum Surge Amps	60000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	1500
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping voltage (RMS)	400
UL1449 let through rating	400, 500, 500
EMI / RFI filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	1.0
Shipping weight (kg)	0.45
Unit Dimensions (HWD/in)	6.25 x 4 x 2.25
Unit Dimensions (HWD/cm)	15.88 x 10.16 x 5.72

<b>Shipping Dimensions (HWD/in)</b>	8.6 x 5.8 x 2.38
<b>Shipping Dimensions (HWD/cm)</b>	21.84 x 14.73 x 6.05
<b>Unit weight (lbs)</b>	0.6
<b>Unit weight (kg)</b>	0.27
<b>Material of construction</b>	Plastic
<b>Receptacle Color</b>	Black
<b>Style</b>	Direct plug-in
<b>Outlets center to center measurement</b>	29mm
<b>CERTIFICATIONS</b>	
<b>UL1449 3rd Edition (AC Suppression)</b>	UL1449 3rd Edition
<b>cUL / CSA (Canada)</b>	cUL
<b>Approvals</b>	RoHS
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$50,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3618](http://www.tripplite.com/en/products/model.cfm?txtModelID=3618).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.