

Easy Pull Long-Run Display Cable - Type-A Analog PVC Trunk Cable, 35 ft. (10.67 m)

MODEL NUMBER: EZA-035



Highlights

- Versatile trunk cable allows for a variety of connection options
- At a diameter of 7/8 in., it easily pulls through conduit or confined spaces using the included end cap with integrated pull tab
- High quality RGB style VGA cable supports resolutions up to 1600 x 1200, as well as Audio pass through

Package Includes

- Easy Pull Type-A VGA Analog PVC Trunk Cable, 35 ft.

Features

- Eliminates the need to field terminate VGA connectors
- Detachable, screw-on connector with pull tab (7/8 in. diameter) makes it easy to pull through tight spaces, and helps protect the cable from strain, dirt, debris and damage when doing so
- Allows cable to be run according to code - inside conduit, drop ceilings, etc.
- Available in both PVC and Plenum versions
- Comes in 35 ft., 50 ft. and 100 ft. lengths
- Supports Video and Audio pass through depending on end kit used
- Choose from a variety of connector combinations for the perfect fit

Specifications

OVERVIEW	
UPC Code	037332141903
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DIN 14 PIN (FEMALE)
Side B - Connector 1	DIN 14 PIN (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	Black; Green
Cable Jacket Color	Black; Green
Cable Length (ft.)	35
Cable Length (m)	10.67
Cable Length (in.)	420
Shipping Dimensions (hwd / in.)	1.70 x 6.70 x 6.90
Shipping Dimensions (hwd / cm)	4.32 x 17.02 x 17.53
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.