



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: INTERNET550SER

Internet Office UPS System - Affordable full system protection with serial interface

Highlights



- 550VA ultra-compact UPS
- Maintains 120V nominal output during blackouts
- Workstation optimized features include serial port, single line TEL / DSL surge suppression and four surge-only outlets
- 99% line-mode efficiency saves energy and operating costs
- Input: NEMA 5-15P (120V 15A) / Output: 8 NEMA 5-15R (120V)
- 3 year product warranty / \$100,000 **Ultimate Lifetime Insurance** (USA, Puerto Rico & Canada only)

Description

Ultra-compact standby UPS with built-in DB9 serial monitoring port protects PCs, network workstations and other systems reliant upon a simple serial communications interface for UPS monitoring and unattended system shutdown. Maintains AC output during blackouts and brownouts starting at 99V. Includes DB9 monitoring port with cabling, TEL/DSL line surge suppression, surge-only outlets and LED indicators. PowerAlert software available free via download.

Package Includes

- INTERNET550SER standby UPS system
- DB9 serial cable for use with PowerAlert UPS monitoring software
- Instruction manual and warranty information

Features

- INTERNET550SER standby UPS offers protection from blackouts, brownouts and surges on both AC and dialup modem lines
- Provides seamless battery derived AC output during blackouts and severe brownouts so that connected equipment can be shut down without data loss
- Built-in serial port interface provides simple communications for automatic system shutdown if power fails while the system runs unattended
- PowerAlert software available via free download from <http://www.tripplite.com>, serial cable included
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment; ideal for unattended kiosk applications
- 4 battery supported outlets protect computer, monitor and one vital system peripheral, plus 4 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Attractive stealth black UPS color scheme
- Built-in single line phone jacks protects peripherals with a standard dialup phone line connection
- Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation
- 550VA /300 watt power handling ability supports entry-level PC systems for several minutes during power fail conditions
- Ultra-compact housing fits anywhere, wall mountable
- Includes attached 6 ft. AC power cord with space saving right angle plug, on/off power switch
- Compatible with 120V/60 Hz applications in USA, Canada, Mexico and other countries
- 3 year warranty (worldwide), plus \$100,000 **connected equipment insurance** (USA, Puerto Rico, & Canada only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	550
Output Watt Capacity (watts)	300
Nominal Output Voltage(s) Supported	115v; 120v
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	8 5-15R outlet(s)
Surge suppression only outlets	4 UPS outlets, 4 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P; Space saving right angled input plug
Input circuit breaker	10A
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	3.5 min. (300w)
Half load runtime (minutes)	10 min. (150w)
DC system voltage	12V DC
Battery recharge rate (included batteries)	Less than 15 hours from 10% to 90%
LEDS ALARMS & SWITCHES	
LED Indicators	2 LEDs indicate power status and overload/check battery status
Alarms	Audible alarm indicates power-failure and overload status

Switches	Combination switch controls on/off power status and self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	420
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL / DSL protection (1 in / 1 out)
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower; Ultra-compact desktop; Wallmount (using keyhole mounting tabs)
Primary form factor	Desktop
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3.1 x 10.9 x 5.7
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	7.9 x 27.7 x 14.5
Installed whole system dimensions in secondary form factor (height x width x depth / inches)	
UPS dimensions in secondary form factor (height x width x depth / cm)	
UPS / Power Module weight (lbs)	6.5
UPS / Power Module weight (kg)	3
Stepdown transformer dimensions (height x width x depth / inches)	
Stepdown transformer dimensions (height x width x depth / cm)	
Included battery pack dimensions (height x width x depth / inches)	
Included battery pack dimensions (height x width x depth / cm)	
UPS Shipping dimensions (height x width x depth / inches)	4.1 x 8 x 13

UPS Shipping dimensions (height x width x depth / cm)	10.4 x 20.3 x 33
Shipping weight (lbs)	7
Shipping weight (kg)	3.2
UPS housing material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	10.3
Battery mode BTU / hr. (full load)	194.3
COMMUNICATIONS	
Communications interface	DB9 Serial
PowerAlert software	Free download from www.tripplite.com
Communications cable	DB9 interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	99
High voltage transfer to battery power (setpoint)	139
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); Meets FCC Part 68 / Industrie Canada (telecommunications); ROHS (Reduction of Hazardous Substances)
WARRANTY	
Standard warranty period	3 years
Connected equipment insurance (USA, Canada, Puerto Rico)	\$100,000 connected equipment insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Audio Cables	CT120	Instant-Read- AC Outlet Circuit Tester	-
Surge Protectors	DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	-
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	-
Surge Protectors	DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	-
Software	WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	-
Extended Warranties	WEXT5-INTERNET	5-Year Extended Warranty - For Internet Office Models	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3116.