

Internet Office 120V 50/60Hz 300VA 150W Standby UPS, Ultra-Compact Desktop 6 Outlets, Tel/DSL/Ethernet Protection, TAA

MODEL NUMBER: INTERNETOFFICE300



Highlights

- 300VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets
- TAA Compliant

Package Includes

- INTERNETOFFICE300 UPS System
- Phone cable
- Instruction manual

Description

Tripp Lite's INTERNETOFFICE300 UPS System provides complete power protection for your entire computer set-up. 300 VA power capacity maintains your Internet connection allowing you to work online through short blackouts or safely shut down during longer ones. Unique design features 6 outlets (3 UPS & surge + 3 surge-only outlets) and diagnostic LEDs. Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment. A 6-ft. telephone cord is also included. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment.

Features

- 300 VA output power rating (150 watts)
- Up to 11 minutes backup time (single PC; 15-in monitor)
- Battery run time: 10 minutes half load/4 minutes full load
- 6 protected outlets (3 UPS & surge + 3 surge-only outlets); 6-ft. cord
- Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment; 6-ft. telephone cord included
- Complete surge protection and EMI/RFI noise filtering
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- 5 diagnostic LEDs indicate AC present, line fault, on battery, overload and battery low/replace
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

| | |
|---|-------------------------------------|
| UPC Code | 037332096654 |
| UPS Type | Standby |
| INPUT | |
| Input Phase | Single-Phase |
| Rated input current (Maximum Load) | 12A |
| Nominal Input Voltage(s) Supported | 120V AC |
| UPS Input Connection Type | 5-15P |
| UPS Input Cord Length (ft.) | 6 |
| UPS Input Cord Length (m) | 1.8 |
| Recommended Electrical Service | 15A 120V |
| OUTPUT | |
| Output Capacity (VA) | 300 |
| Output Capacity (Watts) | 150 |
| Nominal Voltage Details | 120v nominal output in battery mode |
| Frequency Compatibility | 50 / 60 Hz |
| Frequency Compatibility Details | Automatic frequency selection |
| Output Voltage Regulation (Battery Mode) | +/- 5% |
| UPS Output Receptacles (Surge Suppression Only) | 3 UPS outlets, 3 surge-only outlets |
| Output Circuit Breakers | 15A |
| Hot-Swap PDU options | PDUB15 (2U / 8 5-15R outlets) |
| Output AC Waveform (AC Mode) | Sine wave |
| Output AC Waveform (Battery Mode) | PWM sine wave |
| Nominal Output Voltage(s) Supported | 110V; 115V; 120V |
| Output Receptacles | (6) 5-15R |
| Individually Controllable Load Banks | No |
| BATTERY | |
| Runtime Full Load (min.) | 4 min. (150w) |
| Runtime Half Load (min.) | 10 min. (75w) |
| Expandable Runtime | No |
| DC System Voltage (VDC) | 12 |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Power off / on switch |



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

| | |
|---|--|
| LED Indicators | 5 LEDs indicate complete UPS operational status |
| SURGE / NOISE SUPPRESSION | |
| UPS AC Suppression Joule Rating | 380 |
| UPS AC Suppression Response Time | Instantaneous |
| UPS Dataline Suppression | 1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet |
| EMI / RFI AC Noise Suppression | Yes |
| AC Suppression Joule Rating | 380 |
| AC Suppression Response Time | Instantaneous |
| Dataline Suppression | 1 line TEL / DSL or 10Base T Ethernet protection |
| PHYSICAL | |
| Primary Form Factor | Desktop |
| Installation Form Factors Supported with Included Accessories | Tower; Ultra-compact desktop; Wallmount |
| Primary UPS Depth (mm) | 114 |
| Primary UPS Height (mm) | 66 |
| Primary UPS Width (mm) | 279 |
| Shipping Dimensions (hwd / in.) | 4.10 x 8.00 x 12.90 |
| Shipping Dimensions (hwd / cm) | 10.41 x 20.32 x 32.77 |
| Shipping Weight (lbs.) | 5.30 |
| Shipping Weight (kg) | 2.40 |
| UPS Housing Material | ABS |
| UPS Power Module Dimensions (hwd, cm) | 6.60 x 27.94 x 11.43 |
| UPS Power Module Dimensions (hwd, in.) | 2.6 x 11 x 4.5 |
| UPS Power Module Weight (kg) | 1.81 |
| UPS Power Module Weight (lbs.) | 4 |
| ENVIRONMENTAL | |
| Operating Temperature Range | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius |
| Storage Temperature Range | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |
| Relative Humidity | 0 to 95%, non-condensing |
| AC Mode Efficiency Rating (100% Load) | 94% |
| COMMUNICATIONS | |
| Communications Interface | None |



Powering Business Worldwide



| LINE / BATTERY TRANSFER | |
|--|---|
| Transfer Time | 2-4 milliseconds |
| Low Voltage Transfer to Battery Power (Setpoint) | 99V |
| High Voltage Transfer to Battery Power (Setpoint) | 141V |
| APPLICATIONS | |
| UPS Applications | Computer/Peripherals |
| WARRANTY & SUPPORT | |
| Product Warranty Period (U.S. & Canada) | 3-year limited warranty |
| Product Warranty Period (Latin America) | 3-year limited warranty |
| Product Warranty Period (International) | 2-year limited warranty |
| Product Warranty Period (Mexico) | 3-year limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$100,000 Ultimate Lifetime Insurance |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.