



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: HT10DBS

10 outlet, 8ft cord, 3570 joule, All metal housing block, 3-line coaxial 1-line tel/modem 1-line network protection - Isobar Home/Business Theater Premium Surge Suppressor



Highlights

- 10 outlets / 8-ft. cord
- 3570 joule rating
- Isolated Filter Banks / all-metal housing
- 3-line coaxial (gold) surge protection
- 1-line tel/modem and 1-line network (100BaseT, high-speed) surge protection
- \$500,000 [Ultimate Lifetime Insurance](#) (USA and Canada only)

Description

Tripp Lite's HT10DBS Isobar Home/Business Theater Surge Suppressor provides premium protection--3570 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for medium-to-large home/business theater installations: high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. 10 outlets (with transformer spacing and plug-in safety covers), 3-line coaxial protection, 1-line tel/modem protection and 1-line network (100BaseT, high-speed) protection safeguard an entire home/business theater system. \$500,000 [Ultimate Lifetime Insurance](#) coverage (USA and Canada only). Includes all-metal housing, color-coordinated outlet/plug labels, three diagnostic LEDs, 8-ft. cord with a right-angle plug, 6-ft. gold coax cable, 6-ft. phone cord and 6-ft. network cable.

Applications

- Perfect for medium-to-large home/business theater installations: high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more.

Package Includes

- HT10DBS Home/Business Theater Surge Suppressor
- 6-ft. DSS cable
- 6-ft. phone cord
- 6-ft. network cable
- Instruction manual with warranty information

Features

- 3570 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$500,000 [Ultimate Lifetime Insurance](#) (USA and Canada only) covers connected components against surge damage...for life!
- Isolated Filter Banks eliminate interference between connected components
- All-metal housing safely withstands the strongest surges
- 10 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely spaced outlets accommodate up to 6 transformers

- Four plug-in safety covers protect against accidental contact with unused outlets
- 3 sets of surge-protected Type F gold coaxial connectors (with included 6-ft. gold coax cable) safeguard components on cable, satellite and antenna line
- 1-line tel/modem and 1-line network (100BaseT, high-speed) surge protection (with included 6-ft. phone cord and 6-ft. network cable) safeguards personal video recorders (PVRs) on up to two lines simultaneously.
- 8-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 3 diagnostic LEDs alert user to protection, line power and ground status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- All-metal housing (black) stands up to the most demanding environments
- UL and cUL listed
- Lifetime product warranty
- Color-coordinated outlet/plug labels

Specifications

OVERVIEW	
Intended Application	Audio/Video
SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1440
Output volt amp capacity (amps)	12
Outlet quantity / type	10 NEMA 5-15R
Transformer accommodation	Accommodates 6 transformers
INPUT	
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right-angle input plug
Input cord length (ft.)	8 ft.
Input cord length (m)	2.4
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and illuminated 2 position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm line power, protection and ground status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	3570 joules
AC suppression response time	NM = instantaneous CM = < 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	140V

UL1499 let through rating	330V - UL verified
EMI / RFI filtering	Up to 60 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	Yes
PHYSICAL	
Unit Dimensions (HWD/in)	14.25 x 2.25 x 3.5
Unit Dimensions (HWD/cm)	36.2 x 2 x 5.7
Unit weight (lbs)	3.5
Unit weight (kg)	1.6
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting slots allow desk or wall mounting
AC line cord color	Black
Style	Strip
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Standard warranty period	Lifetime
Connected equipment insurance (USA, Canada, Puerto Rico)	\$500,000

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2813.

© 2009 Tripp Lite. All Rights Reserved.