

## Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE - White, 7 ft. (2.13 m)

MODEL NUMBER: N001-007-WH



### Description

This White snagless Cat5e Ethernet cable has two snagless RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair solid UTP and is rated for 350 MHz/1 Gbps communication. All cables are offered in a variety of lengths and colors for all Cat5 and Cat5e cabling needs. Standard, non-snagless Cat5e cables are also available (N002-Series).

### Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 7-ft. (2.13 m) color: White connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002-Series)
- Also available - Cat6 cables (N201-Series)

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| UPC Code   | 037332172549 |
| Technology | Cat5/5e      |
| POWER      |              |

### Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

### System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

### Package Includes

- 7-ft. (2.13 m) White Snagless Cat5e Patch Cable



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                 |                                 |
|---------------------------------|---------------------------------|
| Power Over Cable (PoC) Support  | No                              |
| <b>CONNECTIONS</b>              |                                 |
| Side A - Connector 1            | RJ45 (MALE)                     |
| Side B - Connector 1            | RJ45 (MALE)                     |
| Crossover Wiring                | No                              |
| Contact Plating                 | Gold                            |
| PoE Type                        | Type 2 PoE+ (30W, IEEE 802.3at) |
| Connector Type                  | Molded; Snagless                |
| Wiring Configuration            | EIA/TIA 568B                    |
| Angled Connector                | No                              |
| <b>PHYSICAL</b>                 |                                 |
| Cable Jacket Color              | White                           |
| Cable Jacket Material           | PVC                             |
| Cable Jacket Rating             | CM                              |
| Cable Shielding                 | UTP                             |
| Cable Outer Diameter (OD)       | 5.0 mm                          |
| Number of Conductors            | 4 Pair                          |
| Conductor Material              | Stranded Copper                 |
| Conductor Gauge                 | 26 AWG                          |
| Cable Length (ft.)              | 7                               |
| Cable Length (m)                | 2.13                            |
| Cable Length (in.)              | 84                              |
| Cable Length (cm)               | 213.4                           |
| Shipping Dimensions (hwd / in.) | 0.25 x 5.00 x 7.00              |
| Shipping Dimensions (hwd / cm)  | 0.64 x 12.70 x 17.78            |
| Shipping Weight (lbs.)          | 0.20                            |
| Shipping Weight (kg)            | 0.09                            |
| Unit Dimensions (hwd / in.)     | 0.000 x 0.000 x 0.000           |
| <b>ENVIRONMENTAL</b>            |                                 |
| Operating Temperature Range     | 14° to 104°F (-10° to 40°C)     |
| Storage Temperature Range       | 5° to 122°F (-15° to 50°C)      |
| Operating Humidity Range        | 0% to 90% RH, Non-Condensing    |
| Storage Humidity Range          | 0% to 90% RH, Non-Condensing    |



Powering Business Worldwide

TRIPP LITE  
SERIES

| COMMUNICATIONS                      |  |
|-------------------------------------|--|
| Bandwidth per TIA Standard          | 100 MHz  |
| Maximum Bandwidth as Tested         | 350 MHz  |
| Network Compatibility               | 1 Gbps (Gigabit)   |
| IEEE Standards Supported            | 802.3ab; 802.3at   |
| FEATURES & SPECIFICATIONS           |  |
| Antibacterial                       | No   |
| IP68 Rated                          | No   |
| Snagless Connector                  | No   |
| IP20 Rated                          | No   |
| STANDARDS & COMPLIANCE              |  |
| Product Certifications              | UL Listed; cUL Listed  |
| Product Compliance                  | CE (Europe); RoHS; IEEE 802.3ab 1000Base-T; IEEE 802.3at PoE+; REACH; UKCA |
| WARRANTY & SUPPORT                  |  |
| Product Warranty Period (Worldwide) | Lifetime limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.