



Cat5e 350 MHz Crossover Molded (UTP) Ethernet Cable (RJ45 M/M), PoE - Yellow, 25 ft. (7.62 m)

MODEL NUMBER: N010-025-YW



Highlights

- 25ft Yellow Cat5e Cross Over Cable w/Green Molded Strain Relief
- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- PVC 4-pair stranded UTP

Package Includes

• 25-ft. (7.62 m) Cat5e Yellow Crossover Molded Patch Cable

Description

This Yellow Cat5e Cross-Over Cable has two standard RJ45 male connectors featuring integral strain relief. The cable is designed to connect switch-to-switch, PC-to-PC or Mac-to-Mac, and is perfect in conjunction with 10 and 100 Base-T networks. Molded connectors are a different color to help identify this cable as a cross-over cable and not a standard Ethernet cable. Manufactured from PVC 4-pair stranded UTP and rated for 350 MHz/1 Gbps communication. Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11).

Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 25-ft. (7.62 m) color: Yellow with green connectors. Connectors: RJ45 male
- Cross-over wiring designed to connect Switch-to-Switch or PC-to-PC
- Feature molded connectors with integral strain relief
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE
- 02.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- · Available in other lengths / colors

Specifications

OVERVIEW		
UPC Code	037332164124	
Technology	Cat5/5e	
POWER		
Power Over Cable (PoC) Support	No	





CONNECTIONS		
Side A - Connector 1	RJ45 (MALE)	
Side B - Connector 1	RJ45 (MALE)	
Crossover Wiring	Yes	
Contact Plating	Gold	
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)	
Connector Type	Molded; Crossover	
Wiring Configuration	EIA/TIA 568B to EIA/TIA 568A	
Angled Connector	No	
PHYSICAL		
Cable Jacket Color	Yellow	
Cable Jacket Material	PVC	
Cable Jacket Rating	СМ	
Cable Shielding	UTP	
Cable Outer Diameter (OD)	5.0 mm	
Number of Conductors	4 Pair	
Conductor Material	Stranded Copper	
Conductor Gauge	26 AWG	
Cable Length (ft.)	25	
Cable Length (m)	7.62	
Cable Length (in.)	300	
Cable Length (cm)	762	
Shipping Dimensions (hwd / in.)	0.50 x 5.80 x 6.10	
Shipping Dimensions (hwd / cm)	1.27 x 14.73 x 15.49	
Shipping Weight (lbs.)	0.40	
Shipping Weight (kg)	0.18	
ENVIRONMENTAL		
Operating Temperature Range	14° to 104°F (-10° to 40°C)	
Storage Temperature Range	5° to 122°F (-15° to 50°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
COMMUNICATIONS		
Bandwidth per TIA Standard	100 MHz	





Maximum Bandwidth as Tested	350 MHz	
Network Compatibility	1 Gbps (Gigabit)	
IEEE Standards Supported	802.3ab; 802.3at	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	
Snagless Connector	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Certifications	UL Listed; cUL Listed	
Product Compliance	CE (Europe); RoHS; IEEE 802.3ab 1000Base-T; IEEE 802.3at PoE+; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.