



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: N002-010-BL

10-ft. Cat5e 350MHz Molded Cable (RJ45 M/M) - Blue



Highlights

- Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
- IEEE 802.3ab
- PVC 4-pair stranded UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

Description

Tripp Lite's 10-ft. blue category 5e (Cat5e) patch cable has 2 standard RJ45 molded male connectors featuring integral strain relief. The cable is manufactured from PVC 4-pair stranded UTP and is rated for 350MHz/1Gbps communication. All cables are offered in a variety of lengths and colors for all category 5 (Cat5) and 5e cabling needs. Snagless category 5e patch cables are also available. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.



Package Includes

- 10-ft. Cat5e Blue Patch Cable Molded 350MHz

Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 10-ft. Color: blue
- Connectors: RJ45 male
- Feature molded connectors with integral strain relief
- PVC 4-pair stranded UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available in a snagless design (N001 series) to protect the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- Also available - Cat6 cables (N201 series)
- Warranted to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
Intended Application	Computer Networking
Model Type	Patch Cables
PHYSICAL	
Color	Blue
Style	Cat5/5e
Length	10 ft.
CONNECTIONS	
Connector A	 RJ45 (MALE)
Connector B	 RJ45 (MALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	-
Patch Panels	N001-010-BL	10-ft. Cat5e 350MHz Snagless Molded Cable (RJ45 M/M) - Blue	-
Patch Panels	N002-010-BK	10-ft. Cat5e 350MHz Molded Cable (RJ45 M/M) - Black	-
Patch Panels	N002-010-GN	10-ft. Cat5e 350MHz Molded Cable (RJ45 M/M) - Green	-
Patch Panels	N002-010-GY	10-ft. Cat5e 350MHz Molded Cable (RJ45 M/M) - Gray	-
Patch Panels	N002-010-RD	10-ft. Cat5e 350MHz Molded Cable (RJ45 M/M) - Red	-
Patch Panels	N002-010-YW	10-ft. Cat5e 350MHz Molded Cable (RJ45 M/M) - Yellow	-
Patch Panels	N002-014-BL	14-ft. Cat5e 350MHz Molded Cable (RJ45 M/M) - Blue	-
Patch Panels	N010-007-GY	7-ft. Cat5e 350MHz Molded Cross-over Cable (RJ45 M/M) - Gray	-
Patch Panels	N022-01K-GY	1000-ft. Cat5e 350MHz Bulk Solid-core PVC Cable - Gray	-
Patch Panels	N032-001	Cat5e Straight Through Modular In-line Coupler (RJ45 F/F)	-
Patch Panels	N033-001	Straight Through Modular In-line Coupler (RJ45 F/F)	-
Patch Panels	N050-012	12-Port Cat5e Wall Mount Patch Panel 568B	-

Patch Panels	N052-012	12-Port Cat5e Patch Panel 568B	-
Patch Panels	N052-024	24-Port Cat5e Patch Panel 568B	-
Patch Panels	N052-048	48-Port Cat5e Patch Panel 568B	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2115.