



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@triplite.com

Model #: N201-014-BL

14-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Blue

Highlights



- Meets Category 6 cabling standards.
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 6, draft 11)
- Drastically reduce impedance & structural return loss compared to standard 100MHz wire.
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation
- Feature molded connectors with integral strain relief. Rated for 550 MHz/1 Gbps communication.
- Lifetime product warranty

Description

With Tripp Lite's new category 6 molded patch cables you can stay ahead of the game by using this high-speed cable to distribute data, voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in category 6, category 5e and category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications



Package Includes

- 14-ft. Cat6 Blue Gigabit Patch Cord Snagless Molded

Features

- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Length: 14-ft. color: blue connectors: RJ45 male
- Drastically reduce impedance & structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in other colors and lengths
- Warranted to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
Intended Application	Computer Networking
Model Type	Snagless Patch Cables
INPUT	
Cable Length (ft.)	14
PHYSICAL	
Color	Blue
Style	Cat6/6e/6a
CONNECTIONS	
Connector A	 RJ45 (MALE)
Connector B	 RJ45 (MALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
Approvals	EIA/TIA Cat6 TIA/EIA- 568-B-2.1
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	Lifetime limited warranty

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Patch Cables	N201-003-BL	3-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Blue	1
Patch Cables	N201-005-BL	5-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Blue	1
Patch Cables	N201-007-BL	7-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Blue	1
Patch Cables	N201-010-BL	10-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Blue	1
Patch Cables	N201-014-GN	14-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Green	1
Patch Cables	N201-014-GY	14-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Gray	1
Patch Cables	N201-025-BL	25-ft. Cat6 Gigabit Snagless Molded Patch Cable (RJ45 M/M) - Blue	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2517.

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.