



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: N105-025-GY

25-ft. Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray

Highlights

- Protect your network data from EMI/RFI interference
- Molded boot provides extra strain-relief and durability



Description

Protect your high-speed network from noise and electromagnetic interference with Tripp Lite's 25-ft. gray, Category 5e (Cat5e) Shielded patch cable. This cable features 2, shielded RJ45 50micron Gold molded male connectors with integral strain relief. The cable is manufactured from PVC, 4-pair, stranded shielded twisted pair, and is rated for 350MHz/1Gbps communication. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

Package Includes

- 25ft Gray Cat5e Shielded Patch Cable

Features

- Provides EMI/RFI shielding in Ethernet networks
- Shielded RJ45, w/50-micron gold plated contacts
- 4-pair 24 AWG Stranded STP with drain wire
- Molded boot for extra strain-relief and durability
- TSB 568B (AT&T 258A)Wiring
- TIA/EIA and UL Certified

Specifications

OVERVIEW	
Intended Application	Computer Networking
Model Type	Shielded Patch Cables
PHYSICAL	
Color	Gray
Style	Cat5/5e

Length	25ft
CONNECTIONS	
Connector A	RJ45 (MALE)
Connector B	RJ45 (MALE)
Number of Connectors	2
CERTIFICATIONS	
Certifications	RoHS-Compliant

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Patch Cables	N105-007-GY	7-ft. Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray	-
Patch Cables	N105-010-GY	10-ft. Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray	-
Patch Cables	N105-050-GY	50-ft. Cat5e 350MHz Molded Shielded Patch Cable (RJ45 M/M) - Gray	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3043.