



Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE, Blue, 20 ft. (6.09 m)

MODEL NUMBER: N201-020-BL



Features

- Meets category 6 cabling standards
- · Premium cabling for category 6, category 5e and category 5 applications
- Length: 20-ft. (6.09 m) / Color: blue / Connectors: RJ45 male
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair solid UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- · Available in other colors and lengths

Highlights

- Meets Category 6 cabling standards
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 6, draft 11)
- Drastically reduce impedance and structural return loss compared to standard 100Mhz wire.
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation
- Feature molded connectors with integral strain relief. Rated for 550 MHz/1 Gbps communication

System Requirements

For 1000 Base-T (1Gbps
 Ethernet), 10/100 Base-T
 (Ethernet), 100 Mbps TPDDI,
 155 Mbps ATM, ISDN, voice
 and Token Ring TYPE 3
 applications as well as EIA/TIA
 applications.

Package Includes

20-ft. (6.09 m) Cat6 Blue Gigabit
 Patch Cord Snagless Molded

Specifications

OVERVIEW		
UPC Code	037332122063	
Technology	Cat6; PoE	
PRODUCT OVERVIEW		
Product Overview	Cat6 Gigabit Blue Snagless Patch Cable RJ45 - 20'	





CONNECTIONS		
Side A - Connector 1	RJ45 (MALE)	
Side B - Connector 1	RJ45 (MALE)	
Crossover Wiring	No	
Contact Plating	Gold	
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)	
Connector Type	Snagless; Molded	
Wiring Configuration	EIA/TIA 568B	
Angled Connector	No	
PHYSICAL		
Cable Jacket Color	Blue	
Cable Jacket Material	PVC	
Cable Jacket Rating	СМ	
Cable Shielding	UTP	
Cable Outer Diameter (OD)	6.0 mm	
Number of Conductors	4 Pair	
Conductor Material	Solid Copper	
Conductor Gauge	24 AWG	
Cable Length (ft.)	20	
Cable Length (m)	6.10	
Cable Length (in.)	240	
Cable Length (cm)	609.6	
Shipping Dimensions (hwd / in.)	8.00 x 10.00 x 0.50	
Shipping Dimensions (hwd / cm)	20.32 x 25.40 x 1.27	
Shipping Weight (lbs.)	0.65	
Shipping Weight (kg)	0.29	
ENVIRONMENTAL		
Operating Temperature Range	14° to 122°F (-10° to 50°C)	
Storage Temperature Range	5° to 140°F (-15° to 60°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
COMMUNICATIONS		
Bandwidth per TIA Standard	250 MHz	





Maximum Bandwidth as Tested	500 MHz	
Network Compatibility	1 Gbps (Gigabit)	
IEEE Standards Supported	802.3an; 802.3at	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	
Snagless Connector	Yes	
STANDARDS & COMPLIANCE		
Product Certifications	UL Listed; cUL Listed	
Product Compliance	CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.