



Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), PoE, Black, 50 ft. (15.24 m)

MODEL NUMBER: N201-050-BK



Highlights

- Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications
- Designed to meet Category 6 specifications; reduces crosstalk and return loss
- IEEE 802.3ab
- PVC 4-pair solid UTP
- All cables feature boots with integral strain-relief and RJ45 (Male) connectors

Package Includes

 50-ft. (15.24 m) Cat6 Black Gigabit Patch Cord Snagless Molded

Features

- Length: 50-ft. (15.24 m) (15.24 m)/ Color: Black / Connectors: RJ45 male
- · Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation

Specifications

OVERVIEW		
UPC Code	037332139207	
Technology	Cat6; PoE	
CONNECTIONS		
Side A - Connector 1	RJ45 (MALE)	
Side B - Connector 1	RJ45 (MALE)	
Crossover Wiring	No	
Contact Plating	Gold	
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)	
Connector Type	Snagless; Molded	





Wiring Configuration	EIA/TIA 568B	
Angled Connector	No	
PHYSICAL		
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	СМ	
Cable Shielding	UTP	
Cable Outer Diameter (OD)	6.0 mm	
Number of Conductors	4 Pair	
Conductor Material	Solid Copper	
Conductor Gauge	24 AWG	
Cable Length (ft.)	50	
Cable Length (m)	15.24	
Cable Length (in.)	600	
Cable Length (cm)	1524	
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50	
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27	
Shipping Weight (lbs.)	1.60	
Shipping Weight (kg)	0.73	
ENVIRONMENTAL		
Operating Temperature Range	14° to 122°F (-10° to 50°C)	
Storage Temperature Range	5° to 140°F (-15° to 60°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
COMMUNICATIONS		
Bandwidth per TIA Standard	250 MHz	
Maximum Bandwidth as Tested	500 MHz	
Network Compatibility	1 Gbps (Gigabit)	
IEEE Standards Supported	802.3an; 802.3at	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	
Snagless Connector	Yes	





STANDARDS & COMPLIANCE		
Product Certifications	UL Listed; cUL Listed	
Product Compliance	CE (Europe); RoHS; IEEE 802.3an 10GBase-T; IEEE 802.3at PoE+; REACH; UKCA	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.