


Cat6 Gigabit Solid Core UTP PVC Bulk Ethernet Cable, Blue, 1000 ft. (304.8 m), TAA

MODEL NUMBER: N222-01K-BL



Highlights

- Meets category 6 cabling standards
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- 4pr Solid - CMR PVC Jacket

System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications

Package Includes

- 1000Ft Cat6 Gigabit Bulk Solid Blue PVC Cable

Features

- Designed for premise (in-wall) cabling applications
- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Drastically reduce impedance and structural return loss compared to standard 100MHz wire
- High-quality copper wire
- Length: 1000-ft. Color: Blue Reel-in-a-Box
- 23 AWG, 4-pair solid cable with PVC (CMR) jacket
- Deliver stable performance up to 550MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)

Specifications

OVERVIEW	
UPC Code	037332123077
Technology	Cat6
CONNECTIONS	
Side A - Connector 1	BARE WIRE
Side B - Connector 1	BARE WIRE
Crossover Wiring	No
Connector Type	Bare Wire
Angled Connector	No



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Cable Jacket Color	Blue
Cable Jacket Material	PVC
Cable Jacket Rating	CMR
Cable Shielding	UTP
Cable Outer Diameter (OD)	6.2 mm
Number of Conductors	4 Pair
Conductor Material	Solid Copper
Conductor Gauge	23 AWG
Cable Length (ft.)	1000
Cable Length (m)	304.88
Cable Length (in.)	12000
Cable Length (cm)	30480
Shipping Dimensions (hwd / in.)	13.78 x 14.70 x 13.78
Shipping Dimensions (hwd / cm)	35.00 x 37.34 x 35.00
Shipping Weight (lbs.)	29.75
Shipping Weight (kg)	13.49
Unit Dimensions (hwd / in.)	13.780 x 14.700 x 13.780
ENVIRONMENTAL	
Operating Temperature Range	-4° to 167°F (-20° to 75°C)
Storage Temperature Range	32° to 140°F (0° to 60°C)
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Bandwidth as Tested	500 MHz
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3ab
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; IEEE 802.3ab 1000Base-T; REACH; Trade Agreements Act (TAA)



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.