

## Fiber Optic Mode Conditioning Patch Cable (SC/LC), 5M (16 ft.)

MODEL NUMBER: **N424-05M**



### Highlights

- Converts Singlemode SC GBIC to Multimode LC Patch Panel
- 62.5/125 and 9/125
- Run 1000Base-LX Gigabit Ethernet over MMF by offsetting signal loss

### Package Includes

- SC / Mode Conditioning to LC Fiber Optic Patch Cable, 5M ( 16-ft. )

### Features

- Use SC GBIC Singlemode Transceivers on Multimode Fiber Backbones with LC patch bays
- 62.5/125 and 9/125
- Offsets the Singlemode Laser launch from the center of a Multimode fiber
- Available in a variety of connector combinations

## Specifications

OVERVIEW	
UPC Code	037332127266
Optical Mode	OM1
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	SC DUPLEX (MALE)
Endface Polish	PC
PHYSICAL	
Cable Jacket Color	Orange; Yellow
Connector Color	Blue; Gray; Black
Cable Jacket Material	PVC
Cable Jacket Rating	OFNR
Clad Diameter (microns)	125



Powering Business Worldwide

TRIPP LITE  
SERIES

Core Diameter (microns)	62.5
Number of Fibers	2
Cable Length (ft.)	16.4
Cable Length (m)	5.00
Cable Length (in.)	196.9
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.16
Shipping Weight (kg)	0.08
Fiber Cable Length	5M (16.4 ft)
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 65% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Attenuation @ 850NM	3.0 dB/km
Insertion Loss	MM to MM 0.20 dB; MM to SM 0.30 dB
<b>FEATURES &amp; SPECIFICATIONS</b>	
Push/Pull Tabs	No
Breakout	No
Trunk	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.