



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: OMNIVS800

Omni VS Line Interactive UPS System



Highlights

- 800VA line interactive tower UPS
- Corrects brownouts to 89V, without using battery power
- Workstation optimized features include HID enabled USB port and single line TEL / DSL surge suppression and one surge-only outlet
- Input: NEMA 5-15P (120V 15A) / Output: 7 NEMA 5-15R (120V)
- 3 year product warranty / \$200,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's OMNIVS800 line interactive UPS system offers voltage regulation, surge suppression and long lasting battery support for personal computers, inter-networking equipment and other sensitive electronics. Internal UPS circuits support entry level PC systems for up to 60 minutes during power failures so that connected equipment can be shut down without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. Offers complete desktop power protection in an attractive black tower configuration. Includes 6 battery supported outlets for computer, monitor and one vital system peripheral, plus 1 additional surge suppression-only outlet for printers and other system accessories not requiring battery support. HID-compliant USB port enables optional unattended system shutdown without data loss in case of extended power failure; USB cable included. HID-compliant USB port also enables direct integration with built-in power management and auto-shutdown features of Windows and MAC OS X. PowerAlert software available via free download from www.tripplite.com. Built-in single line phone/Ethernet suppression jacks protect modem, fax machine, cordless phone or other peripheral with a standard dialup, DSL, or data line connection. Built-in audible alarm and 4 front panel LEDs indicate line power status, battery power status, battery low/replace status and voltage boost operation. 800VA/475 watt power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Offers 3.5 minutes battery runtime with a full load of 800VA and 11.5 minutes with a half load of 400VA. Supports battery replacement via built-in access panel. 3 year warranty. \$200,000 [connected equipment insurance](#) (USA & Canada Only).

Package Includes

- OMNIVS800 Line Interactive UPS
- USB and telephone cable
- User manual with warranty information

Features

- OMNIVS800 Uninterruptible Power Supply offers voltage regulation, surge suppression and long lasting battery support
- Supports entry level PCs up to 60 minutes during blackouts to enable shutdown without data loss
- Regulates brownouts as low as 89 volts back to usable levels without using battery power
- 6 UPS battery supported/surge protected outlets, plus 1 additional surge suppression-only outlet
- Built-in HID-compliant USB port and PowerAlert UPS power management software (available via free download at tripplite.com) and cabling provide monitoring of in-depth site power conditions, full UPS status and fault warnings, and output load level
- HID-compliant USB port also enables direct integration with built-in power management and auto-shutdown features of Windows and MAC

OS X

- Single line phone/Ethernet suppression jacks protects standard dialup/DSL, or Ethernet connections
- Audible alarm and 4 front panel LEDs offer complete UPS and line power status information
- 800VA/475 watt power handling ability supports a variety of sensitive electronic equipment
- 3.5 minutes full load runtime (800VA), 11.5 minutes half load runtime (400VA)
- Supports battery replacement via built-in access panel
- 3 year product warranty.
- \$200,000 [connected equipment insurance](#) (USA & Canada Only).

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	800
Output Watt Capacity (watts)	475
Nominal Output Voltage(s) Supported	115v; 120v
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	7 5-15R outlet(s)
Surge suppression only outlets	6 UPS outlets, 1 surge-only outlet
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P; Space saving right angled input plug
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	3.5 min. (475w)
Half load runtime (minutes)	11.5 min. (240w)
DC system voltage	12V DC

Battery recharge rate (included batteries)	Less than 4.5 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC51
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage correction	Input voltages between 89 and 105 are boosted by 14%
LEDS ALARMS & SWITCHES	
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
Alarms	Audible alarm indicates power-failure and low-battery conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	480
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL / DSL or 10Base T Ethernet protection
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Installation form factors supported with optional accessories	Wallmount (use UPSWM - tower mounting kit)
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	10.8 x 5.2 x 7.5
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	27.3 x 13.3 x 19
UPS / Power Module weight (lbs)	15.9
UPS / Power Module weight (kg)	7.2

UPS Shipping dimensions (height x width x depth / inches)	13.5 x 10.2 x 11
UPS Shipping dimensions (height x width x depth / cm)	34.3 x 26 x 27.9
Shipping weight (lbs)	17.5
Shipping weight (kg)	7.9
UPS housing material	PVC
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	49.9
Battery mode BTU / hr. (full load)	455.5
COMMUNICATIONS	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from www.tripplite.com
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	89
High voltage transfer to battery power (setpoint)	139
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); Meets FCC Part 68 / Industrie Canada (telecommunications); ROHS (Reduction of Hazardous Substances)
WARRANTY	

Standard warranty period	3 years
Connected equipment insurance (USA, Canada, Puerto Rico)	\$200,000 connected equipment insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Surge Protectors	DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	-
Surge Protectors	DNET1	Network Surge Suppressor - Essential protection for data and communication lines	-
Surge Protectors	DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	-
USB Hubs/Accessories	U022-010	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	-
Wallmount Bracket	UPSWM	Wallmount Bracket and installation accessories (4 washers, 4 screws, 1 Velcro safety strap)	-
Software	WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	-
Extended Warranties	WEXT5-OMNI	5-Year Extended Warranty - For OmniSmart, OmniPro, OmniVS	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2729.