



VGA Easy Pull High-Resolution RGB Coaxial Cable (HD15 M/M), 100 ft. (30.5 m)

MODEL NUMBER: P503-100



Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection

Package Includes

 100-ft. (30.5 m) Male/Male Easy Pull SVGA/VGA Monitor Cable w/ Connectors

Description

Tripp Lite's 100-ft. (30.5 m) SVGA/VGA Easy Pull Monitor Cable with Connectors makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a HD15 connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. The mini-coax (RGB) and paired video wire construction delivers superior signal quality. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both high density DB15 males are molded and have integral strain relief to ensure they last a long time.

Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- · Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- RGB 75-ohm coax construction for maximum video resolution
- HD15 male to HD15 male molded connectors
- Supports resolutions up to 1600 x 1200

Specifications

OVERVIEW		
UPC Code	037332142276	
Product Type	Passive Cable	
Technology	Coax; VGA/SVGA	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	HD15 (MALE)	





Side B - Connector 1	HD15 (MALE)	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Length (ft.)	100	
Cable Length (m)	30.49	
Cable Length (in.)	1200	
Shipping Dimensions (hwd / in.)	17.00 x 14.00 x 1.00	
Shipping Dimensions (hwd / cm)	43.18 x 35.56 x 2.54	
Shipping Weight (lbs.)	7.60	
Shipping Weight (kg)	3.45	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
IP20 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; EIA/ECA-310-E	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
	·	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.