

## DVI Dual Link Extension Cable, Digital TMDS Monitor Cable (DVI-D M/F), 6 ft. (1.83 m)

MODEL NUMBER: P562-006



### Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Dual Link digital signaling for transmission speeds to 9.9Gbps
- 2560x1600 @ 60Hz Resolution Support
- Gold plated contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

## Specifications

| OVERVIEW                       |                          |
|--------------------------------|--------------------------|
| UPC Code                       | 037332120649             |
| Product Type                   | Passive Cable            |
| Technology                     | DVI                      |
| Cable Type                     | Passive                  |
| CONNECTIONS                    |                          |
| Side A - Connector 1           | DVI-D DUAL LINK (MALE)   |
| Side B - Connector 1           | DVI-D DUAL LINK (FEMALE) |
| Latching or Gripping Connector | No                       |
| PHYSICAL                       |                          |
| Color                          | Black                    |

### Highlights

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600 @ 60Hz
- High Speed Digital Transmission to 9.9Gbps

### System Requirements

- Monitor with DVI, and CPU with a DVI video card. Video card must support Dual Link in order to obtain resolutions up to 2560 x 1600

### Package Includes

- DVI Dual Link Extension TMDS cable - DVI-D, M/F, 6-ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                           |
|--------------------------------------|---------------------------|
| Cable Jacket Color                   | Black                     |
| Cable Length (ft.)                   | 6                         |
| Cable Length (m)                     | 1.83                      |
| Cable Length (in.)                   | 72                        |
| Shipping Dimensions (hwd / in.)      | 10.00 x 8.00 x 0.50       |
| Shipping Dimensions (hwd / cm)       | 25.40 x 20.32 x 1.27      |
| Shipping Weight (lbs.)               | 0.70                      |
| Shipping Weight (kg)                 | 0.32                      |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| IP68 Rated                           | No                        |
| IP20 Rated                           | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                           |
| Product Compliance                   | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>        |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.