

High-Speed HDMI to Mini HDMI Cable with Ethernet (M/M), 6 ft.

MODEL NUMBER: P571-006-MINI



Highlights

- Supports UHD resolutions up to 4K (4:4:4) for crystal-clear video
- Premium foil and braid shielding protects against EMI/RFI noise
- 24K gold-plated connectors for maximum conductivity

Package Includes

High Speed with Ethernet HDMI to Mini-HDMI Cable, 6 ft.

Description

This HDMI to Mini-HDMI cable allows you to connect digital cameras, camcorders and other digital devices with the Mini-HDMI connector directly to your standard HDMI-enabled TV. This cable offers the same baseline performance as standard high-speed HDMI cables (including 1080p video resolution), plus an additional dedicated data channel, known as the HDMI Ethernet Channel, for device networking. HDMI Ethernet Channel functionality is only available if both linked devices are HDMI Ethernet Channel-enabled. Cable supports not only the Ethernet component, but also 3D and Audio Return Channel.

Features

Connects Mini-HDMI and HDMI Devices

- Recommended for mobile users who want a cable that can easily pack away in a backpack, laptop bag or camera bag
- Ideal for connecting a mini-HDMI camcorder, digital camera or tablet to an HDMI display

High Performance and Wide Compatibility

- Supports HD video resolutions up to 1080p
- Superior Quality Ensures a Flawless Signa
- 24K gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Flexible PVC jacket easy to install in tight spaces

Specifications

| OVERVIEW | |
|--------------|---------------|
| UPC Code | 037332175601 |
| Product Type | Passive Cable |
| Technology | HDMI |
| Cable Type | Passive |

| VIDEO | |
|-----------------------------------|-------------------------|
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 30Hz |
| Max Supported Color Depth | 48-bit Deep Color |
| HDR Support | No |
| 3D Video Supported | Yes |
| Chroma Sub Sampling | 4:4:4; 4:2:2 |
| EDID Support | Yes |
| Signal Transmission | Bidirectional |
| AUDIO | |
| Audio Specification | Stereo Audio |
| CONNECTIONS | |
| Side A - Connector 1 | MINI HDMI (MALE) |
| Side B - Connector 1 | HDMI (MALE) |
| Connector Plating | Nickel |
| Contact Plating | Gold |
| Connector Style | Straight |
| Latching or Gripping Connector | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| LED Indicators | 0 |
| PHYSICAL | |
| Color | Black |
| Cable Jacket Color | Black |
| Connector Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Cable Outer Diameter (OD) | 6.0 mm |
| Wire Gauge (AWG) | 30 |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Cable Length (in.) | 72 |
| Ferrite Core | No |
| Minimum Bend Radius | 60mm |
| Shipping Dimensions (hwd / in.) | 0.25 x 7.00 x 7.00 |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--|-------------------------------|
| Shipping Dimensions (hwd / cm) | 0.64 x 17.78 x 17.78 |
| Shipping Weight (lbs.) | 0.10 |
| Shipping Weight (kg) | 0.05 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 140°F (0° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 30% to 90% RH, Non-Condensing |
| Storage Humidity Range | 30% to 90% RH, Non-Condensing |
| COMMUNICATIONS | |
| Consumer Electronics Control (CEC) Supported | Yes |
| FEATURES & SPECIFICATIONS | |
| EMI/RFI Line Noise Protection | No |
| MST Support | No |
| Antibacterial | No |
| IP68 Rated | No |
| IP20 Rated | No |
| Armored Cable | No |
| Ethernet Support | Yes |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.