

## 1.8kW Single-Phase 120V Basic PDU, 14 NEMA 5-15R Outlets, NEMA 5-15P Input, 15 ft. (4.57 m) Cord, 0U Vertical

MODEL NUMBER: PDU1415



Delivers 120V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a high-density IT environment. Ideal for networking, telecom, security, audio/video and sound reinforcement applications.

### Description

The PDU1415 1.8kW Single-Phase 120V Basic PDU is the perfect no-frills unit for networking, telecom, security, audio/video and sound reinforcement applications. Perfectly suited for high-density IT environments, the PDU1415 features a single breakered load bank with 14 NEMA 5-15R outlets. The NEMA 5-15P input plug with long 15-ft. (4.57 m) cord connects to your facility's compatible AC power source, generator or protected UPS to distribute power to connected equipment.

The switchless design prevents an accidental shutdown, which could lead to costly downtime. A 15A circuit breaker protects connected equipment from dangerous overloads. The 24-inch all-metal housing supports toolless 0U vertical mounting in EIA-standard 19-inch racks, as well as on a wall or workbench or under a counter with user-supplied hardware.

### Features

#### Reliable Single-Phase Power Distribution

- Ideal no-frills PDU for networking, telecom, security, audio/video and sound reinforcement applications
- 14 NEMA 5-15R outlets in one breakered load bank
- 15A circuit breaker protects outlets against overloads
- NEMA 5-15P input plug with 15-ft. (4.57 m) cord
- 24 in. all-metal housing

#### Switchless Design

- Prevents accidental shutdowns and costly downtime

#### Versatile Installation Options

- Supports toolless 0U vertical mounting in EIA-standard 19 in. racks
- Also mounts on wall, workbench or under a counter with user-supplied hardware

### Highlights

- NEMA 5-15P input with 15-ft. (4.57 m) cord
- 14 NEMA 5-15R outlets
- Switchless design prevents accidental shutdown
- 24 in. all-metal housing
- Supports toolless 0U vertical button-mounting

### Package Includes

- PDU1415 1.8kW Single-Phase 120V Basic PDU
- Mounting hardware
- Owner's manual



Powering Business Worldwide



## Specifications

| OVERVIEW                          |   |
|-----------------------------------|---|
| UPC Code                          | 037332122247  |
| PDU Type                          | Basic   |
| INPUT                             |   |
| Input Phase                       | Single-Phase  |
| PDU Input Voltage                 | 120   |
| Recommended Electrical Service    | Single-phase 15A 120V service                         |
| Maximum Input Amps                | 15  |
| PDU Plug Type                     | NEMA 5-15P  |
| Input Cord Length (ft.)           | 15  |
| Input Cord Length (m)             | 4.57  |
| OUTPUT                            |   |
| Output Capacity Details           | 1.8kW (120V) total capacity; 12A max per 5-15R outlet |
| Frequency Compatibility           | 50 / 60 Hz  |
| Output Receptacles                | (14) 5-15R  |
| Output Nominal Voltage            | 120V  |
| Overload Protection               | 15A Breaker   |
| USER INTERFACE, ALERTS & CONTROLS |   |
| Switches                          | No power switch                                       |
| SURGE / NOISE SUPPRESSION         |   |
| Automatic Shut-Off                | No  |
| PHYSICAL                          |   |
| Material of Construction          | Metal   |
| Form Factors Supported            | 0U vertical rackmount, wall-mount                     |
| PDU Form Factor                   | Vertical (0U)   |
| Shipping Dimensions (hwd / in.)   | 2.40 x 5.60 x 28.30                                   |
| Shipping Dimensions (hwd / cm)    | 6.10 x 14.22 x 71.88                                  |
| Shipping Weight (lbs.)            | 5.30  |
| Shipping Weight (kg)              | 2.40  |
| Unit Dimensions (hwd / in.)       | 1.750 x 25.750 x 2.250                                |
| Unit Dimensions (hwd / cm)        | 4.45 x 61 x 4.34                                      |



Powering Business Worldwide



|                                      |  |
|--------------------------------------|--|
| Unit Weight (lbs.)                   | 4.6  |
| Unit Weight (kg)                     | 2.09   |
| <b>ENVIRONMENTAL</b>                 |  |
| Operating Temperature Range          | 32° to 104°F (0° to 40°C)  |
| Storage Temperature Range            | -22° to 122°F (-30° to 50°C)   |
| Relative Humidity                    | 5% to 95% non-condensing   |
| Operating Elevation                  | 0-10000 ft. (0-3000 m)   |
| <b>FEATURES &amp; SPECIFICATIONS</b> |  |
| Grounding                            | Grounding lug  |
| <b>STANDARDS &amp; COMPLIANCE</b>    |  |
| Product Certifications               | RETIE (Colombia); CAN/CSA-C22.2 No. 60950-1 (Canada); NOM (Mexico); UL 60950-1 |
| Product Compliance                   | RoHS   |
| <b>WARRANTY &amp; SUPPORT</b>        |  |
| Product Warranty Period (Worldwide)  | 5-year limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.