

VGA Coax Monitor Easy Pull Extension Cable, High Resolution Cable with RGB Coax (HD15 M/F), 100 ft. (30.5 m)

MODEL NUMBER: P501-100



Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- 75ohm mini-coax (RGB) and paired video wire construction delivers outstanding signal quality
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection

Package Includes

- 100 ft. Male/Female Easy Pull SVGA/VGA Monitor Extension Cable w/ Connectors
- Wallplate with HD15 cutout

Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- RGB 75-ohm coax construction for maximum video resolution
- HD15 male to HD15 female molded connectors
- Supports resolutions up to 1600 x 1200

Specifications

OVERVIEW	
UPC Code	037332142269
Technology	Coax; VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black



Powering Business Worldwide



Cable Length (ft.)	100
Cable Length (m)	30.49
Shipping Dimensions (hwd / in.)	1.00 x 7.40 x 7.60
Shipping Dimensions (hwd / cm)	2.54 x 18.80 x 19.30
Shipping Weight (lbs.)	4.40
Shipping Weight (kg)	2.00
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.