



5/5.8kW Single-Phase Monitored PDU, 208/240V Outlets (20 C13 & 4 C19), L6-30P, 10ft Cord, 0U Vertical, TAA

MODEL NUMBER: PDUMNV30HV



Description

Tripp Lite Monitored PDU / Power Distribution Unit offers real-time remote monitoring of voltage, frequency and load levels via built-in network connection. PowerAlert interface supports custom notification of user-specified remote conditions via email, PowerAlert Console Launcher, SNMP, Telnet or SSH interface. PDU output current consumption in amps is displayed via front panel lighted digital display and can be monitored remotely to warn of potential overloads before critical IT mains breakers trip.

Features

- 208/240V Monitored PDU with built-in network interface in 0U 70 in. / 178cm vertical rackmount form factor; 30A maximum capacity (agency de-rated to 24A)
- Attached 10 ft. / 3m NEMA L6-30P input cable
- 24 outlets (20 C13, 4 C19) arranged in two separately breakered 20A output load banks
- 0U 70 in. / 178cm vertical rackmount form factor
- Network interface provides PDU control and data regarding input voltage, frequency and loading information
- Digital display with select button reports load level information in amps for all 3 reported loading segments (Bank 1, Bank 2 and total)
- · Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional ENVIROSENSE temperature / humidity sensor and rack access notification with up to 4 optional SRSWITCH door sensors
- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- · Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- · Tiered access privileges allow an administrator and a guest to login simultaneously
- · Alert notifications via email or SNMP traps offer immediate event notification
- · Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols

Highlights

- Monitored 30A 208/240V PDU in 0U 70in / 178cm vertical rackmount format
- Reports voltage, frequency and load level via ethernet interface
- Visual current meter, Toolless button-mount installation
- NEMA L6-30P input plug with 10ft / 3m line cord
- 24 outlets (20 C13, 4 C19) with included cord retention brackets
- Temperature, humidity and contact-closure monitoring options
- TAA Compliant

Package Includes

- Rackmount PDU
- Plug retention plates
- · Rack mounting brackets
- Owner's manual





- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included cord retention brackets
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

Specifications

OVERVIEW		
UPC Code	037332149541	
PDU Type	Monitored	
INPUT		
Input Phase	Single-Phase	
Recommended Electrical Service	30A 208/240V	
Maximum Input Amps	30	
Maximum Input Amps Details	Agency de-rated to 24A continuous	
PDU Plug Type	NEMA L6-30P	
Input Cord Length (ft.)	10	
Input Cord Length (m)	3.05	
OUTPUT		
Output Capacity Details	5.8kW (240V), 5kW (208V), 4.8kW (200V) total capacity / 30A max (Agency de-rated to 24A), 20A max per breakered outlet bank; 16A max per C19 outlet; 12A max per C13 outlet	
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(20) C13; (4) C19	
Output Nominal Voltage	200; 208; 240	
Overload Protection	Two 20A breakers protect 12 outlets each	
USER INTERFACE, ALERTS & CONTROLS		
Front Panel LCD Display	Digital meter reports PDU output current in amps, Scroll IP-address information; Display can be rotated 180 degrees for installation with the input cable at the top	
Front Panel LEDs	Front panel LEDs indicate which loading segment the digital LCD current display is reporting; Bank 1 LED indicates the meter is reporting load level for outlets 1-12; Bank 2 LED indicates the meter is reporting load level for outlets 13-24; Both LEDs lighted indicates the meter is reporting load level for all outlets combined	
Switches	Press the SCROLL IP button and release to display the configured IP address in 2 digit intervals; Press the SELECT / ROTATE button and release after one second to advance the local display power power consumption for the 3 reported segments: Bank 1, Bank 2 and Banks 1+2; Press the SELECT / ROTATE button and release after two seconds to rotate the display 180 degrees	
SURGE / NOISE SUPPRESSION		
Automatic Shut-Off	No	





PHYSICAL		
Material of Construction	Metal	
Form Factors Supported	0U vertical rackmount installation supported with included mounting brackets; supports tooless mounting in button- mount compatible racks	
PDU Form Factor	Vertical (0U)	
Shipping Dimensions (hwd / in.)	5.00 x 6.30 x 73.20	
Shipping Dimensions (hwd / cm)	12.70 x 16.00 x 185.93	
Shipping Weight (lbs.)	14.60	
Shipping Weight (kg)	6.62	
Unit Dimensions (hwd / in.)	70.000 x 2.190 x 2.650	
Unit Dimensions (hwd / cm)	177.8 x 5.6 x 6.7	
Unit Weight (Ibs.)	11.5	
Unit Weight (kg)	5.22	
ENVIRONMENTAL		
Operating Temperature Range	0C ~ 40C (32F ~ 104F)	
Storage Temperature Range	5 to 122F (-15 to 50C)	
Relative Humidity	5-95% non-condensing	
Operating Elevation	0-10,000	
COMMUNICATIONS		
PowerAlert Software	LX Platform Interface: PowerAlert Device Manager	
Communications Cable	RJ45-to-DB9 configuration/console Access cable	
SNMP Compatibility	Pre-installed SNMPWEBCARD provides remote monitoring via PowerAlert Console Launcher, Telnet, SSH, and SNMP management systems	
Network Compatibility	10 Mbps; 100 Mbps (Fast Ethernet)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	2-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.