



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PM6SN1

**900-Joule Commercial-Grade Surge Suppressor with illuminated On/Off switch, diagnostic LEDs, and a heavy-duty metal housing**



### Highlights

- 6 outlets/6 ft. cord
- 900 joule rating

### Description

The Waber-by-Tripp Lite PM6SN1 Power Strip offers a convenient method of power distribution and surge suppression in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles, 6 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built in surge suppression rated at 900 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15 amp resettable circuit breaker and attractive beige housing with black output receptacles and power cord. Lifetime warranty.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip with surge suppression

SUPPRESSION - 900 joules AC suppression

#### Applications

- Offers multiple outlet power distribution and surge suppression in workbench, wallmount or floor mount applications. Ideal protection for home appliances, entertainment centers, industrial equipment and other electronic loads.

#### Package Includes

- PM6SN1 Power Strip
- Warranty information
- Instruction manual

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs support permanent installation on a wide variety of surfaces

- UL1449 3rd Edition (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6 foot AC line cord
- Lifetime warranty

## Specifications

<b>OVERVIEW</b>	
<b>Intended Application</b>	Industrial/Factory Floor
<b>OUTPUT</b>	
<b>Frequency compatibility</b>	50 / 60 Hz
<b>Output watts</b>	1800
<b>Circuit Breaker (amps)</b>	15
<b>Outlet quantity / type</b>	6 NEMA 5-15R
<b>INPUT</b>	
<b>Recommended Electrical Service</b>	120V (110-125V)
<b>Input connection type</b>	NEMA 5-15P input plug
<b>Input cord length (ft.)</b>	6
<b>Input cord length (m)</b>	1.8
<b>Input cord gauge, type</b>	14 gauge, SJT
<b>Voltage compatibility (VAC)</b>	120
<b>Maximum Surge Amps</b>	45000
<b>LEDS ALARMS &amp; SWITCHES</b>	
<b>Switches</b>	Combination AC circuit breaker and lighted two position power switch controls power to all outlets
<b>Diagnostic LEDs</b>	Protection present (green)
<b>SURGE / NOISE SUPPRESSION</b>	
<b>AC suppression joule rating</b>	900
<b>Protection modes</b>	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
<b>UL1499 let through rating</b>	400V - UL Verified
<b>EMI / RFI filtering</b>	Up to 20dB
<b>Immunity</b>	Conforms to IEE 587 / ANSI C62.41
<b>DATALINE SURGE SUPPRESSION</b>	
<b>Telephone/DSL Protection</b>	No
<b>Cable (Coax) Protection</b>	No
<b>Network (Ethernet) Protection</b>	No
<b>PHYSICAL</b>	
<b>Shipping weight (lbs)</b>	1.5
<b>Shipping weight (kg)</b>	0.7

<b>Unit Dimensions (HWD/in)</b>	12.5 x 2.5 x 1.5
<b>Unit Dimensions (HWD/cm)</b>	31.75 x 6.35 x 3.8
<b>Unit weight (lbs)</b>	1.25
<b>Unit weight (kg)</b>	0.6
<b>Material of construction</b>	Metal
<b>Integrated keyhole mounting tabs</b>	Keyhole mounting tabs enable wall mounting
<b>Receptacle Color</b>	Black
<b>AC line cord color</b>	Black
<b>Style</b>	Strip
<b>Outlets center to center measurement</b>	38.89mm
<b>Keyhole slot center to center measurement</b>	165mm
<b>CERTIFICATIONS</b>	
<b>UL1449 3rd Edition (AC Suppression)</b>	UL1449 3rd Edition
<b>UL1363 (Power Tap)</b>	UL1363
<b>cUL / CSA (Canada)</b>	cUL
<b>WARRANTY</b>	
<b>Product Warranty Period (U.S., Canada &amp; Puerto Rico)</b>	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=1970](http://www.tripplite.com/en/products/model.cfm?txtModelID=1970).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.