


8-Outlet Vertical Power Strip, 6 ft. (1.83 m) Cord, 5-15P, 48 in.

MODEL NUMBER: **PS480806**



The PS480806 power strip provides horizontal or vertical power distribution for rackmount, raceway and workbench applications in a convenient 48-in. mountable housing.

Features

Multi-Outlet Power Distribution

Vertical or Horizontal Moun

Premium Safety Features

Heavy-Duty Housing

Highlights

- Ideal for applications needing multiple convenience outlets for powering a variety of electronic equipment
- 48-in. mountable housing with 8 standard NEMA 5-15R outlets and a 6-ft. power cord
- Lighted, covered On/Off switch and 15-amp circuit breaker
- Sturdy construction and heavy-duty, all-metal housing

Package Includes

- PS480806
- Mounting hardware
- Instruction manual

Specifications

OVERVIEW	
UPC Code	037332186645
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No



Powering Business Worldwide



Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(8) Yes
Right-Angle Outlets	No
Outlet Spacing	5.67
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Included Mounting Accessories	Includes mounting clips
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	5.67 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.60 x 4.10 x 51.50
Shipping Dimensions (hwd / cm)	6.60 x 10.41 x 130.81
Shipping Weight (lbs.)	3.40
Shipping Weight (kg)	1.54
Unit Dimensions (hwd / in.)	1.250 x 1.500 x 48.000
Unit Dimensions (hwd / cm)	3.18 x 3.81 x 121.92
Unit Weight (lbs.)	2.56
Unit Weight (kg)	1.16
Outlet Spacing	5.67 in.
FEATURES & SPECIFICATIONS	
Antimicrobial	No



Powering Business Worldwide



Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.