



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PV1250FC

### PowerVerter Plus Inverter - Industrial-Strength Power for Heavy-Duty Applications

#### Highlights



- 12V DC input; 120V AC output; 2 outlet
- 1250 watts continuous output
- Peak surge output: OverPower (up to 1 hour) - 1875 watts, Double-Boost (up to 10 seconds) - 2500 watts
- High efficiency power conversion
- Automatic overload protection

#### Description

Utilize your vehicle's battery to efficiently power work site power tools, pumps, as well as your laptop computer. Continuously supplies 1250 watts of 120VAC power to (2) AC outlets from any 12VDC battery source. Frequency control locks AC output at 60Hz for operating stability of motor loads and other inductive loads with high current startup requirements.

#### Applications

- Ideal for power tools, pumps, fans, desktop computer systems, laptops, portable electronics, battery chargers for cell phones and games, full size TV/DVD & stereo systems, camcorders, lighting and other AC applications under 1250 watts continuous/2500 watts peak.

#### Package Includes

- PV1250FC inverter
- Instruction manual

#### Features

- Allows users to run large, motorized AC appliances from any 12V battery or automotive DC system
- Converts 12V DC battery power to 120V AC power
- 1,250 watts continuous output power
- Peak output power: OverPower (up to 1 hour) - 1875 watts, Double-Boost (up to 10 seconds) - 2500 watts
- 2 outlets; DC input terminals for 12V battery connection
- Frequency control for operating stability
- High-efficiency operation conserves batteries to prolong run time
- Diagnostic LEDs indicate load level (high, medium, and low) and battery charge (high, medium, and low)
- DC fusing protects inverter against overload
- RJ45 port allows connection of APS/PowerVerter Remote Switch ([APSRM4](#))
- Automatic overload shutdown
- Ignition interlock jack

## Specifications

<b>SYSTEM OVERVIEW</b>	
Voltage compatibility (VDC)	12
<b>OUTPUT</b>	
Frequency compatibility	60 Hz
Output watts	1250
Continuous output capacity (watts)	1250
Peak output capacity (watts)	2500
Output nominal voltage	120V
Output voltage regulation	Maintains PWM sine wave output voltage of 120 V AC (+/-5%)
Output frequency regulation	60 Hz (+/- 0.3 Hz)
Overload protection	Circuit breaker
Outlet quantity / type	2 AC outlets
<b>INPUT</b>	
Recommended Electrical Service	Requires 12V DC input source capable of delivering 127A for the required duration (when used at full capacity). For automotive applications, professional hardwire installation with 200A battery system fusing is recommended.
Maximum input amps / watts	Full continuous load - 127A at 12V DC, No load - 2.2A at 12V DC
Input connection type	Set of 2 DC input terminals
Input cord length details	User supplies cabling. 4 gauge or larger recommended.
<b>BATTERY</b>	
DC system voltage (VDC)	12
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	3 position on/off/remote switch enables simple on/off power control plus "remote" setting that enables distant on/off control of the inverter system when used in conjunction with optional APRM4 remote
Front panel LEDs	Set of 6 LEDs offer continuous status information on load percentage (6 levels reported) and battery charge level (7 levels reported). See manual for sequences.
<b>PHYSICAL</b>	
Shipping weight (lbs)	24.8
Shipping weight (kg)	11.2
Cooling method	Fan
Unit Dimensions (HWD/in)	7 x 8.75 x 9

<b>Unit Dimensions (HWD/cm)</b>	17.78 x 22.23 x 22.86
<b>Shipping Dimensions (HWD/in)</b>	12.5 x 11 x 10.75
<b>Shipping Dimensions (HWD/cm)</b>	31.75 x 27.94 x 27.31
<b>Unit weight (lbs)</b>	23.2
<b>Unit weight (kg)</b>	10.5
<b>Material of construction</b>	Polycarbonate
<b>Style</b>	Heavy-duty
<b>Form factors supported</b>	Mounting slots enable permanent placement of inverter on any horizontal surface (see manual for additional mounting information)
<b>ENVIRONMENTAL</b>	
<b>Relative Humidity</b>	0-95% non-condensing
<b>SPECIAL FEATURES</b>	
<b>Appearance</b>	Black color
<b>Remote control capability</b>	Yes
<b>WARRANTY</b>	
<b>Product Warranty Period (U.S., Canada &amp; Puerto Rico)</b>	1 year (Outside the U.S. and Canada, call for warranty information)

## Related Items

### Optional Products

Product Type	Related Model	Description	Qty.
Inverter Accessories	APSRM4	Remote Control Module - for Tripp Lite Inverters and Inverter/Chargers	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3056](http://www.tripplite.com/en/products/model.cfm?txtModelID=3056).