

Smart Pro line interactive UPS System - NAFTA assembled version of SMART2200NET

MODEL NUMBER: **SM2200NAFTA**



Description

Tripp Lite's SM2200NAFTA intelligent, line interactive large tower UPS system protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 27 minutes half load runtime and 11 minutes fully loaded. Runtime is expandable with optional BP24V28-2U (limit 1) and BP24V70-3U external battery packs. 2200VA/1700 watt power handling capability supports a variety of networking, telecom and other sensitive electronic applications. Includes 6 protected outlets. Supports remote monitoring of UPS and site power conditions via built-in RS-232 enabled monitoring port, plus standard UPS monitoring via 2 built in contact closure ports. Includes PowerAlert UPS monitoring and unattended shutdown software with complete cabling. Built-in audible alarm and front panel LEDs indicate line power, battery power, battery charge level, load level, plus voltage regulation status. Network grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges. Attractive large gray tower housing. \$250,000 connected equipment insur.

Features

- SM2200NAFTA line interactive UPS offers battery derived AC output during power outages, voltage regulation during brownouts and overvoltages, plus network-grade AC surge suppression
- 2200VA/1700 watt power handling capability supports a variety of networking, telecom and other sensitive electronic devices
- Large internal batteries offer runtimes of 27 minutes at half load (1100VA/850 watts) and 11 minutes at full load (2200VA/1700 watts)
- Runtime is further expandable with optional external BP24V28-2U (limit 1) and BP24V70-3U (multi-pack compatible) battery packs
- Automatic Voltage Regulation (AVR) circuits maintain 120V nominal output over an input voltage range of 87-140V
- Includes 6 fully protected NEMA 5-15R outlets with 2 single outlet load banks that can be individually powered off and back on again via software interface
- PowerAlert UPS monitoring and unattended shutdown software enables configurable network broadcast messaging, email notification, event logging and running user defined script commands
- Offers simultaneous monitoring of up to 3 directly connected devices through included DB9 contact closure and RS-232 enabled interfaces, or the monitoring of any number of additional servers over IP with included PowerAlert monitoring software
- In addition to the contact closure monitoring of on battery, low battery and power restored messaging, built-in RS-232 interface supports messaging of UPS and line power status, including AC line voltage, DC battery voltage and remaining battery capacity

Highlights

- 2200VA / 2.2kVA line interactive, extended-run tower UPS
- Maintains 120V nominal output over an input range of 87 to 140V
- Network communications supported via 3 DB9 ports (1 serial / 2 contact closure)
- Input: NEMA 5-15P (120V 15A) / Output: 6 NEMA 5-15R (120V)
- \$250,000 Ultimate Lifetime Insurance (USA, Puerto Rico and Canada only)

Package Includes

- SM2200NAFTA UPS System
- PowerAlert Software and three 6 foot network cables
- Warranty information
- Instruction manual



Powering Business Worldwide



- Supports activate self-test and UPS output power control for delayed or immediate reboot of connected equipment
- Diagnostic LEDs (indicate 17 performance conditions)
- UL (USA), cUL (Canada), NOM (Mexico), FCC Class A (Business) Listed
- \$250,000 Ultimate Lifetime Insurance (USA & Canada Only)

Specifications

OVERVIEW	
UPC Code	037332137807
INPUT	
Rated input current (Maximum Load)	15A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	20A
UPS Input Cord Length (ft.)	8
UPS Input Cord Length (m)	2.4
Recommended Electrical Service	20A 120V
OUTPUT	
Output Capacity (VA)	2200
Output Capacity (kVA)	2.2
Output Capacity (Watts)	1700
Output Capacity (kW)	1.7
Power Factor	0.8
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-13% / +5%
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Two switchable single outlet 5-15R load banks
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(6) 5-15R
BATTERY	



Powering Business Worldwide



UPS Power Module Dimensions (hwd, cm)	43.18 x 22.86 x 31.75
UPS Power Module Dimensions (hwd, in.)	17 x 9 x 12.5
UPS Power Module Weight (kg)	36.29
UPS Power Module Weight (lbs.)	80
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	58.4
AC Mode Efficiency Rating (100% Load)	99%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	863.7
COMMUNICATIONS	
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; contact closure communications via two additional DB9 ports (3 total)
PowerAlert Software	Included
Communications Cable	3 DB9 cables included
Communications Interface	DB9 Serial; Contact closure
LINE / BATTERY TRANSFER	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	87
High Voltage Transfer to Battery Power (Setpoint)	140
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.