



6-Outlet Commercial-Grade Surge Protector, 6 ft. (1.83 m) Cord, 900 Joules, 12.5-in. length

MODEL NUMBER: PM6SN1











Highlights

- 6 outlets/6-ft. (1.83 m) cord
- 900 joule rating

Package Includes

- PM6SN1 Power Strip
- · Warranty information
- Instruction manual

Description

The PM6SN1 Power Strip offers a convenient method of power distribution and surge suppression in workbench, wall-mount or floor-mount applications. Includes six NEMA 5-15R outlets, six-foot (1.8-meter) AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 900 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features metal housing, lighted power switch with integrated 15A resettable circuit breaker and attractive beige housing with black output receptacles and power cord.

Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles
- Lighted combination power switch with integrated circuit breaker
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1449 3rd Edition (USA/400V rating), UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity
- 6-ft. (1.83 m) AC line cord
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
 equipment damage and indicating replacement is required

Specifications

OVERVIEW		
UPC Code	037332101013	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	





Recommended Electrical Service	120V (110-125V)	
Input Cord Gauge Type	14 gauge; SJT	
Input Cord Gauge (AWG)	14	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	45000	
Input Plug Type	NEMA 5-15P	
Input Cord Details	TLS	
Input Cord Length (ft.)	6	
Right-Angle Plug	No	
Input Cord Length (m)	1.83	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CONTROLS		
Diagnostic LED(s)	Yes	
Switches	Combination AC circuit breaker and lighted two position power switch controls power to all outlets	
Diagnostic LED Details	Protection present (green)	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	900	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
UL1449 Let Through Rating	400V - UL Verified	
EMI / RFI Filtering	Up to 20 dB	
Immunity	Conforms to IEE 587 / ANSI C62.41	
Automatic Shut-Off	Yes	
Tationian original		
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		





Material of Construction	Metal	
Power Cord Color	Black	
Housing Color	Beige	
Mounting Holes or Slots	Yes	
Slot or Hole Mount Measurement (Center to Center)	165 mm	
Outlets Measurement (Center to Center)	38.89mm	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	2.25 x 15.00 x 6.00	
Shipping Dimensions (hwd / cm)	5.72 x 38.10 x 15.24	
Shipping Weight (lbs.)	1.77	
Shipping Weight (kg)	0.80	
Unit Dimensions (hwd / in.)	1.500 x 12.750 x 2.500	
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8	
Unit Weight (lbs.)	1.25	
Unit Weight (kg)	0.57	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1449; UL 1363; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.