



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SMART3000CRMXL

SmartPro Compact Rackmount UPS System - Precision Protection for Network / Telecom Wiring Closets and Reduced Depth Installations

Highlights



- 3000VA / 3kVA line interactive 4U rack / tower UPS with reduced mounting depth and high power factor 2880w (with plug) or 3600W (hardwire) capacity
- Maintains sine-wave 120V nominal output over an input range of 83 to 145V
- Network communications supported via USB port, serial port, SNMP/Web card slot and EPO interface
- Expandable runtime with optional external battery packs
- Input: NEMA L5-30P or hardwire (120V 30A) / Output: 8 NEMA 5-15/20R, 1 L5-30R (120V)
- 2 year product warranty / \$250,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lites SmartPro Compact Rackmount Uninterruptible Power Supply (UPS) offers line interactive voltage regulation, network grade surge suppression and long lasting battery support for critical network hardware during blackouts and extended power failures. Special reduced-depth housing, larger internal batteries, higher rated wattage and included 2 post rackmount installation hardware makes these systems ideal for network and telecom wiring closets and other limited-space installations. Runtime is expandable with optional BP48V48RT4U and BP48V24-2U reduced-depth external battery packs.

SMART3000CRMXL 4U rackmount 3000VA UPS offers battery-derived sine wave AC output during power failures and extreme voltage variations. Supports 3000VA/2880 watts when powered via included L5-30P input plug. Supports up to 3600VA/3600 watts when hardwired to a 120V 30A input source. Line interactive Automatic Voltage Regulation (AVR) provides two levels of voltage boost during brownouts and one level of voltage cut during overvoltage conditions to maintain regulated 120V nominal output over an input range of 83-145V. Includes NEMA L5-30P input plug (or hardwire input), L5-30R and 5-15/20R output receptacles. Optional SNMPWEBCARD offers remote management and control of the UPS via direct network connection. Additional ENVIROSENSE accessory, when used in conjunction with SNMPWEBCARD reports temperature, humidity and status of up to two directly connected contact closure sensors. HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once. Includes PowerAlert monitoring software with USB and serial cables. Emergency Power Off (EPO) interface. Integrated 3-bank programmable PDU switching supports load shedding and remote-reboot of up to 3 individual connected devices. 3-stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation LEDs. Audible alarm. Self-test. 2-post rackmount accessories included; 2-9U STAND tower stands and 4POSTRAILKIT 4 post rackmount kit available. Field-replaceable, hot-swappable internal batteries and external battery packs. Attractive all-black color scheme. 2-year warranty and \$250,000 [connected equipment insurance](#); extended warranty and service contracts available.

Applications

Special reduced-depth housing, larger internal batteries, higher rated wattage and included 2 post rackmount installation hardware makes these systems ideal for network and telecom wiring closets and other limited-space installations

Package Includes

- SmartPro Compact 4U Rackmount UPS system
- 2 post rackmount installation brackets
- USB and Serial Cabling
- Owner's manual with warranty information

Features

- Tripp Lite's SmartPro Compact Rackmount Uninterruptible Power Supply (UPS) offers line interactive voltage regulation, network grade surge suppression and long lasting battery support for critical network hardware during blackouts and extended power failures
- Special reduced-depth housing, larger internal batteries, higher rated wattage and included 2 post rackmount installation hardware makes these systems ideal for network and telecom wiring closets and other limited-space installations
- Runtime is expandable with optional BP48V48RT4U and BP48V24-2U reduced-depth external battery packs
- SMART3000CRMXL 4U rackmount 3000VA/2880 watt UPS offers battery-derived sine wave AC output during power failures and extreme voltage variations
- Supports loading up to 3600 watts when hardwired
- Line interactive Automatic Voltage Regulation (AVR) provides two levels of voltage boost during brownouts and one level of voltage cut during overvoltage conditions to maintain regulated 120V nominal output over an input range of 83-145V
- Includes NEMA L5-30P input plug (hardwire line cord installation supported), L5-30R and 5-15/20R output receptacles
- Network management interfaces support simultaneous communications via USB port, DB9 serial port and optional SNMP/Web management accessory card slot
- Optional SNMPWEBCARD offers remote management and control of the UPS via direct network connection
- Additional ENVIROSENSE accessory, when used in conjunction with SNMPWEBCARD reports temperature, humidity and status of up to two directly connected contact closure sensors
- HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X
- 97% efficiency in line power mode offers substantially lower operating costs than lower efficiency UPS types
- Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once
- Includes PowerAlert monitoring software with USB and serial cables
- Emergency Power Off (EPO) interface
- Integrated 3-bank programmable PDU switching supports load shedding and remote-reboot of up to 3 individual connected devices
- 3-stage metered current monitoring and battery charge status LEDs; Utility power and voltage regulation LEDs; Audible alarm; Self-test
- 2-post rackmount accessories included; 2-9U STAND tower stands and 4POSTRAILKIT 4 post rackmount kit available
- Field-replaceable, hot-swappable internal batteries and external battery packs
- Attractive all-black color scheme
- 2-year warranty and \$250,000 [connected equipment insurance](#); extended warranty and service contracts available

Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120 volts
OUTPUT	
Output Volt Amp Capacity (VA)	3000
Output Watt Capacity (watts)	2880
Output Capacity Details	Supports 3600 watts max with hardwire input
Nominal Output Voltage(s) Supported	120v
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	-18%, +8%

Built-in UPS output receptacles	8 5-15/20R outlet(s); 1 L5-30R outlet(s)
Built-in controllable switched load banks	Three switchable single-outlet 5-15/20R load banks
Output circuit breaker	20A (x2) - each 20A breaker protects 4 5-15/20R outlets / 30A breaker protects L5-30R
INPUT	
Rated input current (at maximum load)	24A (L5-30P input), 30A (hardwire)
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	L5-30P; Hardwire
UPS Input cord length (ft.)	10 ft.
Recommended Electrical Service	120V 30A
BATTERY	
Full load runtime (minutes)	7.5 min. (2880w)
Half load runtime (minutes)	19 min. (1440w)
External battery pack compatibility	BP48V24-2U (limit 1); BP48V48RT4U (multi-pack compatible)
DC system voltage	48VDC
Battery recharge rate (included batteries)	Less than 7.2 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC54 (quantity 2)
Battery Access	Battery access door allows hot swap battery replacement without powering connected equipment off
VOLTAGE REGULATION	
Voltage regulation description	Automatic Voltage Regulation (AVR) circuits maintain clean, regulated computer-grade 120V nominal output, without using battery power, during brownouts to 83V and overvoltages to 145V
Overvoltage correction	Input voltages between 127 and 145V AC are reduced by 12%
Undervoltage correction	Input voltages between 96 and 108 are boosted by 12%
Severe undervoltage correction	Input voltages between 83 and 95 are boosted by 24%
LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Alarms	3 function audible alarm indicates power failure conditions (4 short beeps every 10 seconds), overload (continuous short beeps) and low battery (continuous tone)
Switches	Yes, includes 2 front panel mounted push-button switches for system enable, self-test and alarm cancel functions. Back panel includes battery charge level switch for internal or external battery configurations
SURGE / NOISE SUPPRESSION	

UPS AC suppression joule rating	570 joules
EMI / RFI AC noise suppression	Yes
AC suppression response time	Instantaneous
PHYSICAL	
Installation form factors supported with included accessories	2 post 19 inch rackmount (mounting rail kit included)
Installation form factors supported with optional accessories	4 post rackmount (4POSTRAILKIT); Tower (2-9USTAND)
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	7 x 17.3 x 16.8
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	17.8 x 43.9 x 42.7
Installed whole system total rack space height (rack spaces)	4U
UPS / Power Module weight (lbs)	102
UPS / Power Module weight (kg)	46.3
UPS Shipping dimensions (height x width x depth / inches)	13.2 x 23.6 x 22.8
UPS Shipping dimensions (height x width x depth / cm)	33.5 x 59.9 x 57.9
Shipping weight (lbs)	124
Shipping weight (kg)	56.3
UPS housing material	Steel
Cooling method	Fan
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0-95%, non-condensing
AC mode BTU / hr. (full load)	408
Battery mode BTU / hr. (full load)	2149.5
COMMUNICATIONS	

Communications interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
WatchDog compatibility	Yes, compatible with Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application / OS or hard power off/on reboot of connected equipment ideal for unattended kiosk applications
EPO port	Includes RJ11 EPO (emergency power off) port and interconnection cable
SNMP compatibility	Yes, includes slot for optional SNMPWEBCARD accessory (#SNMPWEBCARD)
Software and cabling included	Yes, includes PowerAlert software CD-ROM and complete cabling
LINE / BATTERY TRANSFER	
Transfer time	5 ms. (typical)
Low voltage transfer to battery power (setpoint)	83
High voltage transfer to battery power (setpoint)	145
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
Appearance	Attractive black rackmount housing, optional use 2U black front bezel included to enable black color appearance
CERTIFICATIONS	
Certifications	Tested to UL1778 (USA), CSA (Canada), NOM (Mexico), Class A (Emissions)
WARRANTY	
Standard warranty period	2 year product warranty
Connected equipment insurance (USA, Canada, Puerto Rico)	2-year warranty and \$250,000 connected equipment insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Tower Stands	2-9USTAND	Tower Stand - Expandable Tower Base Stand UPS Accessory	-
Rackmount/Wallmount Kits	4POSTRAILKIT	Supports UPS systems in 4-post rackmount applications.	-
External Battery Packs	BP48V24-2U	BP48V242U - External Battery Pack for UPS System - LIMIT 1	-
External Battery Packs	BP48V48RT4U	Shallow-Depth External Battery Pack For UPS Systems	-
SNMP Accessories	ENVIROSENSE	Power Management Tools - Environmental Sensor	-
Power Distribution	PDU2430	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	-
Power Distribution	PDUMH30NET	Switched, Metered PDU with Remote Monitoring - 2U Rackmount Power Distribution Unit for Networks with Individually Switchable Outlets, Current Metering, Remote Monitoring and Control	-
Power Distribution	PDUMV30	Metered 0U Vertical Rack PDU - Metered Power Distribution Unit for Network Applications	-

Power Distribution	PDUMV30NET	Switched, Metered PDU with Remote Monitoring - 0U Vertical Rackmount Power Distribution Unit for Networks with Individually Switchable Outlets, Current Metering, Remote Monitoring and Control	-
SNMP Accessories	SNMPWEBCARD	Power Management Tools - Internal SNMP/Web Card	-
Start-Up/Warranty Services	WEXT3-2200-3000	3-Year Extended Warranty - 1-year extension of standard 2-year warranty	-
Start-Up/Warranty Services	WEXT5-2200-3000	5-Year Extended Warranty - 3-year extension of standard 2-year warranty	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3824.