



Powering Business Worldwide

# SCSI/Fibre Channel - 10-ft. SCSI Cable HD50M to HD50M Double Shielded

MODEL NUMBER: **S366-010**



### Highlights

- Premium double-shielded cable
- 25 twisted-pair conductors

### System Requirements

- Any external SCSI II device or controller card requiring HD50 interface

### Package Includes

- 10-ft. SCSI cable HD50M to HD50M double shielded

### Description

Multi-platform SCSI II external peripheral cable HD50M/M. This 10ft cable is designed to connect two SCSI II (fast SCSI) devices together. Manufactured using double shielded 25 twisted pair high impedance cable. Constructed with low-capacitance, impedance matched, 28 AWG, stranded, tinned copper cable with insulated in polypropylene. Tripp Lite warrants this product to be free from defects in materials and workmanship for life.

### Features

- Backwards compatibility with previous SCSI generations
- Double shielded (foil and braid)
- 25 twisted pair conductors
- Low-capacitance impedance matched 28 AWG stranded tinned copper insulated in polypropylene
- All Tripp Lite SCSI products, regardless of the SCSI generation, meet the latest specifications of ANSI
- Tripp Lite offers a complete line of internal and external solutions for SCSI/RAID and fibre channel ranging from the very latest Ultra 320 to legacy SCSI-1 and every combination in between
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

## Specifications

OVERVIEW	
UPC Code	037332014092
CONNECTIONS	
Side A - Connector 1	HD50 (MALE)
Side B - Connector 1	HD50 (MALE)
PHYSICAL	



Powering Business Worldwide

Color	Beige
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.50 x 10.00 x 1.25
Shipping Dimensions (hwd / cm)	31.75 x 25.40 x 3.18
Shipping Weight (lbs.)	1.13
Shipping Weight (kg)	0.51
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.