



Smart Pro Line Interactive 2U Rack/Tower Extended Run UPS - NAFTA assembled version of SMART2200RMXL2U

MODEL NUMBER: SM2200RMNAFTA





Description

2200VA line interactive UPS system for server, network and telecommunications equipment. 2U rackmount or tower form factor with an installed depth of only 19 inches. Expandable battery runtime with optional BP48V24-2U and BP48V60RT-3U external battery packs. Uninterruptible Power Supply (UPS) switches to battery-derived AC output during power failures and extreme voltage variations. Line interactive Automatic Voltage Regulation (AVR) offers two levels of voltage boost during brownouts and one level of voltage cut during overvoltages to maintain regulated 100, 110, 120v selectable output over an input range of 83-145V. Includes NEMA 5-20P input plug (with NEMA 5-15P plug option) and both NEMA 5-15R and 5-15/20R output receptacles. Network-grade AC surge and noise suppression. Network management interfaces support simultaneous communications via USB port, DB9 serial port and SNMPWEBCARD slot. HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports simultaneous detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces. Includes PowerAlert monitoring software and complete cabling. Emergency Power Off (EPO) interface. Integrated 3-bank PDU switching supports load shedding and remote-reboot of connected equipment. 3stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation LEDs. Audible alarm. Self-test. 4-post rackmount accessories included; 2-9USTAND tower kit and 2POSTRMKITWM two post rack & wallmount accessories available. Field-replaceable, hot-swappable internal batteries and external battery packs. Attractive all-black color scheme. \$250,000 connected equipment insurance;

Features

- SmartPro line interactive UPS system is ideal for voice, data, medical and industrial networking applications
- Line interactive Automatic Voltage Regulation (AVR) offers two levels of voltage boost during brownouts and one level of voltage cut during overvoltages
- Maintaints continuous operation through blackouts, voltage fluctuations and surges
- Corrects line voltage conditions as low as 83V and as high as 145 back to selectable 100/110/120V nominal values
- Standard internal battery set offers 16 minutes at half load (800w) and 6 minutes at full load (1600w)
- Optional BP48V24-2U and BP48V60RT3U external rack/tower battery packs enable extended runtime operation
- Compact rackmount form factor installs using only 2 rack spaces (2U) with a maximum installed depth
 of only 19 inches

Highlights

- 2200VA / 2.2kVA line interactive, extended-run 2U rack / tower UPS
- Maintains sine-wave 100/110/120V nominal output over an input range of 83 to 145V
- Network communications supported via HID enabled USB port, DB9 serial port, SNMP/Web card slot and EPO interface
- Current monitoring and switched PDU control via 3 individually controllable load banks
- Input: NEMA 5-20P (120V 20A / includes 5-15P plug 120V 15A) / Output: 4 NEMA 5-15/20R, 4 NEMA 5-15R (120V)
- \$250,000 Ultimate Lifetime Insurance (USA, Puerto Rico and Canada only)

Package Includes

SM2200RMNAFTA UPS system PowerAlert software CD-ROM USB, serial and EPO cabling Owner's manual with warranty information





- Ships with all mounting accessories for 4 post rackmount installation
- Optional 2POSTRMKITWM enables 2 post rackmount or wallmount installation
- Optional 2-9USTAND accessory enables small-footprint upright tower placement
- Network interfaces support simultaneous communications via built-in USB, DB9 serial and SNMPWEBCARD slot
- HID compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Included PowerAlert UPS monitoring software supports safe unattended shutdown, monitoring and control via local connected servers, with the built-in ability to shutdown any number of additional servers over IP
- UPS interface supports on-battery, low-battery, power-restored, AC-voltage, DC-voltage, output current
 monitoring, battery charge current, battery capacity, AC line frequency, timed inverter sutoff, activate
 self-test, load bank output power control and remote reboot
- Built-in Emergency Power Off (EPO) interface with cable
- NEMA 5-20P input plug (user-installable NEMA 5-15P replacement plug included) / NEMA 5-15R & NEMA 5-15/20R output receptacles
- Integrated 3 bank switched PDU enables remote outlet management for load shedding or remote reboot
 of individual load banks (Each bank controls 1 outlet per load bank)
- Front panel LEDs offer current monitoring and battery charge level information
- UPS ships fully assembled in full compliance with DOT regulations, no time consuming connection of internal batteries by user required
- \$250,000 ULtimate Lifetime Insurance

Specifications

OVERVIEW			
UPC Code	037332137814		
INPUT			
Rated input current (Maximum Load)	13.3A (120V), 14.6A (110V), 16.0A (100V)		
Nominal Input Voltage(s) Supported	120V AC		
UPS Input Connection Type	5-20P		
Input Circuit Breakers	20A		
UPS Input Cord Length (ft.)	10		
UPS Input Cord Length (m)	3.1		
Recommended Electrical Service	20A 120V		
ОИТРИТ			
Output Capacity (VA)	2200		
Output Capacity (kVA)	2.2		
Output Capacity (Watts)	1600		
Output Capacity (kW)	1.6		
Power Factor	0.7		
Nominal Voltage Details	120V default (voltage selection via back panel dipswitches)		





	T 1	
Frequency Compatibility	50 / 60 Hz	
Output Voltage Regulation (Line Mode)	-14%, +6%	
Output Voltage Regulation (Battery Mode)	+/- 5%	
Load Management Receptacles	Three switchable single-outlet 5-15R load banks	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	Pure Sine wave	
Nominal Output Voltage(s) Supported	100V; 110V; 120V	
Output Receptacles	(4) 5-15R; (4) 5-15/20R	
BATTERY		
Runtime Full Load (min.)	6 min. (1600w)	
Runtime Half Load (min.)	16 min. (800w)	
Expandable Runtime	Yes	
External Battery Pack Compatibility	BP48V24-2U (limit 1); BP48V60RT-3U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V60RT-3U">BP48V60RT-3U-Rack-Tower-Battery-Pack-Enclosure-DC-Cabling-select-UPS-Systems~BP48V60RT-3U">BP48V60RT-3U"<bpartage and="" and<="" td=""></bpartage>	
DC System Voltage (VDC)	48	
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%	
Battery Access	Front panel battery access door	
Internal UPS Replacement Battery Cartridge	RBC94-2U	
Battery Replacement Description	Hot-swappable, user replaceable batteries	
VOLTAGE REGULATION		
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 79 to overvoltages to 147	
Overvoltage Correction	Voltage reduction of 12% applies when input is between 127 and 145 (120V), 116 and 133 (110V), 106 and 121 (100V)	
Undervoltage Correction	Voltage boost of 12% applies when input voltage is between 96 and 108 (120V), 87 and 99 (110V), 83 and 90 (100V)	
Severe Undervoltage Correction	Voltage boost of 24% applies when input voltage is between 83 and 95 (120V only)	
USER INTERFACE, ALERTS & CONTROLS		
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; rear panel protected switches support nominal voltage selection	
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status	
Audible Alarm	Audible alarm indicates power-failure, overload and low-battery conditions	





LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status		
SURGE / NOISE SUPPRESSION			
UPS AC Suppression Joule Rating	570		
UPS AC Suppression Response Time	Instantaneous		
EMI / RFI AC Noise Suppression	Yes		
PHYSICAL			
Primary Form Factor	Rackmount		
Rack Height	2U		
Cooling Method	Fan		
Included Mounting Accessory Description	Adjustable mounting rail kit included		
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND">2-9USTAND)		
Primary UPS Depth (mm)	483		
Primary UPS Height (mm)	89		
Primary UPS Width (mm)	445		
Shipping Dimensions (hwd / in.)	9.00 x 23.50 x 20.00		
Shipping Dimensions (hwd / cm)	22.86 x 59.69 x 50.80		
Shipping Weight (lbs.)	72.00		
Shipping Weight (kg)	32.66		
UPS Housing Material	Steel		
UPS Power Module Dimensions (hwd, cm)	8.89 x 44.45 x 48.26		
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.5 x 19		
UPS Power Module Weight (kg)	29.03		
UPS Power Module Weight (lbs.)	64		
ENVIRONMENTAL			
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius		
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius		
Relative Humidity	0 to 95%, non-condensing		
AC Mode BTU / Hr. (Full Load)	168.2		
AC Mode Efficiency Rating (100% Load)	97%		





Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	604.4		
COMMUNICATIONS			
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions		
PowerAlert Software	Included		
Communications Cable	USB and DB9 cabling included		
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications		
Communications Interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface		
LINE / BATTERY TRANSFER			
Transfer Time	2-4 milliseconds		
Low Voltage Transfer to Battery Power (Setpoint)	83 (120V), 87 (110V), 83 (100V)		
High Voltage Transfer to Battery Power (Setpoint)	145 (120V), 133 (110V), 121 (100V)		
FEATURES & SPECIFICATIONS			
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported		
High Availability UPS Features	Hot swappable batteries		
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks		
Grounding Details	Back panel grounding lug		
WARRANTY & SUPPORT			
Product Warranty Period (Worldwide)	2-year limited warranty		
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.