

# TAA SmartPro 120V 2.2kVA 1.92kW Line-Interactive Sine Wave UPS, 2U, Extended Run, Network Card Options, LCD, USB, DB9

MODEL NUMBER: SM2200RMLX2UTAA



## Description

The SM2200RMLX2UTAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. SmartPro® Line-Interactive UPS with enhanced LCD interface offers network-grade power protection for critical server, network and telecommunications equipment. Line-Interactive Uninterruptible Power Supply (UPS) with built-in Auto-Voltage Regulation (AVR) actively corrects brownouts and overvoltages back to usable levels while maintaining a full battery charge in case of power failure. This unique configuration excels in exceptionally poor power environments with two separate levels of voltage boost to correct both slight undervoltages and severe brownout conditions. Interactive LCD interface reports UPS operating mode, detailed UPS and site-power data, plus enables a variety of UPS setup and configuration options. Super-fast switchover from line to battery power occurs within milliseconds to maintain operation of connected equipment without interruption or reboot. 96-percent line-mode efficiency offers reduced heat emissions and operating costs. Communications interfaces support communications via USB, DB9 serial and a slot for an optional network management card. HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and macOS. Network communications ports enable detailed monitoring of equipment load levels, self-test data and utility power conditions. PowerAlert® UPS monitoring and auto-shutdown software is available via free download. Switched output load banks enable scheduled and real-time remote reboot and load shedding of select outlets. Emergency Power Off (EPO) interface. LCD display panel easily rotates for viewing in rack-mount or tower configurations. Audible alarm with push-button momentary alarm-cancel and silent-mode configuration options. Programmable self-test. Field-replaceable, hot-swappable battery modules.

## Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- SMART2200RMLX2U line interactive 2U rack/tower UPS with 2200VA / 2.2kVA / 1920W capacity and extended runtime options Line interactive UPS with Automatic Voltage Regulation (AVR) corrects brownouts and overvoltages from 83 to 145V
- NEMA 5-20P input plug; 4 NEMA 5-15/20R and 4 5-15R output receptacles, Two independently switched output load banks
- Maintains uninterrupted operation of connected networking equipment during blackouts, surges, brownouts and overvoltages
- High 96% efficiency rating in line-power mode offers reduced power consumption and BTU emissions
- Internal batteries offer 12 minutes at 50% load (960W) and 4.5 minutes at 100% load (1920W)
- Extended runtime is available with optional BP48V24-2U / BP48V242UTAA (limit 1) OR BP48V60RT3U / BP48V60RT3UTAA (no limit), Output is reduced to 1600 watts maximum with external battery packs

## Highlights

- 2.2kVA / 2200VA / 1920W line interactive 2U rack/tower UPS, Sine Wave
- Extended runtime options up to 1600W, 0.9 Power Factor, Interactive LCD interface
- USB, RS232, EPO and slot for network communication card options
- 120V NEMA 5-20P input, 4 NEMA 5-15R & 4 NEMA 5-15/20R outlets
- TAA Compliant for GSA Schedule purchases
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

## Package Includes

- SM2200RMLX2UTAA TAA Compliant UPS system
- USB, Serial & EPO cabling
- 4 post installation kit
- Owner's manual



Powering Business Worldwide



- External battery configurations require the use of External Battery Configuration Software (see manual)
- Hot-swappable, user-replaceable internal batteries and external battery packs can be replaced with no disruption to connected equipment
- Following an extended power outage, the UPS will automatically restart into line-power mode, begin powering connected equipment and recharge the battery system, all without user interaction
- Front panel LCD monitoring screen with MODE and ENTER buttons reports operating mode with 5-bar battery charge graphic, plus 7 selectable screens of detailed UPS and site power information
- LCD interface also supports a number of advanced user setup and operating preferences
- Ships with 4-post rack-mount installation hardware; Optional 2POSTRMKITWM enables 2-post rack-mount/wallmount installation; Optional 2-9USTAND enables tower placement
- Communications interfaces support communications via USB, DB9 serial and slot for network management card options; Compatible with UPS management card options TLNETCARD, WEBCARDLX and SNMPWEBCARD
- HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and macOS
- USB & Serial ports enable data-saving unattended shutdown when used with PowerAlert software, available via FREE download from [tripplite.eaton.com/products/power-alert](http://tripplite.eaton.com/products/power-alert)
- Built-in Emergency Power Off (EPO) interface with cable

## Specifications

OVERVIEW	
UPC Code	037332152800
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	16A (120V)
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-20P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	20A 120V
OUTPUT	
Output Capacity (VA)	2200
Output Capacity (kVA)	2.2
Output Capacity (Watts)	1920
Output Capacity (kW)	1.92
Output Capacity Details	Output is reduced to 1600 watts maximum when used with external battery packs
Power Factor	0.87
Nominal Voltage Details	120v nominal output in battery mode



Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	570
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Included Mounting Accessory Description	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount ( <a href="https://tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> ); 2-4 post front rail rackmount ( <a href="https://tripplite.eaton.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT</a> ); 4 post rackmount short-depth ( <a href="https://tripplite.eaton.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM</a> ); Tower ( <a href="https://tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> ); Wallmount ( <a href="https://tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> )
Minimum Required Rack Depth (cm)	55.88
Minimum Required Rack Depth (inches)	22
Minimum Required Rack Depth with External Battery Pack (cm)	66
Minimum Required Rack Depth with External Battery Pack (in.)	26
Minimum Required Rack Depth without External Battery Pack (cm)	62
Minimum Required Rack Depth without External Battery Pack (in.)	24.5
Optional Mounting Accessory Notes	Optional <a href="https://tripplite.eaton.com/2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND">2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND</a> ; enables upright tower UPS placement; <a href="https://tripplite.eaton.com/2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM">2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM</a> ; enables wall-mount and 2-post rackmount installation; <a href="https://tripplite.eaton.com/4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM">4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM</a> ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); <a href="https://tripplite.eaton.com/Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT">Heavy-Duty-2-post-Front-Mounting-Ear-Kit~UPSHDEARKIT</a> ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support

Primary UPS Depth (mm)	490
Primary UPS Height (mm)	88
Primary UPS Width (mm)	440
Shipping Dimensions (hwd / in.)	8.80 x 24.00 x 20.90
Shipping Dimensions (hwd / cm)	22.35 x 60.96 x 53.09
Shipping Weight (lbs.)	78.00
Shipping Weight (kg)	35.38
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.79 x 43.99 x 49.00
UPS Power Module Dimensions (hwd, in.)	3.46 x 17.32 x 19.29
UPS Power Module Weight (kg)	26.13
UPS Power Module Weight (lbs.)	57.6
Unit Weight (lbs.)	57.600
Unit Weight (kg)	26.13
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	306
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	1157
Audible Noise	45 dBA maximum, front side 1m
<b>COMMUNICATIONS</b>	
Network Management Cards	&nbsp;<a class="productLink" href="//tripplite.eaton.com/Web-Management-Accessory-Card-SmartPro-SmartOnline-UPS-Systems~TLNETCARD">TLNETCARD</a>&nbsp;; &nbsp;<a class="productLink" href="//tripplite.eaton.com/Network-Card-Eaton-Tripp-Lite-Series-UPS-Systems~WEBCARDLXE">WEBCARDLXE</a>&nbsp;
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB and DB9 cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at <a href="https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite">https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite</a>
Network Management Card Description	Network management card optional
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)



Powering Business Worldwide



LINE / BATTERY TRANSFER	
Transfer Time	5 milliseconds (line to battery mode); 1 millisecond (battery to line mode)
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
Grounding Details	Back panel grounding lug
APPLICATIONS	
UPS Applications	Large Network
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 &nbsp;<a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &nbsp;

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.