

## SmartRack 8U/12U/22U Expandable Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open Frame Rack

MODEL NUMBER: SRWO8U22



Expandable open-frame rack stores 8U, 12U or 22U of 19-inch rack equipment up to 18 inches deep in locations with limited floor space where a locked enclosure is not required. Allows easy access to equipment and cabling.

### Description

The SRWO8U22 SmartRack 8U/12U/22U Expandable Flat-Pack Low-Profile Switch-Depth Wall-Mount 2-Post Open-Frame Rack stores and organizes EIA-standard 19-inch rack equipment compatible with 2-post mounting in network wiring closets, back offices and other secure IT areas with limited floor space where a locked enclosure is not required. Mounted to the wall or resting on the floor, this rack offers fast, easy access to network components and cabling.

Constructed from heavy-duty steel with a durable black powder-coated finish, the rack has a maximum load capacity of 150 lbs (68 kgs). The expandable design allows you to assemble the rack in an 8U, 12U or 22U configuration to meet your current needs, while leaving rack space in reserve for future expansion. The rack is simple to assemble and mount to the wall. Threaded 12-24 mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails accommodate equipment up to 18 inches deep, such as network switches and patch panels. Assembly and equipment-mounting hardware is included.

### Features

#### Saves Valuable Workspace

- Perfect for network wiring closets, back offices and other secure areas with limited floor space where a locked enclosure is not required
- Stores and organizes EIA-standard 19 in. rack equipment compatible with 2-post mounting
- Maximum load capacity of 150 lbs (68 kgs)

#### Expandable 2-Post Open Frame Design

- Assembles in 8U, 12U or 22U configuration to meet current needs
- Expands to add equipment later without having to buy a bigger rack
- Allows easy access for installing, configuring and servicing equipment and cabling

#### Easy Assembly and Installation

- Wall-mounting holes spaced 16 in. apart for standard wall stud placement

### Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Configures to 8U, 12U or 22U of rack space
- Allows easy access to equipment and cabling
- Stores 19 in. rack equipment up to 18 in. deep
- Simple to assemble and mount

### Package Includes

- (24) 12-24 equipment mounting screws
- (8) M6 x 12 Phillips-head screws
- (16) M5 x 10 Phillips-head screws
- (2) Short vertical mounting rails
- (2) Long vertical mounting rails
- (2) Mounting rail tie plates
- (2) Top/bottom panel frames
- (2) Support straps
- (8) Zip ties
- 3 mm hex key
- Owner's manual

- Vertical mounting rails accommodate equipment up to 18 in. deep, such as network switches and patch panels
- Rails support threaded-hole equipment mounting
- Rack spaces numbered for easy reference
- Includes assembly and equipment-mounting hardware

## Specifications

OVERVIEW	
UPC Code	037332156778
Device Compatibility	Patch Panel; Network Switch
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	22U
Rack Depth	Shallow
Maximum Device Depth (cm)	46.33
Maximum Device Depth (in.)	18.24
Maximum Device Depth (mm)	463
Maximum Weight Capacity (lbs.)	150
Maximum Weight Capacity (kg)	68
Shipping Dimensions (hwd / in.)	3.70 x 22.80 x 21.80
Shipping Dimensions (hwd / cm)	9.40 x 57.91 x 55.37
Shipping Weight (lbs.)	19.00
Shipping Weight (kg)	8.62
Unit Dimensions (hwd / in.)	42.300 x 20.110 x 18.240
Unit Dimensions (hwd / cm)	45.22 (8U), 63 (12U), 107.45 (22U) x 51.08 x 46.33
Unit Weight Details	Weight varies depending on configuration 8U = 11.21lbs, 12U = 12.23lbs, 22U = 15.03lbs
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	



Powering Business Worldwide



Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.