



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SMART1500CRMXL

SmartPro 1.5kVA Line Interactive Sine Wave UPS, 1440w, Extended-run & SNMPWEBCARD options, 2U Rack/Tower, USB, Serial, EPO, 120V

Highlights

- 1.5kVA / 1500VA / 1440W line interactive UPS, 0.96 power factor
- 120V output, Corrects brownouts and overvoltages from 83V to 145V
- 2U rack/tower compatible, Hot-swappable batteries, Sine wave output
- USB, RS232, EPO and slot for optional SNMP/WEB card
- Expandable runtime, 97% line-mode efficiency, 3 switched load banks
- NEMA 5-15P input, 8 NEMA 5-15R outlets



Description

Tripp Lite's SmartPro Compact Rackmount Uninterruptible Power Supply (UPS) offers line interactive voltage regulation, network grade surge suppression and long lasting battery support for critical network hardware during blackouts and extended power failures. Larger internal batteries and higher rated wattage makes these systems ideal for network and telecom wiring closets and other limited-space installations. Runtime is expandable with optional BP48V48RT4U and BP48V24-2U reduced-depth external battery packs. SMART1500CRMXL 2U rackmount 1500VA/1440 watt UPS offers battery-derived sine wave AC output during power failures and extreme voltage variations. Line interactive Automatic Voltage Regulation (AVR) provides two levels of voltage boost during brownouts and one level of voltage cut during overvoltage conditions to maintain regulated 120V nominal output over an input range of 83-145V. Includes NEMA 5-15P input plug and NEMA 5-15R output receptacles. Network management interfaces support simultaneous communications via USB port, DB9 serial port and optional SNMP/Web management accessory card slot. Optional SNMPWEBCARD offers remote management and control of the UPS via direct network connection. Additional ENVIROSENSE accessory, when used in conjunction with SNMPWEBCARD reports temperature, humidity and status of up to two directly connected contact closure sensors. HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X. Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once. Includes PowerAlert monitoring software with USB and serial cables. Emergency Power Off (EPO) interface. Integrated 3-bank programmable PDU switching supports load shedding and remote-reboot of up to 3 individual connected devices. 3-stage metered current monitoring and battery charge status LEDs. Utility power and voltage regulation LEDs. Audible alarm. Self-test. 4-post rackmount accessories included; 2-9U STAND tower stands and 2-POSTRMTKITW 2 post rackmount kit available. Field-replaceable, hot-swappable internal batteries and external battery packs. Attractive all-black color scheme.

Package Includes

- SmartPro compact rackmount UPS System
- 4-post rackmount installation hardware
- USB and serial cabling

Features

- Tripp Lite's SmartPro Compact Rackmount Uninterruptible Power Supply (UPS) offers line interactive voltage regulation, network grade surge suppression and long lasting battery support for critical network hardware during blackouts and extended power failures
- Larger internal batteries and higher rated wattage make these systems ideal for network and telecom wiring closets and other limited-space installations
- Runtime is expandable with optional BP48V48RT4U and BP48V24-2U reduced-depth external battery packs
- Some external battery configurations require the use of Tripp Lite's [External Battery Configuration Software](#) (see manual)
- SMART1500CRMXL 2U rackmount 1500VA / 1440 watt UPS offers battery-derived sine wave AC output during power failures and extreme voltage variations
- Line interactive Automatic Voltage Regulation (AVR) provides two levels of voltage boost during brownouts and one level of voltage cut during overvoltage conditions to maintain regulated 120V nominal output over an input range of 83-145V
- Includes NEMA 5-15P input plug and NEMA 5-15R output receptacles

- Network management interfaces support simultaneous communications via USB port, DB9 serial port and optional SNMP/Web management accessory card slot
- Optional SNMPWEBCARD offers remote management and control of the UPS via direct network connection
- Additional ENVIROSENSE accessory, when used in conjunction with SNMPWEBCARD reports temperature, humidity and status of up to two directly connected contact closure sensors
- HID-compliant USB interface enables full integration with built-in power management and auto shutdown features of Windows and Mac OS X
- 97% efficiency in line power mode offers substantially lower operating costs than lower efficiency UPS types
- Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via all 3 network interfaces at once
- Includes PowerAlert monitoring software with USB and serial cables
- Emergency Power Off (EPO) interface
- Integrated 3-bank programmable PDU switching supports load shedding and remote-reboot of up to 3 individual connected devices
- 3-stage metered current monitoring and battery charge status LEDs; Utility power and voltage regulation LEDs; Audible alarm; Self-test
- 4-post rackmount accessories included; 2-9U STAND tower stands and 2-POSTRMKITWM 2-post rackmount kit available
- Field-replaceable, hot-swappable internal batteries and external battery packs
- Attractive all-black color scheme

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output kVA capacity (kVA)	1.5
Output Watt Capacity (watts)	1440
Output kW capacity	1.4
Output power factor	1
Nominal Output Voltage(s) Supported	120V
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	-14%, +8%
Output voltage regulation (Battery mode)	+/- 5%
Built-in UPS output receptacles	8 5-15R outlet(s)
Built-in controllable switched load banks	Three switchable single-outlet 5-15R load banks
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave
INPUT	
Rated input current (at maximum load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
Input circuit breaker	15A

UPS Input cord length (ft.)	10
UPS Input cord length (m)	3
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	6 min. (1440w)
Half load runtime (minutes)	14 min. (720w)
Expandable battery runtime	Extended runtime supported via optional external battery packs
External battery pack compatibility	BP48V24-2U (limit 1); BP48V48RT4U (multi-pack compatible)
DC system voltage (VDC)	48
Battery recharge rate (included batteries)	Less than 3 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC94-2U
Battery Access	Front panel battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage correction	Input voltages between 127 and 145 are reduced by 12%
Undervoltage correction	Input voltages between 96 and 108 are boosted by 12%
Severe undervoltage correction	Input voltages between 83 and 95 are boosted by 24%
LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Alarms	Audible alarm indicates power-failure, overload and low-battery conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; rear panel protected switches support nominal voltage selection
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	570
UPS AC suppression response time	Instantaneous
EMI / RFI AC noise suppression	Yes
PHYSICAL	

Installation form factors supported with included accessories	4 post 19 inch rackmount (mounting rail kit included)
Installation form factors supported with optional accessories	2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND)
Primary form factor	Rackmount
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3.5 x 17.5 x 19
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	8.9 x 44.4 x 48.3
Installed whole system total rack space height (rack spaces)	2U
Secondary form factor	Tower (requires 2-9USTAND)
UPS / Power Module weight (lbs)	60
UPS / Power Module weight (kg)	27.2
UPS Shipping dimensions (height x width x depth / inches)	9.2 x 24 x 20
UPS Shipping dimensions (height x width x depth / cm)	23.5 x 61 x 50.8
Shipping weight (lbs)	70.7
Shipping weight (kg)	32.1
UPS housing material	Steel
Cooling method	Fan
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	151.4
Battery mode BTU / hr. (full load)	544
COMMUNICATIONS	
Communications interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions
PowerAlert software	Included

Communications cable	USB and DB9 cabling included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	5.5 milliseconds
Low voltage transfer to battery power (setpoint)	83
High voltage transfer to battery power (setpoint)	145
SPECIAL FEATURES	
High availability UPS features	Hot swappable batteries
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (U.S., Canada & Puerto Rico)	2-year warranty, 3 year with registration . Note: registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Product Type	Related Model	Description	Qty.
Extended Warranties	WEXT5-500-1500	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1
External Battery Packs	BP48V24-2U	BP48V242U - External Battery Pack for UPS System	1
External Battery Packs	BP48V48RT4U	Shallow-Depth External Battery Pack For UPS Systems	1
Power Cables	P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Power Cables	P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
Power Cables	P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
Power Cables	P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
Power Cables	P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
Power Distribution	PDU1215	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
Power Distribution	PDUB15	Dual source Power Distribution Unit / PDU with Manual Transfer Switch enables Hot-swappable UPS Replacement in Critical Network Applications	1

Power Distribution	PDUMH15	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
Power Distribution	PDUMH15AT	Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching	1
Power Distribution	PDUMH15ATNET	Switched, Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching, individual outlet control and remote network interface	1
Power Distribution	PDUMNH15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
Power Distribution	PDUMNV15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
Power Distribution	PDUMV15	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
Power Distribution	PDUMV15NET	Switched, Metered PDU with Remote Monitoring - 0U Vertical Rackmount Power Distribution Unit for Networks with Individually Switchable Outlets, Current Metering, Remote Monitoring and Control	1
Power Distribution	PDUNV	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
Power Distribution	PDUV15	Safe, reliable power distribution for critical networking equipment	1
Printer Cables	P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
Rackmount/Wallmount Kits	2POSTRMKITWM	Enables 2-Post Rackmount or Wallmount Installation of Select Rackmount UPS Systems	1
Replacement Batteries	RBC94-2U	2U UPS Replacement Battery Cartridge for select Tripp Lite SmartPro UPS	1
SNMP Accessories	ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
SNMP Accessories	SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
Software	WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	1
Tower Stands	2-9USTAND	Enables Tower Placement of Rackmount UPS Systems	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3826.

Copyright © 2011 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.