



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SS7619-15

Tripp Lite Power Strip with Surge Suppression - Multiple outlets wherever you need them

Highlights

- 24 outlets
- 15-ft. cord
- 72-in. length
- 450-joule rating



Description

The SS7619-15 6-ft. power strip with AC surge suppression offers a convenient method of horizontal or vertical power distribution in equipment racks, computer rooms, workbenches, raceways and more. Includes 24 NEMA 5-15R output receptacles with 2.795-in. center-to-center spacing, 15-ft. AC line cord and adjustable mounting clips for installation in a wide variety of applications. Protects connected equipment from transient surges and line noise with built-in surge suppression rated at 450 joules. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15A resettable circuit breaker and attractive gray color scheme.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 24 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT: 6-ft. corded vertical/raceway power distribution strip

SURGE SUPPRESSION: 450 joules

Applications

- Offers outlet power distribution with surge suppression for multiple loads in equipment racks, computer rooms, workbenches and raceways in a variety of internetworking, telecommunications, audio/video and live sound applications.

Package Includes

- SS7619-15 Power Strip/Surge Suppressor
- Set of adjustable mounting clips
- Warranty information
- Instruction manual

Specifications

OVERVIEW	
Intended Application	Computer Networking, Industrial/Factory Floor
SYSTEM OVERVIEW	

Voltage compatibility	120 VAC
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Output volt amp capacity (amps)	15A
Outlet quantity / type	24 NEMA 5-15R
Outlet spacing	2.795-in. (center to center)
INPUT	
Recommended Electrical Service	120V
Input connection type	NEMA 5-15P
Input cord length (ft.)	15-ft.
Input cord length (m)	4.6
Input cord gauge, type	14 gauge, SJT
LEDS ALARMS & SWITCHES	
Switches	Lighted two-position power switch controls power to all outlets
Locking switch cover	Transparent locking switch cover prevents accidental shutoff
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	450 joules
UL1499 let through rating	
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (HWD/in)	72 x 1.5 x 1.5
Unit Dimensions (HWD/cm)	182.9 x 3.8 x 3.8
Material of construction	Metal
Mounting accessories included	Set of adjustable mounting clamps
Receptacle Color	Black
AC line cord color	Black
Style	Strip
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363

cUL / CSA (Canada)	cUL
WARRANTY	
Standard warranty period	Lifetime

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=1949.