



# SmartPro 120V 2.2kVA 1.7kW Line-Interactive UPS, Tower, Extended run, 3 DB9 ports

### MODEL NUMBER: SMART2200NET





#### **Description**

SMART2200NET intelligent line-interactive large tower UPS system protects servers, networking accessories and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Large internal batteries offer 27 minutes half-load runtime and 11 minutes fully loaded. Runtime is expandable with optional BP24V28-2U (limit 1) and BP24V70-3U external battery packs. 2200VA/1700W power handling capability supports a variety of networking, telecom and other sensitive electronic applications. Includes six protected outlets. Supports remote monitoring of UPS and site power conditions via built-in RS-232 enabled monitoring port, plus standard UPS monitoring via two built-in contact closure ports. PowerAlert® UPS monitoring and unattended shutdown software is available via free download. Built-in audible alarm and front-panel LEDs indicate line power, battery power, battery charge level, load level, plus voltage regulation status. Network-grade AC surge suppression protects equipment from damage and performance problems resulting from transient surges.

#### **Features**

- SMART 2200NET line interactive UPS offers battery derived AC output during power outages, voltage regulation during brownouts and overvoltages, plus network-grade AC surge suppression
- 2200VA/1700 watt power handling capability supports a variety of networking, telecom and other sensitive electronic devices
- Large internal batteries offer runtimes of 27 minutes at half load (1100VA/850 watts) and 11 minutes at full load (2200VA/1700 watts)
- Runtime is further expandable with optional external BP24V28-2U (limit 1) and BP24V70-3U (multi-pack compatible) battery packs
- Intelligent battery management system extends battery life
- Automatic Voltage Regulation (AVR) circuits maintain 120V nominal output over an input voltage range of 87-140V
- Includes 6 fully protected NEMA 5-15R outlets with 2 single outlet load banks that can be individually
  powered off and back on again via software interface
- DB9 ports enable data-saving unattended shutdown when used with PowerAlert software, available via FREE download from tripplite.eaton.com/products/power-alert
- Offers simultaneous monitoring of up to 3 directly connected devices through included DB9 contact closure and RS-232 enabled interfaces
- In addition to the contact closure monitoring of on battery, low battery and power restored messaging, built-in RS-232 interface supports messaging of UPS and line power status, including AC line voltage, DC battery voltage and remaining battery capacity

#### **Highlights**

- 2.2kVA / 2200VA line interactive, extended-run tower UPS
- 120V output, Corrects brownouts and overvoltages from 87V to 140V
- 3 DB9 communication ports (1 RS232 / 2 contact-closure)
- Front panel status LEDs with load and battery capacity display
- 2 independently switchable output load banks
- NEMA 5-15P input, 6 NEMA 5-15R outlets

### **Package Includes**

- SMART2200NET UPS System
- Three 6ft network cables
- Instruction manual





- Supports activate self-test and UPS output power control for delayed or immediate reboot of connected equipment
- Diagnostic LEDs (indicate 17 performance conditions)

## **Specifications**

OVERVIEW		
UPC Code	037332032041	
UPS Type	Line-Interactive	
INPUT		
Input Phase	Single-Phase	
Rated input current (Maximum Load)	15A	
Nominal Input Voltage(s) Supported	120V AC	
UPS Input Connection Type	5-15P	
Input Circuit Breakers	20A	
UPS Input Cord Length (ft.)	8	
UPS Input Cord Length (m)	2.4	
Recommended Electrical Service	20A 120V	
Input Cord Length (ft.)	8	
Input Cord Length (m)	2.44	
OUTPUT		
Output Capacity (VA)	2200	
Output Capacity (kVA)	2.2	
Output Capacity (Watts)	1700	
Output Capacity (kW)	1.7	
Output Capacity Details	Output is reduced to 1200W maximum with 1-2 external battery packs and 800W maximum with 3 or more external battery packs	
Power Factor	0.8	
Nominal Voltage Details	120v nominal output in battery mode	
Frequency Compatibility	60 Hz	
Output Voltage Regulation (Line Mode)	-13% / +5%	
Output Voltage Regulation (Battery Mode)	+/- 5%	
Load Management Receptacles	Two switchable single outlet 5-15R load banks	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	PWM sine wave	





Nominal Output Voltage(s) Supported	110V; 115V; 120V		
Output Receptacles	(6) 5-15R		
Individually Controllable Load Banks	Yes		
The state of the s			
BATTERY			
Battery Type	Valve Regulated Lead Acid (VRLA)		
Runtime Full Load (min.)	11 min. (1700W)		
Runtime Half Load (min.)	27 min. (850W)		
Expandable Runtime	Yes		
External Battery Pack Compatibility	<a class="productLink" href="//tripplite.eaton.com/External-24V-2U-Rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V28-2U">BP24V28-2U</a> (limit 1); <a class="productLink" href="//tripplite.eaton.com/External-24V-3U-Rack-Tower-Battery-Pack-select-Tripp-Lite-UPS-Systems~BP24V70-3U">BP24V70-3U</a> (multi-pack compatible)		
DC System Voltage (VDC)	24		
Battery Recharge Rate (Included Batteries)	Less than 9 hours from 10% to 90% (typical, full load discharge)		
VOLTAGE REGULATION			
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 87 to 140		
Overvoltage Correction	Input voltages between 127 and 140 are reduced by 12%		
Undervoltage Correction	Input voltages between 95 and 105 are boosted by 10%		
Severe Undervoltage Correction	Input voltages between 87 and 94 are boosted by 22%		
USER INTERFACE, ALERTS & CONTROLS			
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; set of 4 rear-panel switches control system enable and contact closure port inverter shutoff commands		
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status		
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions		
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status		
SURGE / NOISE SUPPRESSION			
UPS AC Suppression Joule Rating	720		
UPS AC Suppression Response Time	Instantaneous		
EMI / RFI AC Noise Suppression	Yes		
PHYSICAL			
Primary Form Factor	Tower		
Rack Height	OU		
Primary UPS Depth (mm)	318		





Low Voltage Transfer to Battery			
Transfer Time	2-4 milliseconds		
LINE / BATTERY TRANSFER			
Communications interiace	Outrade Goodie, DD9 Oction		
Description  Communications Interface	Contact closure; DB9 Serial		
Network Management Card	Network management not supported		
Communications Cable	3 DB9 cables included		
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at https://tripplite.eaton.com/products/power-alert		
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions; contact closure communications via two additional DB9 ports (3 total)		
COMMUNICATIONS			
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	867		
AC Mode Efficiency Rating (100% Load)	99%		
AC Mode BTU / Hr. (Full Load)	59		
Relative Humidity	0 to 95%, non-condensing		
Storage Temperature Range	5° to 122°F (-15° to 50°C)		
Operating Temperature Range	32° to 104°F (0° to 40°C)		
ENVIRONMENTAL			
Unit Weight (kg)	36.29		
Unit Weight (lbs.)	80.0000		
Unit Dimensions (hwd / in.)	17.000 x 9.000 x 12.500		
UPS Power Module Weight (lbs.)	80		
UPS Power Module Weight (kg)	36.29		
UPS Power Module Dimensions (hwd, in.)	17 x 9 x 12.5		
UPS Power Module Dimensions (hwd, cm)	43.18 x 22.86 x 31.75		
UPS Housing Material	Polycarbonate		
Shipping Weight (kg)	37.27		
Shipping Weight (lbs.)	82.16		
Shipping Dimensions (hwd / cm)	34.92 x 41.91 x 57.15		
Shipping Dimensions (hwd / in.)	13.75 x 16.50 x 22.50		
Primary UPS Width (mm)	229		





Lligh Voltage Transfer to Dettern			
High Voltage Transfer to Battery Power (Setpoint)	140		
FEATURES & SPECIFICATIONS			
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported		
High Availability UPS Features	Surge/noise protection		
APPLICATIONS			
UPS Applications	Large Network		
STANDARDS & COMPLIANCE			
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778		
Product Compliance	RoHS; FCC Part 15 Class A (USA)		
WARRANTY & SUPPORT			
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: <a class="insuranceLink" href="//tripplite.eaton.com/support/product-warranty-registration">Registration is required</a> for 3-year warranty.		
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>		

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.