



SmartOnline 3-Phase 120/208V 30kVA 24kW Double-Conversion UPS, Extended Run, 2 internal batteries, Network Card Options, Tower, DB9 Serial, Hardwire

MODEL NUMBER: SU30K3/3





Description

Tripp Lite's SU30K3/3 30kVA SmartOnline 3-Phase Intelligent, True On-Line UPS System has been redesigned to save valuable space and simplify runtime scalability. Power and battery components are combined into a single, small-footprint module (the smallest in its class). A robust internal battery runtime capability can be easily extended by installing additional optional internal battery packs through the convenient front panel access door. The SU30K3/3 provides mission-critical equipment with the highest level of power protection available. Large capacity 30,000VA/24,000 watt UPS continually converts incoming AC power into filtered DC power, and then resynthesizes it back into AC power with a pure sine wave. Perfectly regulated, continuous sine wave output with zero transfer time offers compatibility with all equipment types. IGBT inverter technology produces output power with <3% THD (total harmonic distortion), allowing connected equipment to perform at its peak. A 3:1 crest factor safely supports a variety of equipment, even those with wildly-fluctuating power demands. Extremely efficient operation saves money by lowering electricity consumption. Hardwire input and output connections. SU30K3/3 features 120/208V AC, 3-phase, 4-wire (plus ground), wye input and output. It also features a wide input voltage correction range: 96-144/166-250V AC. Frequency is 50 or 60 Hz (auto-selectable). SU30K3/3 includes internal power and battery components in a single small footprint tower module. Battery support can be extended with additional internal battery packs. A manual bypass switch as well as an automatic bypass function ensure 100% availability of connected equipment by safely passing through AC power when the UPS requires maintenance. Three built-in communication ports (RS-232, contact closure and AS-400) work with PowerAlert Software, available via free download, to simultaneously provide shutdown commands and reporting on multiple servers without the need for costly accessories. An accessory slot accepts an optional internal SNMP card (model # SNMPWEBCARD) for remote shutdowns, reboots and more. A Battery Start Switch allows cold restart of UPS during a prolonged blackout to utilize its batteries for periodic system access or data retrieval. An Emergency Power Off button turns UPS output OFF and disables Bypass output. Built-in Emergency Power Off (EPO) interface supports remote emergency

Highlights

- 30,000 VA (30kVA) tower UPS with internal batteries
- Saves valuable space and simplifies runtime scalability
- 3-phase hardwire input and output (120/208VAC). Wide input voltage correction range (96 - 144V AC / 166 - 250V AC)
- IGBT technology and zero transfer time, on-line, doubleconversion operation
- 3 communication ports, Network card slot and EPO jack

Package Includes

- SU30K3/3 UPS System (power and battery components in one module)
- DB9 cabling
- · Warranty information
- · Instruction manual





shutdown in large facilities. Front panel combination LCD/LED display alerts users to a variety of UPS operational modes and conditions. A start-up service program is recommended to enhance the reliability of the installation.

Features

- Saves valuable space: power and battery components combined into a single small-footprint module
- Simplifies runtime scalability: convenient front panel battery access for expandable runtime with additional internal battery packs
- True on-line, double conversion UPS with IGBT technology provides pure, sine wave AC output at all times
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- 30,000VA/24,000 watt power capacity with 3-phase, hardwire 120/208V AC input/output connections
- Features a wide input voltage correction range: 96 144/166 250V AC
- Included internal batteries provide 13 minutes runtime at half load (12,000 watts) and 5 minutes runtime at full load (24,000 watts)
- 3:1 crest factor safely supports a variety of equipment, even those with wildly-fluctuating power demands
- Extend runtime by installing an optional internal battery pack (model # SURBC2030) through the front
 panel access door. SU30K3/3 includes 3 internal battery packs and accepts 1 additional internal battery
 pack. A standalone battery module compartment with a 4 battery pack capacity and daisy-chain
 capability (model # SUBF2030) is available to further extend runtime.
- 3 communication ports (RS-232, contact closure and AS-400)
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD, MODBUSCARD and RELAYIOCARD
- Manual bypass switch as well as an automatic bypass function ensures 100% availability of connected equipment by safely passing through AC power when the UPS system requires maintenance
- Battery Start Switch allows cold restart of UPS during a prolonged blackout to utilize its batteries for periodic system access or data retrieval
- · Emergency Power Off button turns UPS output OFF and disables Bypass output
- Serial port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from tripplite.eaton.com/products/power-alert
- Start-up service program is recommended to enhance the reliability of the installation
- Built-in Emergency Power Off (EPO) interface supports remote emergency shutdown in large facilities
- Combination LED/LCD display

Specifications

OVERVIEW		
UPC Code	037332136671	
UPS Type	On-Line	
INPUT		
Input Phase	3-Phase	
Rated input current (Maximum Load)	90A (per phase, online)	





Nominal Input Voltage(s) Supported	120/208V 3-PH Wye	
Nominal Input Voltage Description	3-Phase Wye, 4 wire (L1, L2, L3, N, G)	
UPS Input Connection Type	Hardwire	
ОИТРИТ		
Output Capacity (VA)	30000	
Output Capacity (kVA)	30	
Output Capacity (Watts)	24000	
Output Capacity (kW)	24	
Power Factor	0.8	
Crest Factor	3:1	
Frequency Compatibility	50 / 60 Hz	
Output Voltage Regulation (Line Mode)	+/- 2%	
Output Voltage Regulation (Battery Mode)	+/- 2%	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	Pure Sine wave	
Nominal Output Voltage(s) Supported	120/208V 3-PH Wye	
Output Receptacles	Hardwire	
Individually Controllable Load Banks	No	
BATTERY		
Runtime Full Load (min.)	5 min. (24kw)	
Runtime Half Load (min.)	13 min. (12kw)	
Expandable Runtime	Yes	
Expandable Runtime Description	Includes a battery housing with space for 1 optional SURBC2030 battery pack for extended runtime. Additional runtime capacity is available by adding SUBF2030 and additional SURBC2030 batteries - see runtime chart for specific recommendations	
External Battery Pack Compatibility	BP240V350; BP240V400; BP240V400C ; BP240V500; BP240V500C; SUBF2030 (holds 4 SURBC2030);	





Internal UPS Replacement Battery Cartridge	SURBC2030 ">a>a>a>a>a>a>a>a>a>a>a>a>a>a>a>a>a>a>a
Battery Replacement Description	Hot-swappable, replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	Maintains continuous operation without using battery power during overvoltages to 144 / 250 (3-Phase, 4-Wire, wye), reducing output within 2% of nominal
Undervoltage Correction	Maintains continuous operation without using battery power during brownout / undervoltage conditions to 96 / 166 (3-Phase, 4-Wire, wye)
USER INTERFACE, ALERTS & CON	ITROLS
Front Panel LCD Display	SELECTABLE LCD DISPLAY: indicates a wide range of UPS operational and fault/warning conditions including operational mode, alarm/shutdown conditions, input/output voltage/frequency, battery voltage, load percentage and more (see manual)
Switches	ON button turns UPS's inverter ON. "OFF" button turns UPS's inverter OFF. "Select" Button browses through items displayed on LCD screen. "Enter" button selects items displayed on LCD screen. "Select" and "Enter" buttons used simultaneously mute UPS alar
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch
Audible Alarm	Alarms warn against a variety of operational conditions: low-battery, overload, shutdown, bypass and more
LED Indicators	7 LED DISPLAY: AC input, bypass input, AC-DC charger, DC-AC inverter, AC output, bypass operation and battery operation
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	2032
AC Suppression Response Time	Instantaneous
PHYSICAL	
Primary Form Factor	Tower
Cooling Method	Fans
Installation Form Factors Supported with Included Accessories	Tower
Primary UPS Depth (mm)	963
Primary UPS Height (mm)	912
Primary UPS Width (mm)	495
Shipping Dimensions (hwd / in.)	43.50 x 28.00 x 44.00
Shipping Dimensions (hwd / cm)	110.49 x 71.12 x 111.76
Shipping Weight (lbs.)	475.00
Shipping Weight (kg)	215.46
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	91.19 x 49.53 x 96.27





35.9 x 19.5 x 37.9		
300.28		
662		
ENVIRONMENTAL		
+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius		
+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius		
5 to 95%, non-condensing		
3150		
1940		
COMMUNICATIONS		
SNMPWEBCARD; TLNETCARD ; WEBCARDLX; MODBUSCARD ; RELAYIOCARD		
RS232, contact closure and AS400 monitoring ports are supported by 3 separate DB9 ports		
For local monitoring via the UPS's built-in communication ports, download PowerAlert software at https://tripplite.eaton.com/products/power-alert		
DB9 cabling included		
DB9 Serial; Contact closure; Slot for SNMP/Web interface		
LINE / BATTERY TRANSFER		
No transfer time (0 ms.) in online, double-conversion mode		
Maintains continuous operation during undervoltages as low as 96/166V AC (3-Phase, 4-Wire, wye). Below this point, output is maintained utilizing battery reserves.		
Maintains continuous operation during overvoltages as high as 144 / 250V AC (3-Phase, 4-Wire, wye). Above this point, output is maintained utilizing battery reserves.		
FEATURES & SPECIFICATIONS		
Cold-start operation supported		
Automatic inverter bypass; Hot swappable batteries		
1-year limited warranty		
2-year limited warranty		
1-year limited warranty		
2-year limited warranty		





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.