



**Tripp Lite**  
 1111 West 35th Street  
 Chicago, IL 60609 USA  
 Telephone: +(773) 869 1234  
 E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SR2POST

### 45U 2-Post SmartRack Open Frame Rack - Organize and Secure Network Rack Equipment



#### Highlights

- 45U 2-post open frame rack
- Black aluminum with round threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

#### Description

SmartRack 2 post open frame racks are ideal for space constrained or cost conscious 19-inch rack mount applications. Multiple units can be bolted together side by side.

#### Features

- Supports 800lbs of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- Numbered mounting positions
- Bolt down provisions
- Self squaring design
- Black finish
- Easy assembly
- Five year repair or replacement warranty

#### Specifications

PHYSICAL	
Shipping weight (lbs)	29
Shipping Dimensions (HWD/in)	7 X 3 X 85
Unit Dimensions (in)	84 x 20.3 x 4.75 (14" total depth with support base)

#### Related Items

#### Optional Products

Product Type	Related Model	Description	Qty.
--------------	---------------	-------------	------

KVM Switches & Accessories	<a href="#">B019-000</a>	KVM Switch Accessories - 2-Post Rackmount Bracket for B020,B021, B040, and B070 Consoles and KVM Consoles	-
KVM Switches & Accessories	<a href="#">B020-008-17-IP</a>	Console KVM Switch - 8-Port NetDirector 1U Rackmount Console IP KVM Switch w/17" LCD	-
KVM Switches & Accessories	<a href="#">B021-000-17</a>	Rackmount Console - 1U Rackmount Console with 17" LCD	-
Rackmount Consoles	<a href="#">B021-000-19</a>	Rackmount Console - 1U Rackmount Console with 19" LCD	-
Rackmount Consoles	<a href="#">B021-000-19-SH</a>	Rackmount Console - 1U Short-Depth Rackmount Console with 19" LCD	-
KVM Switches & Accessories	<a href="#">B040-008-19</a>	NetController 19" VGA Console KVM Switch - 8 Port	-
KVM Switches & Accessories	<a href="#">B040-016-19</a>	NetController 19" VGA Console KVM Switch - 16 Port	-
Patch Panels	<a href="#">N252-012</a>	12-Port Cat6 Patch Panel 568B	-
Patch Panels	<a href="#">N252-024</a>	24-Port Cat6 Patch Panel 568B	-
Patch Panels	<a href="#">N252-048</a>	48-Port Cat6 Patch Panel 568B	-
Rack Accessories	<a href="#">SRBOLTDOWN</a>	Bolt-Down Kit (Secures included stabilizing brackets or optional stabilizing plates to facility floor.)	-
Rack Accessories	<a href="#">SRCABLEDUCT1U</a>	1U Horizontal Cable Manager (Finger duct with cover.)	-
Rack Accessories	<a href="#">SRCABLEDUCTVRT</a>	6 (1.8 m) Vertical Cable Manager (Double finger duct with cover; toolless mounting.)	-
Rack Accessories	<a href="#">SRCABLELADDER</a>	10 x 1 (3 m x 0.3 m) Cable Ladder (Includes 2 sections; requires SRCABLETRAY.)	-
Rack Accessories	<a href="#">SRCABLERING1U</a>	1U Horizontal Cable Manager (Flexible ring type.)	-
Rack Accessories	<a href="#">SRCABLERING2U</a>	2U Horizontal Cable Manager (Flexible ring type.)	-
Rack Accessories	<a href="#">SRCABLERINGVRT</a>	6 (1.8 m) Vertical Cable Manager (Flexible ring type; toolless mounting.)	-
Rack Accessories	<a href="#">SRFAN3U</a>	3U Fan Panel, 120V (3 high-performance fans; 210 CFM; 5-15P plug.)	-
Rack Accessories	<a href="#">SRSCREWS</a>	Threaded hole hardware kit - 50 each #12-24 screws	-
Rack Accessories	<a href="#">SRSHELF2P</a>	2U Cantilever Fixed Shelf (60 lb / 27 kg capacity; 18-in. / 457 mm depth.)	-
Rack Accessories	<a href="#">SRXFAN3U</a>	3U Fan Panel, 230V (3 high-performance fans; 210 CFM; C14 inlet.)	-
Rack Accessories	<a href="#">UPSHDEARKIT</a>	Heavy-Duty Mounting Ear Kit (Supports 2U cabinets up to 65 lb / 29 kg from front vertical rails in 4-post racks and enclosures. Not suitable for 2-post mounting.)	-

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3208](http://www.tripplite.com/en/products/model.cfm?txtModelID=3208).