

SmartOnline 208/240, 230V 6kVA 4.2kW Double-Conversion UPS, 6U Rack/Tower, Extended Run, Oversize Batteries, Network Card Slot, DB9, Hardware

MODEL NUMBER: SU6000RT3UHVXL



Description

Tripp Lite Smart Online UPS systems offer high performance power protection ideal for critical server and network equipment in datacenters, computer rooms and network closets. Online, double-conversion Uninterruptible Power Supply (UPS) maintains perfectly regulated output power by continuously converting raw AC input to DC, then re-converting output back to AC. Fully regulated sine wave AC output with +/-2% voltage regulation powers network equipment continuously, even during severe brownouts and overvoltages, all without depleting UPS battery reserves. Maintains battery-derived AC output during power failures with zero transfer time. Extended runtime options available. Interactive LCD interface reports UPS operating mode, detailed UPS and site-power data, plus enables a variety of UPS setup and configuration options. Highly efficient operation in optional economy mode saves BTU heat output and energy costs. Network management interfaces support communications via RS-232, contact-closure and slot for optional network management card options. Built-in DB9 port offers both enhanced RS-232 data and basic contact closure monitoring ability. PowerAlert monitoring software is available via free download. Emergency Power Off (EPO) interface. LED display reports UPS operating mode, line power availability, battery mode operation, inverter operation, ECO mode status and output power availability. Audible alarm with push-button momentary alarm-cancel and silent-mode LCD configuration options. Programmable self-test. Fault-tolerant auto-bypass mode. Field-replaceable, hot-swappable internal batteries and external battery packs.

Features

- True on-line, double conversion UPS provides pure, sine wave AC output at all times
- World-wide compatibility with Euro 50Hz and High Voltage North American 60Hz power
- Maintains continuous operation through blackouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, electrical impulses, frequency variations and other hard to solve power problems

Highlights

- 6000VA / 6kVA / 4200W on-line double-conversion UPS
- 200/208/220/230/240V 50/60Hz output, Economy mode option
- 6U Rack/Tower compatible; Hot-swappable battery modules
- RS232 & EPO ports; Slot for network card options
- Front panel LEDs with detailed LCD monitoring and control screen
- Ships with high capacity BP240V10RT3U battery pack
- Hardwire input (3 wire); Hardwire output

Package Includes

- SU6000RT3UPM 3U UPS Power Module
- BP240V10RT3U 3U external battery pack
- Serial and EPO cables
- Mounting hardware to support each 3U module in 4 post rack enclosures
- 2-9USTAND tower stand set
- Warranty information
- Instruction manual



Powering Business Worldwide



- 6000VA/4200 watt power capacity with hardwire input/output connections
- Accepts input voltages between 156 and 276, regulating output within 2% of selectable 200/208/220/230/240v AC output
- 30 minutes runtime at half load (2100W) / 12 minutes at full load (4200W) with included BP240V10RT3U external battery pack
- Expandable runtime with multiple external battery packs
- Intelligent battery management system extends battery life
- Innovative design makes unit adaptable for rackmount, tower, or stacking applications
- Power module and battery pack require only 3 rack spaces each (6U total rack space usage)
- DB9 serial port for network interface; SNMP compatible
- Compatible with Tripp Lite UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD, MODBUSCARD and RELAYIOCARD
- Serial port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from triplite.eaton.com/products/power-alert
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Diagnostic LEDs
- Mounting hardware included with each 3U module for 4 post rackmount installation, 2 post telecom rack compatible with separate purchase 2POSTRMKITHD (2 required)
- Includes RJ11 EPO (emergency power off) port and interconnection cable
- \$250,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332172105
UPS Type	On-Line
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	30A
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 220V AC; 230V AC; 240V AC
UPS Input Connection Type	Hardwire
UPS Input Connection Description	Supports North American 208/240V input (L1,L2,G) and International 230/220/240V (L,N,PE) input wiring; Optional SUPDM11 backplate adds 2 L6-30R outlets and L6-30P input cord
Input Circuit Breakers	40A double-pole
Recommended Electrical Service	30A 208/220/230/240V
OUTPUT	
Output Capacity (VA)	6000
Output Capacity (kVA)	6
Output Capacity (Watts)	4200
Output Capacity (kW)	4.2

Output Capacity Details	Supports up to 102% load continuously in double conversion mode, 102 to 125% for 1 minute, 126% to 150% for 30 seconds; Loads over 150% trigger immediate bypass mode operation to support loads directly from mains power; Double conversion mode is automatically restored as load levels are reduced to 90% or less
Power Factor	0,7
Crest Factor	3:1
Nominal Voltage Details	Voltage selection via front panel LCD interface
Frequency Compatibility	50 / 60 Hz
Frequency Compatibility Details	Output frequency matches input nominal on startup
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 2%
Output Receptacle Backplate Options	Optional SUPDM11 backplate adds 2 L6-30R outlets and L6-30P input cord
Output Circuit Breakers	40A double-pole
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	200V; 208V; 220V; 230V; 240V
Output Receptacles	Hardwire
Individually Controllable Load Banks	No
BATTERY	
Runtime Full Load (min.)	12 min. (4200w)
Runtime Half Load (min.)	30 min. (2100w)
Expandable Runtime	Yes
Expandable Runtime Description	Includes one expandable BP240V10RT3U external battery pack; built-in daisychain throughput connected supports the connection of multiple additional BP240V10RT3U external battery packs
External Battery Pack Compatibility	BP240V10RT3U
DC System Voltage (VDC)	240
Battery Recharge Rate (Included Batteries)	Less than 6 hours from 10% to 80% (typical, full load discharge)
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	2% output voltage regulation during overvoltages to 276

Undervoltage Correction	2% output voltage regulation during undervoltages to 156
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions
Alarm Cancel Operation	Alarm cancel switch
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
LED Indicators	6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status; LCD screen offers additional information and control options
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Rackmount
Rack Height	6U
Cooling Method	Fan
Included Battery Pack Dimensions (hwd / in.)	5.2 x 17.5 x 25
Included Battery Pack Weight (lbs.)	136.5
Included Battery Pack Weight (kg)	61.92
Included Mounting Accessory Description	2 sets of adjustable 4 post rack rails included (for UPS and battery pack components); 2-9USTAND tower kit included (supports up to 9U in tower format)
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2POSTRMKITHD);
Minimum Required Rack Depth (cm)	95.25
Minimum Required Rack Depth (inches)	37.5
Optional Mounting Accessory Notes	2 sets of 2POSTRMKITHD ; required for 2 post rackmount installation of separate power module and battery pack
Primary UPS Depth (mm)	660
Primary UPS Height (mm)	132
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	27.50 x 40.00 x 48.00
Shipping Dimensions (hwd / cm)	69.85 x 101.60 x 121.92
Shipping Weight (lbs.)	323.00
Shipping Weight (kg)	146.51
UPS Housing Material	Steel



Powering Business Worldwide



Green Energy-Saving Features	High efficiency economy mode operation; Schedulable daily hours of economy mode operation
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.