

TAA-Compliant 45U SmartRack 2-Post Open Frame Rack - Organize and Secure Network Rack Equipment

MODEL NUMBER: SR2POSTAA



Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 45U 2-post open frame rack
- Black aluminum with 12-24 threaded and numbered mounting holes
- Toolless button holes to accept PDUs or cable managers

Description

Tripp Lite's TAA Compliant 45U 2-Post SmartRack Open Frame Rack is an economical way to accommodate 45U of rack space for 19-inch rackmount applications in limited spaces that do not require a lockable enclosure. Its heavy-duty, aluminum construction can safely support 800 lbs. of rackmount equipment, and its open design provides easy access to equipment and cabling. The black, textured powder coat finish makes it resistant to scratching while giving it a "classic," attractive appearance. The SR2POSTAA is easy to install due to a self-squaring design combined with 12-24 threaded and numbered mounting positions along with bolt down provisions. It provides toolless button-hole mounting for vertical PDUs and cable managers. In high-density environments, multiple units can be bolted together side by side for easy expansion or customization. The SR2POSTAA is in full TAA (Trade Agreements Act) compliance for easy addition to GSA Schedule contracts and other government contracts, as well as EIA-compliant for vendor-neutral compatibility with 19-inch rackmount equipment. It is backed by a 5-year warranty.

Features

- Supports 800lbs of rackmount equipment
- Textured powder coat finish
- Heavy Duty Aluminum construction
- 12-24 threaded and numbered mounting positions
- Bolt down provisions
- Toolless button holes to accept PDUs or cable managers
- Self squaring design
- Black finish
- Easy assembly

Specifications



Powering Business Worldwide



OVERVIEW	
UPC Code	037332154040
Rack Type	Open-Frame
PHYSICAL	
Color	Black
Rack Height	45U
EIA Mounting Rails	12-24 threaded and numbered mounting holes
Mounting Holes or Slots	Yes
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Shipping Dimensions (hwd / in.)	4.53 x 6.50 x 87.99
Shipping Dimensions (hwd / cm)	11.51 x 16.51 x 223.49
Shipping Weight (lbs.)	33.10
Shipping Weight (kg)	15.01
Unit Dimensions (hwd / in.)	84.010 x 20.300 x 13.500
Unit Dimensions (hwd / cm)	213.36 x 51.56 x 12.07
Weight Capacity - Stationary (kg)	363
Weight Capacity - Stationary (lbs.)	800
Mounting Details	Toolless button holes to accept PDUs or cable managers
FEATURES & SPECIFICATIONS	
Pre-Installed Casters	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.