

SmartOnline 208/240 & 120V 6kVA 5.4kW Double-Conversion UPS, 6U Rack/Tower, Extended Run, Network Card Options, USB, DB9 Serial, Bypass Switch, Outlets

MODEL NUMBER: SU6000RT4UTF



Description

Featuring true on-line operation with pure sine wave output, zero transfer time to battery and complete UPS replacement capability with no downtime, the SU6000RT4UTF provides the highest level of protection available for mission-critical equipment from all power problems. It converts incoming AC power to DC, and re-converts it back to filtered AC output with a pure sine wave, providing ultimate protection. The SU6000RT4UTF has a 6kVA/5400W capacity and 16 AC outlets (four 5-15R; eight 5-15/20R; two L6-20R; two L6-30R). Using the 2U transformer, the SU6000RT4UTF can support both low- and high-voltage equipment.

With its detachable PDU, the SU6000RT4UTF is easily hot-swappable by a user of any skill set—no need for lengthy and expensive service calls, and no downtime if a repair or battery replacement is needed. In bypass mode, the PDU passes power to equipment without the use of the power and battery modules, allowing them to be removed while keeping your application in operation.

UPS battery backup keeps connected equipment operational through short power failures, and provides time to save data and perform an orderly system shutdown in case of a prolonged blackout. The SU6000RT4UTF's runtime can be expanded with external battery packs.

The SU6000RT4UTF features a highly efficient (96%) economy mode setting that can significantly reduce a facility's energy costs by minimizing heat output, reducing cooling requirements and consuming less electricity.

An LCD display with LED indicators enables IT personnel to monitor operating modes and conditions. The LCD/LED panel rotates for viewing in horizontal rack or vertical tower installations and includes an audible alarm that signals various conditions.

The SU6000RT4UTF features a USB port and a DB9 port that, when used with downloadable PowerAlert® software, provides comprehensive network power monitoring and control. An optional network management card enables the UPS to operate as an IP managed device.

The unit requires only 6U of rack space in a standard rack enclosure and can be installed in a 2-post rack using the 2POSTRMKITHD accessory (2 required), or in a tower configuration with the 2-USTAND accessory.

Features

- SU6000RT4UTF 6000VA / 6kVA / 5400 watt on-line, double-conversion UPS system in a 6U rack/tower compatible configuration (4U power module plus 2U low-voltage transformer; at 208V nominal, output is limited to 4992 watts)
- Full-time active power conditioning maintains clean, continuous dual-conversion AC output free of voltage fluctuations, power interruptions and line noise

Highlights

- 6000VA / 6kVA / 5400W on-line double-conversion 4U rack/tower UPS, Sine Wave
- Includes 4U UPS power module with maintenance bypass switch and 2U transformer module
- Extended runtime options, Interactive LCD interface, Economy-mode option, 0.9 power factor
- USB, RS232 & EPO ports; Slot for network management card options
- NEMA L6-30P 208/240V 60Hz input; NEMA L6-30R, L6-20R (208/240V), 5-15/20R and 5-15R (120V) outlets

Package Includes

- SU6000RT4UHVPM hot swappable UPS Power Module
- SUPDMB6K Detachable PDU with Maintenance Bypass Switch
- SU6000XFMR2U low voltage transformer
- 1 x 6-ft. USB Cable
- 1 x 6-ft. DB9 Cable
- 4-Post Rackmount Hardware (2 sets)



Powering Business Worldwide



- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Detachable back panel PDU contains input line cord connection, output receptacles and manual bypass switch to support hot-swappable whole UPS replacement with no interruption to connected equipment
- L6-30P input plug
- UPS supported outlets include two L6-30R, two L6-20R, 8 5-15/20R and 4 5-15R outlets
- Included rail kit supports 4U 19-inch rack-mount installation in 4-post racks
- Optional 2POSTRMKITHD supports installation in 2-post 19-inch racks (2 required for SU6000RT4UTF)
- Optional 2-9USTAND supports upright tower placement (1 required for SU6000RT4UTF)
- Maximum installed rack depth of only 21.8 in. / 55.3 cm
- Maintains full-time sine wave output within 2% of selected 208/240V and 120V nominal at 60 Hz in double conversion mode
- Corrects brownouts to 156V at full load (100V at 50% load or less)
- Corrects overvoltages to 290V at full load (300V at 90% load or less)
- Double-conversion operation offers full-time AC to DC, then DC to AC conversion to maintain perfectly regulated sine wave AC output with enhanced protection from harmonic distortion, fast electrical impulses and other hard-to-solve power problems not addressed by other UPS types
- High efficiency ECONOMY MODE operation significantly reduces BTU heat output and operating energy costs
- Network-grade AC surge and noise suppression
- Supports detailed monitoring of equipment load levels, self-test data and utility power conditions via built-in RS-232, USB and optional network management card options
- Compatible with UPS management card options TLNETCARD, WEBCARDLX, SNMPWEBCARD, MODBUSCARD and RELAYIOCARD
- Optional RELAYIOMINI interface module offers three configurable hard contact closure outputs for custom event notification (requires removal of USB interface module)
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and macOS
- USB & Serial ports enable data-saving unattended shutdown when used with PowerAlert software, available via FREE download from triplite.eaton.com/products/power-alert
- Front panel LEDs and LCD readout with scroll controls support front-panel visual monitoring of all major UPS functions with support for a variety of control options to support advanced UPS settings and configurations
- LED/LCD display panel rotates for viewing in rack-mount or tower configurations
- Supports Emergency Power Off (EPO) via built-in interface
- Battery independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even when batteries are expired and require replacement
- BP192V12-3U external battery packs are field replaceable and hot swappable
- Intelligent battery management system with temperature-compensated charging extends battery life
- Some external battery configurations require the use of External Battery Configuration Software (see manual)

Specifications

OVERVIEW	
UPC Code	037332157102
UPS Type	On-Line
INPUT	



Powering Business Worldwide



Input Phase	Single-Phase
Rated input current (Maximum Load)	31.9A (200V), 30.6A (208V), 29A (220V), 27.7A (230V), 26.6A (240V)
Nominal Input Voltage(s) Supported	208V AC; 240V AC
Nominal Input Voltage Description	Factory configured to 208V
UPS Input Connection Type	L6-30P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	30A
OUTPUT	
Output Capacity (VA)	6000
Output Capacity (kVA)	6
Output Capacity (Watts)	5400
Output Capacity (kW)	5.4
Output Capacity Details	Output capacity de-rates to 4992 watts when used at 208V nominal; Supports up to 105% load continuously in double conversion mode, 106 to 125% for 1 minute, 126% to 150% for 30 seconds; Loads over 150% trigger immediate bypass mode operation to support loads directly from mains power; Double conversion mode is automatically restored as the overload is cleared
Power Factor	.9
Crest Factor	3:1
Nominal Voltage Details	This configuration requires the Power Module be set to 208 or 240V output voltage; included step-down transformer supports 120V output (when the voltage-selection switch on the transformer module is set to match the 208 or 240V power module setting)
Frequency Compatibility	60 Hz
Frequency Compatibility Details	Output frequency regulation +/-0.05Hz (free running)
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 2%
Output Receptacle Details	Output receptacles and input line cord are mounted on a detachable PDU backplate with bypass switch to enable hot-swappable power module replacement
Output Circuit Breakers	High voltage 20A breaker protects L6-20R outlets, L6-30R outlets are unbreakered; Low voltage 20A breakers protect 4 5-15/20R outlets each; Low voltage 15A breakers protect 2 5-15/20R outlets each
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	120V; 208V; 240V
Output Receptacles	(4) 5-15R; (8) 5-15/20R; (2) L6-20R; (2) L6-30R
Individually Controllable Load Banks	No

BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	2 min. (5400W)
Runtime Half Load (min.)	8.5 min. (2700W)
Expandable Runtime	Yes
External Battery Pack Compatibility	BP192V1037C-1PH; BP192V12-3U ; BP192V1407C-1PH; BP192V557C-1PH; BP192V787C-1PH; BP192V5RT2U ; (limit 1)
DC System Voltage (VDC)	192
Battery Recharge Rate (Included Batteries)	6 hours from 10% to 90% (typical, full load discharge)
Battery Access	Front panel battery access door
Internal UPS Replacement Battery Cartridge	 RBC5-192 ;
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Online, double-conversion power conditioning
Overvoltage Correction	Corrects overvoltages as high as 300V (<90% load) and 280V (full load)
Undervoltage Correction	Corrects undervoltages as low as 100 (<50% load) and 155V (full load); derates linearly
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Switches	Includes main power off/on switch, plus 2 switches to set and execute scrollable LCD functions. A manual bypass switch featured on the detachable PDU allows for complete removal of the UPS during routine maintenance without disrupting power to connected loads.
Alarm Cancel Operation	Alarm cancel switch
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
LED Indicators	6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	2595
UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Primary Form Factor	Rackmount
Rack Height	6U
Cooling Method	Fans

Included Mounting Accessory Description	Two sets of adjustable 4 post 19 inch rackmount installation rails included
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount (2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND)
Maximum Device Depth (cm)	55.37
Maximum Device Depth (in.)	21.8
Maximum Device Depth (mm)	554
Minimum Required Rack Depth (cm)	63.50
Minimum Required Rack Depth (inches)	25
Minimum Required Rack Depth with External Battery Pack (cm)	74
Minimum Required Rack Depth with External Battery Pack (in.)	29
Minimum Required Rack Depth without External Battery Pack (cm)	65
Minimum Required Rack Depth without External Battery Pack (in.)	25.7
Optional Mounting Accessory Notes	2 post rackmount installation requires two 2-Post-Rack-Mount-Installation-Kit-3U-Larger-UPS-Transformer-Battery-Pack-Components~2POSTRMKITHD ; accessories; Tower installation requires one 2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND ; accessory
Primary UPS Depth (mm)	526
Primary UPS Height (mm)	174
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	22.20 x 23.60 x 29.10
Shipping Dimensions (hwd / cm)	56.39 x 59.94 x 73.91
Shipping Weight (lbs.)	234.40
Shipping Weight (kg)	106.32
Stepdown Transformer Dimensions (hwd / cm)	8.89 x 44.45 x 55.37
Stepdown Transformer Dimensions (hwd / in.)	3.50 x 17.50 x 21.80
Stepdown Transformer Height (mm)	89
Stepdown Transformer Width (mm)	445
Stepdown Transformer Depth (mm)	554
Stepdown Transformer Weight (kg)	32.93
Stepdown Transformer Weight (lbs.)	72.6
UPS Housing Material	Steel

UPS Power Module Dimensions (hwd, cm)	17.40 x 44.45 x 52.58
UPS Power Module Dimensions (hwd, in.)	6.85 x 17.50 x 20.70
UPS Power Module Weight (kg)	52.71
UPS Power Module Weight (lbs.)	116.2
Unit Dimensions (hwd / in.)	10.050 x 17.500 x 21.800
Unit Weight (lbs.)	188.800
Unit Weight (kg)	85.64
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	1767
AC Economy Mode BTU / Hr. (Full Load)	768
AC Mode Efficiency Rating (100% Load)	90%
AC Economy Mode Efficiency Rating (100% Load)	96%
Online Mode Heat Dissipation (BTU/Hr) @ Full Load	1767
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	2279
Operating Elevation	Up to 6500 ft.
Audible Noise	60 dBA at front side 1 meter
COMMUNICATIONS	
Network Management Cards	 TLNETCARD WEBCARDLXE MODBUSCARD RELAYIOCARD
Network Monitoring Port Description	Additional contact closure support with optional RELAYIOCARD and RELAYIOMINI interface cards. RELAYIOMINI installation requires removal of panel containing USB ports
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert software at https://tripplite.eaton.com/products/power-alert
Communications Cable	USB, DB9 serial and EPO cables included
WatchDog Compatibility	Yes
Network Management Card Description	Network management card optional
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)



Powering Business Worldwide



LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Transfer Time (Economy Mode)	8ms. typical power failure response in optional economy mode
Low Voltage Transfer to Battery Power (Setpoint)	156V (full load) / 100V (50% load or less, derates linearly)
High Voltage Transfer to Battery Power (Setpoint)	280V (full load) / 300V (90% load or less)
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring (requires WEBCARDLXE); Automatic inverter bypass; Hot swappable batteries; Hot swappable UPS power module; Manual bypass switch; Remote management; Surge/noise protection; Zero transfer time
Green Energy-Saving Features	High efficiency economy mode operation; Support for daily startup and shutoff; Schedulable daily hours of economy mode operation
APPLICATIONS	
UPS Applications	Mission Critical Applications
STANDARDS & COMPLIANCE	
Product Certifications	IEC 61000; CSA (Canada); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA); UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.